





- 1) FINISH: SILVER PLATE
- 2) VOLTAGE RATING: 100VDC
- 3) DWV: 350 VDC FOR 1 MINUTE
- 4) TEMPERATURE COEFFICIENT: 7K0-00321 (Z7S)
- 5) CAPACITANCE RANGE (1000HRS): 90pF-120pF
- 6) D.F. MAX = 3.5%
- 7) BAND COLOR: GREEN
- 8) INSULATION RESISTANCE: 50 GIGAOHM MIN AT 100 VDC FOR 2 MINUTES
- 9) FT CIRCUIT

NOTE: CIRCUIT TYPE: FT

- 10) THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND IS COPYRIGHTED. EXCEPT WITH THE WRITTEN PERMISSION OF SPECTRUM CONTROL, INC. OR ITS SUBSIDIARIES, SUCH INFORMATION SHALL NOT BE PUBLISHED OR DISCLOSED TO OTHERS, OR USED FOR ANY PURPOSE AND THIS DOCUMENT SHALL NOT BE DUPLICATED IN WHOLE OR IN PART.



		00	REV. NO.	UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES. SCALE: 1:1	TOLERANCES UNLESS OTHERWISE SPECIFIED Fractions $\pm 1/64$	 SPECTRUM CONTROL INC.	FAIRVIEW PENNSYLVANIA	
		CN 23536-CPD	CHANGE NOTICE		Dec. $.xx \pm$ ---	Dwn. KAUFFMAN	Description	C8150173321101B
					Dec. $.xxx \pm$.003	Date: 10-25-05	FT CAPACITOR	
					Angles $\pm 0^\circ 30'$	Engr: JOE V. III		
				 THIRD ANGLE PROJECTION	CODE IDENT. NO. 0LSP2	Sheet <u>1</u> of <u>1</u>		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Spectrum Control:](#)

[C8150173321101B](#)