Features:



- 0201 to 2512 standard terminations and
  0508 to 1225 long side terminations available
- Low resistance, TCR and inductance
- Excellent long-term stability
- High precision current sensing
- "-UP" High power version
- RoHS compliant, REACH compliant, lead free, and halogen free
- AEC-Q200 compliant
- For anti-sulfur version, see CSRT-AS Series – Anti-sulfur Metal Film Low Resistance Chip Resistor

Electrical Specifications

Type/Code	Power Rating (W) @ 70ºC	TCR (ppm/ºC)	Ohmic Range (Ω) and Tolerance	
			0.5%	1% and 5%
CSRT0201	0.2	± 100	0.05 - 0.091	
		± 50	0.1 - 10	
CSRT0402	0.25	± 100	0.05 - 0.091	
		± 50	0.1 - 10	
CSRT0603	0.4	± 100	0.05 - 0.091	
		± 50	0.1 - 10	
CSRT0805	0.5	± 150	0.039 - 0.047	
		± 100	0.05 - 0.091	
		± 50	0.1 - 10	
CSRT1206	0.5	± 200	-	0.01 - 0.036
	1	± 150	0.039 - 0.047	
		± 100	0.05 - 0.091	
		± 50	0.1 - 10	
CSRT1210	1	± 150	0.039 - 0.047	
		± 100	0.05 - 0.091	
		± 50	0.1 - 10	
CSRT2010	1.5	± 50	0.1 - 10	
CSRT2512	3	± 50	0.1 - 10	
CSRT2512-UP	3.5	± 50	0.05 - 50	

V = √(P*R)

Electrical Specifications – Long Side Termination

Type/Code	Power Rating (W) @ 70ºC	TCR (ppm/ºC)	Ohmic Range (Ω) and Tolerance	
			0.5%	1% and 5%
CSRT0508	1	± 100	0.1 - 2	0.01 - 2
CSRT0612	1			
CSRT1020	2			
CSRT1225	3			

V = √(P*R)

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Mechanical Specifications



Type/Code	Weight (mg)	L Body Length	W Body Width	H Body Height	I_1 Top Termination	I_2 Bottom Termination	Unit
CSRT0201	0.18	0.024 ± 0.001 0.60 ± 0.03	0.012 ± 0.001 0.30 ± 0.03	0.010 ± 0.002 0.26 ± 0.05	0.006 ± 0.002 0.15 ± 0.05	0.006 ± 0.002 0.15 ± 0.05	inches mm
CSRT0402	0.58	0.039 ± 0.004 1.00 ± 0.10	0.020 ± 0.002 0.50 ± 0.05	0.014 ± 0.002 0.35 ± 0.05	0.008 ± 0.004 0.20 ± 0.10	0.010 ± 0.004 0.25 ± 0.10	inches mm
CSRT0603	2.1	0.063 ± 0.004 1.60 ± 0.10	0.031 ± 0.004 0.80 ± 0.10	0.018 ± 0.004 0.45 ± 0.10	0.010 ± 0.006 0.25 ± 0.15	0.012 ± 0.006 0.30 ± 0.15	inches mm
CSRT0805	4.9	0.079 ± 0.004 2.00 ± 0.10	0.049 ± 0.004 1.25 ± 0.10	0.022 ± 0.004 0.55 ± 0.10	0.014 ± 0.008 0.35 ± 0.20	0.016 ± 0.008 0.40 ± 0.20	inches mm
CSRT1206 (0.01 Ω - 0.036 Ω)	8.6	0.130 ± 0.008 3.30 ± 0.20	0.067 ± 0.008 1.70 ± 0.20	0.026 ± 0.008 0.65 ± 0.20	0.008 ± 0.006 0.20 ± 0.15	0.027 ± 0.008 0.68 ± 0.20	inches mm
CSRT1206 (0.039 Ω - 10 Ω)		0.122 ± 0.004 3.10 ± 0.10	0.063 ± 0.004 1.60 ± 0.10	0.022 ± 0.004 0.55 ± 0.10	0.016 ± 0.008 0.40 ± 0.20	0.018 ± 0.008 0.45 ± 0.20	inches mm
CSRT1210	14.3	0.122 ± 0.004 3.10 ± 0.10	0.098 ± 0.006 2.50 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.020 ± 0.008 0.50 ± 0.20	0.020 ± 0.008 0.50 ± 0.20	inches mm
CSRT2010	22.4	0.197 ± 0.008 5.00 ± 0.20	0.098 ± 0.006 2.50 ± 0.15	0.022 ± 0.004 0.55 ± 0.10	0.024 ± 0.010 0.60 ± 0.25	0.024 ± 0.010 0.60 ± 0.25	inches mm
CSRT2512	40.9	0.248 ± 0.008 6.30 ± 0.20	0.126 ± 0.008 3.20 ± 0.20	0.028 ± 0.006 0.70 ± 0.15	0.026 ± 0.010 0.65 ± 0.25	0.026 ± 0.010 0.65 ± 0.25	inches mm
CSRT2512 (-UP)	52.3	0.248 ± 0.008 6.30 ± 0.20	0.126 ± 0.008 3.20 ± 0.20	0.028 ± 0.006 0.70 ± 0.15	0.026 ± 0.010 0.65 ± 0.25	0.026 ± 0.010 0.65 ± 0.25	inches mm

Mechanical Specifications – Long Side Termination



Type/Code	Weight (mg)	L Body Length	W Body Width	H Body Height	I_1 Top Termination	I_2 Bottom Termination	Unit
CSRT0508	5.2	0.049 ± 0.004 1.25 ± 0.10	0.079 ± 0.004 2.00 ± 0.10	0.022 ± 0.006 0.55 ± 0.15	0.010 ± 0.006 0.25 ± 0.15	0.014 ± 0.006 0.35 ± 0.15	inches mm
CSRT0612	9.3	0.063 ± 0.006 1.60 ± 0.15	0.126 ± 0.008 3.20 ± 0.20	0.022 ± 0.006 0.55 ± 0.15	0.012 ± 0.008 0.30 ± 0.20	0.020 ± 0.008 0.50 ± 0.20	inches mm
CSRT1020	24.4	0.098 ± 0.006 2.50 ± 0.15	0.197 ± 0.006 5.00 ± 0.15	0.022 ± 0.006 0.55 ± 0.15	0.016 ± 0.008 0.40 ± 0.20	0.020 ± 0.008 0.50 ± 0.20	inches mm
CSRT1225	41.2	0.126 ± 0.008 3.20 ± 0.20	0.248 ± 0.008 6.30 ± 0.20	0.022 ± 0.006 0.55 ± 0.15	0.024 ± 0.010 0.60 ± 0.25	0.031 ± 0.010 0.80 ± 0.25	inches mm

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Performance Characteristics			
Test Item	Test Method	Test Condition	Test Limits
Temperature Coefficient of Resistance (TCR)	JIS C-5201-1 4.8 IEC-60115-1 4.8	TCR +125°C, 25°C is the reference temperature	Refer to Electrical Specifications table
Short Time Overload	JIS C-5201-1 4.13 IEC-60115-1 4.13	Standard Power: 6.25 times rated power whichever is less for 5 seconds High Power and wide terminal type: 5 times rated power whichever is less for 5 seconds	± (1% + 0.001Ω)
Insulation Resistance	JIS C-5201-1 4.8 IEC-60115-1 4.8	100 VDC for 1 minute	≥ 10GΩ
Dielectric Withstanding Voltage	JIS C-5201-1 4.7	0805, 0508, 0612 and above applied 500 VAC, 1 minute 0201, 0402, 0603 applied 300 VAC, 1 minute	No short or burned on the appearance
Core Body Strength	JIS C-5201-1 4.15	Central part pressurizing force: 10 N, 10 seconds	No breakage.
Solderability	JIS C-5201-1 4.17 IEC-60115-1 4.17	245 ± 5°C for 3 ± 0.5 seconds	>95% coverage - no visual damage
Resistance to Soldering Heat	JIS C-5201-1 4.18 IEC-60115-1 4.18	260 ± 5°C for 10 seconds	± (1% + 0.001Ω) No visual damage
Leaching	JIS C5201-1 4.18 IEC-60068-2-58 8.2.1	260 ± 5°C for 30 seconds	>95% coverage - no visual damage
Rapid Change of Temperature	JIS C-5201-1 4.19 IEC-60115-1 4.19	-55 to +155°C, 300 cycles	± (1% + 0.001Ω) No visual damage
Damp Heat with Load	JIS C-5201-1 4.24 IEC-60115-1 4.24	40 ± 2°C, 90 ~ 95% R.H., rated power or max. working current whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hours "OFF"	± (1% + 0.001Ω)
Biased Humidity	MIL-STD-202 Method 103	1000 hours; 85°C/85% RH, 10% of operating power. Measurement at 24 ± 4 hours after test conclusion.	± (0.5% + 0.05Ω)
Load Life (Endurance)	JIS C-5201-1 4.25 IEC-60115-1 4.25.1	70 ± 2°C, rated power or max. working current whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hours "OFF"	± (1% + 0.001Ω)
High Temperature Exposure	JIS C-5201-1 4.25 IEC 60068-2-2	At +155 ± 5°C for 1000 + 48/- 0 hours all sizes, except 2512-UP At +170 ± 5°C for 1000 + 48/- 0 hours for 2512-UP	± (1% + 0.001Ω)
Resistance to Solvent	JIS C-5201-1 clause 4.29	The tested resistor be immersed into isopropyl alcohol of 20 ~ 25°C for 60 seconds. Then the resistor is left in room for 48 hours	± (1% + 0.001Ω) No visual damage
Terminal Strength	JIS C-5201-1 4.32 AEC Q200-006	Pressurizing force for 10 seconds. 0201: 3.4 N; 0402 and 0603: 8 N; 0805, 0612 and above: 17.7 N	No breakage
Bending Strength	JIS C-5201-1 4.33 IEC-60115-1 4.33	Bending once for 5 seconds. D: 0201, 0402, 0603, 0805 = 5 mm 1206, 1210, 0508, 0612 = 3 mm 2010, 2512, 1020, 1225 = 2 mm	± (1% + 0.001Ω) No visual damage

Operating temperature range is -55 to +155°C for all sizes except 2512-UP
Operating temperature range for 2512-UP is -55°C to +170°C

Power Derating Curve:



This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Soldering Profiles

Reflow Soldering Profile



Wave Soldering Profile



Rework temperature (hot air equipment): 350°C, 3 ~ 5 seconds
Recommended reflow methods:
IR, vapor phase oven, hot air oven
If reflow temperatures exceed the recommended profile, devices may not meet the performance requirements.

Recommended Pad Layout



Type/Code	a	b	c	Unit
CSRT0201	0.010 0.25	0.033 0.85	0.014 0.35	inches mm
CSRT0402	0.020 0.50	0.063 1.60	0.028 0.70	inches mm
CSRT0603	0.031 0.80	0.094 2.40	0.039 1.00	inches mm
CSRT0805	0.051 1.30	0.114 2.90	0.057 1.45	inches mm
CSRT1206 (0.01 Ω - 0.036 Ω)	0.047 1.20	0.189 4.80	0.072 1.84	inches mm
CSRT1206 (0.039 Ω - 10 Ω)	0.087 2.20	0.165 4.20	0.071 1.80	inches mm
CSRT1210	0.079 2.00	0.173 4.40	0.106 2.70	inches mm
CSRT2010	0.150 3.80	0.260 6.60	0.106 2.70	inches mm
CSRT2512 (-UP)	0.193 4.90	0.319 8.10	0.134 3.40	inches mm
CSRT0508	0.016 0.40	0.071 1.80	0.079 2.00	inches mm
CSRT0612	0.020 0.50	0.102 2.60	0.126 3.20	inches mm
CSRT1020	0.039 1.00	0.159 4.05	0.217 5.50	inches mm
CSRT1225	0.047 1.20	0.205 5.20	0.276 7.00	inches mm

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Reel Specifications



Type/Code	A	B	C	D	W	M	Unit
CSRT0201	0.079 ± 0.020 2.00 ± 0.50	0.531 ± 0.039 13.50 ± 1.00	0.827 ± 0.039 21.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.453 ± 0.079 11.50 ± 2.00	7.008 ± 0.079 178.00 ± 2.00	inches mm
CSRT0402							
CSRT0603							
CSRT0805							
CSRT1206	0.079 ± 0.020 2.00 ± 0.50	0.531 ± 0.039 13.50 ± 1.00	0.827 ± 0.039 21.00 ± 1.00	2.362 ± 0.039 60.00 ± 1.00	0.453 ± 0.079 11.50 ± 2.00	7.008 ± 0.079 178.00 ± 2.00	inches mm
CSRT1210					0.453 ± 0.079 11.50 ± 2.00		inches mm
CSRT2010					0.630 ± 0.079 16.00 ± 2.00		inches mm
CSRT2512 (-UP)					0.630 ± 0.079 16.00 ± 2.00		inches mm
CSRT0508					0.453 ± 0.079 11.50 ± 2.00		inches mm
CSRT0612					0.453 ± 0.079 11.50 ± 2.00		inches mm
CSRT1020					0.630 ± 0.079 16.00 ± 2.00		inches mm
CSRT1225					0.630 ± 0.079 16.00 ± 2.00		inches mm

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Packaging Specifications - Paper Tape



Type/Code	A	B	W	E	F	Unit
CSRT0201	0.018 ± 0.004 0.45 ± 0.10	0.030 ± 0.004 0.75 ± 0.10	0.315 ± 0.008 8.00 ± 0.20	0.069 ± 0.004 1.75 ± 0.10	0.138 ± 0.002 3.50 ± 0.05	inches mm
CSRT0402	0.028 ± 0.004 0.70 ± 0.10	0.047 ± 0.004 1.20 ± 0.10				inches mm
CSRT0603	0.041 ± 0.008 1.05 ± 0.20	0.071 ± 0.008 1.80 ± 0.20				inches mm
CSRT0805	0.061 ± 0.008 1.55 ± 0.20	0.091 ± 0.008 2.30 ± 0.20				inches mm
CSRT1206	0.075 ± 0.008 1.90 ± 0.20	0.120 ± 0.008 3.05 ± 0.20				inches mm
CSRT1210	0.112 ± 0.008 2.85 ± 0.20	0.120 ± 0.008 3.05 ± 0.20				inches mm
CSRT0508	0.061 ± 0.008 1.55 ± 0.20	0.091 ± 0.008 2.30 ± 0.20				inches mm
CSRT0612	0.075 ± 0.008 1.90 ± 0.20	0.120 ± 0.008 3.05 ± 0.20				inches mm

Type/Code	G	H	T	P	D	Unit
CSRT0201	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.002 2.00 ± 0.05	0.014 ± 0.004 0.35 ± 0.10	0.079 ± 0.004 2.00 ± 0.10	0.059 +0.004/-0 1.50 +0.10/-0	inches mm
CSRT0402			0.018 ± 0.004 0.45 ± 0.10	0.079 ± 0.004 2.00 ± 0.10		inches mm
CSRT0603			0.024 ± 0.004 0.60 ± 0.10	0.157 ± 0.004 4.00 ± 0.10		inches mm
CSRT0805			0.030 ± 0.004 0.75 ± 0.10	0.157 ± 0.004 4.00 ± 0.10		inches mm
CSRT1206			0.030 ± 0.004 0.75 ± 0.10	0.157 ± 0.004 4.00 ± 0.10		inches mm
CSRT1210			0.030 ± 0.004 0.75 ± 0.10	0.157 ± 0.004 4.00 ± 0.10		inches mm
CSRT0508			0.030 ± 0.004 0.75 ± 0.10	0.157 ± 0.004 4.00 ± 0.10		inches mm
CSRT0612			0.030 ± 0.004 0.75 ± 0.10	0.157 ± 0.004 4.00 ± 0.10		inches mm

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Packaging Specifications – Plastic Tape



Type/Code	A	B	W	E	F	G	Unit
CSRT2010	0.110 ± 0.008 2.80 ± 0.20	0.220 ± 0.008 5.60 ± 0.20	0.472 ± 0.004 12.00 ± 0.10	0.069 ± 0.004 1.75 ± 0.10	0.217 ± 0.002 5.50 ± 0.05	0.157 ± 0.004 4.00 ± 0.10	inches mm
CSRT2512 (-UP)	0.134 ± 0.008 3.40 ± 0.20	0.264 ± 0.008 6.70 ± 0.20					inches mm
CSRT1020	0.110 ± 0.008 2.80 ± 0.20	0.220 ± 0.008 5.60 ± 0.20					inches mm
CSRT1225	0.134 ± 0.008 3.40 ± 0.20	0.264 ± 0.008 6.70 ± 0.20					inches mm

Type/Code	H	T	T1	P	D	D1	Unit
CSRT2010	0.079 ± 0.002 2.00 ± 0.05	0.009 ± 0.004 0.23 ± 0.10	0.033 ± 0.006 0.85 ± 0.15	0.157 ± 0.004 4.00 ± 0.10	0.059 +0.004/-0 1.50 +0.10/-0	0.059 ± 0.004 1.50 ± 0.10	inches mm
CSRT2512 (-UP)							
CSRT1020							
CSRT1225							

RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

RoHS Compliance Status

Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition	Lead-Free Mfg. Effective Date (Std Product Series)	Lead-Free Effective Date Code (YY/WW)
CSRT	Thin Film Current Sensing Resistor	SMD	YES	100% Matte Sn over Ni	Always	Always

"Conflict Metals" Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the "conflict region" of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Compliance to “REACH”

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, “The Registration, Evaluation, Authorization and Restriction of Chemicals”, otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

Environmental Policy

It is the policy of Stackpole Electronics, Inc. to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

How to Order

C	S	R	T	2	5	1	2	F	T	1	R	0	0	-	U	P

Product Series

CSRT

Size

Code	W
0201	0.2
0402	0.25
0603	0.4
0805	0.5
1206	0.5
	1
1210	1
2010	1.5
2512	3
2512 (-UP)	3.5
0508	1
0612	1
1020	2
1225	3

Tolerance

Code	Tol	Values*
D	0.5%	E24
F	1%	
J	5%	

(*) E96 values may be available

Packaging

Code	Description	Size	Quantity
T	7" Reel Paper Tape	0201, 0402	10000
		0603, 0805, 1206 1210, 0508, 0612	5000
	7" Reel Plastic Tape	2010, 2512 1020, 1225	4000

Resistance Value

Four characters with the multiplier used as the decimal holder. "L" used as multiplier of 10^{-3} for any value under 0.1 ohm.

0.01 ohm = 10L0
0.068 ohm = 68L0
10 ohm = 10R0

Special

Code	Description
blank	Standard
-UP	High Power

This specification may be changed at any time without prior notice.
Please confirm technical specifications before use.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SEI Stackpole:

CSRT2512FTR250-UP CSRT0402FT50L0 CSRT0402FTR150 CSRT0402FTR750 CSRT0603FT9R10
CSRT0603FTR510 CSRT0805FT5R60 CSRT0805FT68L0 CSRT0805FTR270 CSRT0805FTR300
CSRT1206FT13L0 CSRT1206FT2R00 CSRT1206FTR680 CSRT1210FTR100 CSRT2010FTR100
CSRT2512FT1R10-UP CSRT2512FT56L0-UP CSRT2512FTR220 CSRT2512FTR390-UP CSRT2512FTR470
CSRT0402FT1R80 CSRT0402FT5R10 CSRT0402FTR250 CSRT0402FTR470 CSRT0603FT1R10
CSRT0603FT8R20 CSRT0603FTR180 CSRT0603FTR330 CSRT0805FT39L0 CSRT0805FTR180
CSRT1206FT15L0 CSRT1206FTR250 CSRT1210FT6R80 CSRT1210FTR120 CSRT2512FT2R40
CSRT2512FTR620-UP CSRT0402FT75L0 CSRT0402FTR300 CSRT0603FT1R20 CSRT0603FT1R50
CSRT0603FT5R10 CSRT0603FTR270 CSRT0805FT10R0 CSRT0805FTR150 CSRT1206FT1R50
CSRT1210FT1R80 CSRT1210FT2R20 CSRT1210FT50L0 CSRT1210FT68L0 CSRT1210FTR820
CSRT2010FT10R0 CSRT2010FT3R90 CSRT2010FT4R70 CSRT2010FTR200 CSRT2010FTR240
CSRT2512FT3R90-UP CSRT2512FT4R30-UP CSRT2512FTR270-UP CSRT0402FT1R10 CSRT0402FTR200
CSRT0603FT3R00 CSRT0603FT3R30 CSRT0603FTR110 CSRT0603FTR120 CSRT0805FT6R80
CSRT0805FTR330 CSRT1206FT5R10 CSRT1210FT3R00 CSRT1210FT3R90 CSRT1210FTR470
CSRT2010FT7R50 CSRT2512FT1R10 CSRT2512FT1R30 CSRT2512FT82L0-UP CSRT2512FT91L0-UP
CSRT2512FTR430-UP CSRT2512FTR910 CSRT0402FT1R20 CSRT0402FTR270 CSRT0603FT2R50
CSRT0603FT3R90 CSRT0603FTR360 CSRT0805FT7R50 CSRT0805FTR750 CSRT0805FTR910
CSRT1206FT43L0 CSRT1206FT6R20 CSRT1210FT75L0 CSRT2010FT1R20 CSRT2010FT1R50
CSRT2010FT3R00 CSRT2010FTR300 CSRT2512FT2R20-UP CSRT2512FT3R60 CSRT2512FTR360
CSRT2512FTR470-UP CSRT0402FT1R00 CSRT0603FT2R70 CSRT0603FT3R60 CSRT0603FTR100