

RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

Features:

- RMCF – standard power ratings
- RMCP – high power ratings
- Nickel barrier terminations standard
- Power derating from 100% at 70°C to zero at +155°C
- RoHS compliant, REACH compliant, and halogen free
- AEC-Q200 compliant (except 01005 and 0201 sizes)
- For ultra-high power, see [RMCP-UP Series – Thick Film Ultra High-Power Chip Resistor](#)



Electrical Specifications - RMCF

Type/Code	Power Rating (W) @ 70°C	Max. Working Voltage (V) ⁽¹⁾	Max. Overload Voltage (V)	Jumper Rated Current (A)	TCR (ppm/°C)	Ohmic Range (Ω) and Tolerance ⁽²⁾	
						1%	5%
RMCF01005	0.03	15	30	0.5	± 300	10 - 97.6	
					± 200	100 - 1M	
RMCF0201	0.05	25	50	0.5	± 400	1 - 9.76	
					± 200	10 - 10M	
RMCF0402	0.063	50	100	1	± 200	1 - 9.76	
					± 100	10 - 1M	
					± 200	1.02M - 22.1M	1.1M - 22M
RMCF0603	0.1	75	150	1	± 500	0.1 - 0.499	
					± 400	0.5 - 0.976	
					± 200	1 - 9.76	1 - 22M
					± 100	10 - 1M	-
					± 200	1.02M - 22.1M	-
RMCF0805	0.125	150	300	2	± 200	0.1 - 9.76	0.1 - 22M
					± 100	10 - 1M	-
					± 200	1.02M - 22.1M	-
RMCF1206	0.25	200	400	2	± 200	0.1 - 9.76	0.1 - 22M
					± 100	10 - 1M	-
					± 200	1.02M - 22.1M	-
RMCF1210	0.5	200	400	3	± 200	0.1 - 0.976	
					± 400	1 - 9.76	
					± 100	10 - 10M	
RMCF2010	0.75	200	400	3	± 200	0.1 - 0.976	
					± 400	1 - 9.76	
					± 200	-	10 - 10M
					± 100	10 - 10M	-
RMCF2512	1	200	400	3	± 200	0.1 - 0.976	
					± 400	1 - 9.76	
					± 200	-	10 - 10M
					± 100	10 - 10M	-

Notes: (1) Lesser of $\sqrt{P \cdot R}$ or maximum working voltage

(2) Contact Stackpole for higher or lower values

RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

Electrical Specifications - RMCP

Type/Code	Power Rating (W) @ 70°C	Max. Working Voltage (V) ⁽¹⁾	Max. Overload Voltage (V)	Jumper Rated Current (A)	TCR (ppm/°C)	Ohmic Range (Ω) and Tolerance ⁽²⁾
						1%, 5%
RMCP0201	0.063	25	50	1	-200 / +400 ± 200	1 - 9.76 10 - 10M
RMCP0402	0.125	50	100	1.5	± 200 ± 100	1 - 9.76 10 - 10M
RMCP0603	0.25	75	150	2	± 200 ± 100	1 - 9.76 10 - 10M
RMCP0805	0.33	150	300	2.5	± 200 ± 100	1 - 9.76 10 - 10M
RMCP1206	0.5	200	400	3.5	± 400 ± 100	1 - 9.76 10 - 10M
RMCP1210	0.66	200	400	5	± 400 ± 100	1 - 9.76 10 - 10M
RMCP2010	1	200	400	6	± 200 ± 100	1 - 9.76 10 - 10M
RMCP2512	2	250	500	7	± 200 ± 100	1 - 9.76 10 - 10M

Notes: (1) Lesser of $\sqrt{P \cdot R}$ or maximum working voltage

(2) Contact Stackpole for higher or lower values


The resistance value range for RMCP jumper is max. 0.02Ω

Electrical Specifications - Jumper

Type/Code	Jumper Rated Current (A)	Max Overload Current (A)*	Jumper Resistance Value (Ω)
RMCF01005	0.5	1	0.05 max.
RMCF0201	0.5	1	
RMCF0402	1	3	
RMCF0603	1	5	
RMCF0805	2	10	
RMCF1206	2	10	
RMCF1210	3	12	
RMCF2010	3	12	
RMCF2512	3	15	

* < 1 second and 1 time

Mechanical Specifications



Type/Code	Typical Unit Weight (mg)	L Body Length	W Body Width	H Body Height	a Top Termination	b Bottom Termination	Unit
RMCF01005	0.07	0.016 ± 0.001 0.40 ± 0.02	0.008 ± 0.001 0.20 ± 0.02	0.005 ± 0.001 0.13 ± 0.02	0.004 ± 0.001 0.10 ± 0.03	0.004 ± 0.001 0.10 ± 0.03	inches mm
RMCF0201 RMCP0201	0.16	0.024 ± 0.001 0.60 ± 0.03	0.012 ± 0.001 0.30 ± 0.03	0.009 ± 0.002 0.23 ± 0.05	0.006 ± 0.002 0.15 ± 0.05	0.006 ± 0.002 0.15 ± 0.05	inches mm
RMCF0402 RMCP0402	0.57 0.62	0.039 ± 0.004 1.00 ± 0.10	0.020 ± 0.002 0.50 ± 0.05	0.012 ± 0.004 0.30 ± 0.10	0.006 ± 0.004 0.15 ± 0.10	0.010 ± 0.006 0.25 ± 0.15	inches mm
RMCF0603 RMCP0603	1.9 2.0	0.061 ± 0.006 1.55 ± 0.15	0.031 ± 0.006 0.80 ± 0.15	0.018 ± 0.006 0.45 ± 0.15	0.012 ± 0.008 0.30 ± 0.20	0.012 ± 0.008 0.30 ± 0.20	inches mm
RMCF0805 RMCP0805	5.0 4.4	0.079 ± 0.008 2.00 ± 0.20	0.049 ± 0.004 1.25 ± 0.10	0.020 ± 0.006 0.50 ± 0.15	0.014 ± 0.010 0.35 ± 0.25	0.014 ± 0.010 0.35 ± 0.25	inches mm

RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

Mechanical Specifications (cont.)

Type/Code	Typical Unit Weight (mg)	L Body Length	W Body Width	H Body Height	a Top Termination	b Bottom Termination	Unit
RMCF1206 RMCP1206	8.9	0.126 ± 0.010 3.20 ± 0.25	0.063 ± 0.006 1.60 ± 0.15	0.022 ± 0.006 0.55 ± 0.15	0.020 ± 0.012 0.50 ± 0.30	0.020 ± 0.012 0.50 ± 0.30	inches mm
RMCF1210 RMCP1210	15.6 16.0	0.126 ± 0.010 3.20 ± 0.25	0.098 ± 0.010 2.50 ± 0.25	0.022 ± 0.006 0.55 ± 0.15	0.020 ± 0.012 0.50 ± 0.30	0.020 ± 0.012 0.50 ± 0.30	inches mm
RMCF2010 RMCP2010	23.6 24.2	0.197 ± 0.008 5.00 ± 0.20	0.098 ± 0.008 2.50 ± 0.20	0.022 ± 0.006 0.55 ± 0.15	0.024 ± 0.012 0.60 ± 0.30	0.024 ± 0.014 0.60 ± 0.35	inches mm
RMCF2512 RMCP2512	40.0 39.4	0.248 ± 0.008 6.30 ± 0.20	0.126 ± 0.010 3.20 ± 0.25	0.022 ± 0.008 0.55 ± 0.20	0.024 ± 0.012 0.60 ± 0.30	0.024 ± 0.014 0.60 ± 0.35	inches mm


Performance Characteristics

Test	Test Specifications	Test Conditions (JIS-C 5202)
Short Time Overload	± (2% + 0.1Ω)	2.5 x rated voltage for 5 seconds
	Jumper: Max 0.05Ω after test	0201 = 1 A 0402 / 0603 = 2.5 A 0805 / 1206 / 1210 / 2010 / 2512 = 5 A
Dielectric Withstanding Voltage	No flashover or breakdown	100 VAC, 1 minute
Resistance to Soldering Heat	± 1%	260 ± 5°C, for 10 seconds ± 0.5 seconds (Solder Bath)
Solderability	95% coverage, minimum	235 ± 5°C, for 2 seconds ± 0.5 seconds (Colophonium flux)
Temperature Cycle	± (1% + 0.05Ω) Jumper (< 0.05Ω)	-65°C: 30 minutes 25°C: 2 to 3 minutes 155°C: 30 minutes 25°C: 2 to 3 minutes (5 Cycles)
Load Life (Endurance)	1% and below: ± (1% + 0.05Ω) 2% and 5%: ± (3% + 0.1Ω) Value < 1Ω: ± (3% + 0.1Ω) Jumper: Max 0.1Ω after test.	70 ± 2°C, RCWV or max. working voltage whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hour "OFF"
Voltage Coefficient	± 100 (ppm/V)	1/10 rated voltage for 3 seconds max. then rated voltage for 3 seconds max.
Robustness of Termination	± (1% + 0.05Ω)	Bend of 2 mm for 5 ± 1 seconds
Resistance to Solvent	1%: ± (0.5% + 0.05Ω) 5%: ± (0.5% + 0.05Ω) Jumper: Max. 0.05Ω after test	The tested resistor should be immersed into isopropyl alcohol of 20 to 25°C for 60 seconds. Then the resistor is left in the room for 48 hours.
Damp Heat with Load	1%: ± (1% + 0.05Ω) 5%: ± (2% + 0.05Ω) Values < 1Ω: ± (3% + 0.1Ω) Jumper: Max. 0.1Ω after test	40 ± 2°C, 90%~95% R.H. RCWV or max. working voltage whichever is less for 1000 hours with 1.5 hours "ON" and 0.5 hours "OFF"

Operating temperature range is -55 to +155°C for all sizes except for 01005 size

Operating temperature range for 01005 is -55 to +125°C

Power Derating Curve:



Repetitive Pulse Information

(This information is for reference only and is not guaranteed performance.)


If repetitive pulses are applied to resistors, pulse wave form must be less than “Pulse Limiting Voltage”, “Pulse Limiting Current” or “Pulse Limiting Wattage” calculated by the formula below.

$$V_p = K\sqrt{P \times R \times T/t}$$

$$I_p = K\sqrt{P/R \times T/t}$$

$$P_p = K^2 \times P \times T/t$$

Where: V_p : Pulse limiting voltage (V)
 I_p : Pulse limiting current (A)
 P_p : Pulse limiting wattage (W)
 P : Power rating (W)
 R : Nominal resistance (ohm)
 T : Repetitive period (sec)
 t : Pulse duration (sec)
 K : Coefficient by resistors type (refer to below matrix)
[V_r : Rated Voltage (V), I_r : Rated Current (A)]



Note 1: If $T > 10 \rightarrow T = 10$ (sec), $T/t > 1000 \rightarrow T/t = 1000$

Note 2: If $T > 10$ and $T/t > 1000$, “Pulse Limiting power (Single pulse) is applied

Note 3: If $V_p < V_r$ ($I_p < I_r$ or $P_p < P$), V_r (I_r , P) is V_p (I_p , P_p)

Note 4: Pulse limiting voltage (current, wattage) is applied at less than rated ambient temperature. If ambient temperature is more than the rated temperature (70°C), please decrease power rating according to “Power Derating Curve”

Note 5: Please assure sufficient margin for use period and conditions for “Pulse Limiting Voltage”


Note 6: If the pulse waveform is not square wave, please judge after transform the waveform into square wave according to the “Waveform Transformation to Square Wave”.

RMCF Coefficient (K) Matrix


Ohmic Value	K
$R < 10\Omega$	0.50
$10\Omega \leq R < 100\Omega$	0.45
$100\Omega \leq R < 1K\Omega$	0.35
$1K\Omega \leq R < 10K\Omega$	0.25
$10K\Omega \leq R$	0.20

Waveform Transformation to Square Wave


1. Discharge curve wave with time constant " t " → Square wave




2. Damping oscillation wave with time constant of envelope " t " → Square wave




3. Half-wave rectification wave → Square wave



4. Triangular wave → Square wave



5. Special wave → Square wave




RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

Recommended Pad Layout



Type/Code	A	B	C	Unit
RMCF01005	0.008 0.20	0.020 0.50	0.008 0.20	inches mm
RMCF0201 RMCP0201	0.012 0.30	0.039 1.00	0.016 0.40	inches mm
RMCF0402 RMCP0402	0.020 0.50	0.059 1.50	0.024 0.60	inches mm
RMCF0603 RMCP0603	0.031 0.80	0.083 2.10	0.035 0.90	inches mm
RMCF0805 RMCP0805	0.047 1.20	0.118 3.00	0.051 1.30	inches mm
RMCF1206 RMCP1206	0.087 2.20	0.165 4.20	0.063 1.60	inches mm
RMCF1210 RMCP1210	0.087 2.20	0.165 4.20	0.110 2.80	inches mm
RMCF2010 RMCP2010	0.138 3.50	0.240 6.10	0.110 2.80	inches mm
RMCF2512 RMCP2512	0.193 4.90	0.315 8.00	0.138 3.50	inches mm

Recommended Solder Profile

This information is intended as a reference for solder profiles for Stackpole resistive components. These profiles should be compatible with most soldering processes. These are only recommendations. Actual numbers will depend on board density, geometry, packages used, etc., especially those cells labeled with “**”.

100% Matte Tin / RoHS Compliant Terminations

Soldering iron recommended temperatures: 330°C to 350°C with minimum duration.
Maximum number of reflow cycles is 3.

Wave Soldering

Description	Maximum	Recommended	Minimum
Preheat Time	80 seconds	70 seconds	60 seconds
Temperature Diff.	140°C	120°C	100°C
Solder Temp.	260°C	250°C	240°C
Dwell Time at Max	10 seconds	5 seconds	*
Ramp DN (°C/sec)	N/A	N/A	N/A

Temperature Diff. = Difference between final preheat stage and soldering stage.

RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor


Stackpole Electronics, Inc.

Resistive Product Solutions

Convection IR Reflow


Description	Maximum	Recommended	Minimum
Ramp Up (°C/sec)	3°C/sec	2°C/sec	*
Dwell Time > 217°C	150 seconds	90 seconds	60 seconds
Solder Temp.	260°C	245°C	*
Dwell Time at Max.	30 seconds	15 seconds	10 seconds
Ramp DN (°C/sec)	6°C/sec	3°C/sec	*

Recommended Resistor Reflow Profile



Packaging (EIA Standard RS-481)

Reel Specifications



Reel Type	Wa	M	A	B	C	D	Unit
7" reel for 8 mm tape	0.354 ± 0.020	7.008 ± 0.079	0.079 ± 0.020	0.531 ± 0.020	0.827 ± 0.020	2.362 ± 0.039	inches
	9.00 ± 0.50	178.00 ± 2.00				60.00 ± 1.00	mm
10" reel for 8 mm tape	0.394 ± 0.020	10.000 ± 0.079	2.00 ± 0.50	13.50 ± 0.50	21.00 ± 0.50	3.937 ± 0.039	inches
	10.00 ± 0.50	254.00 ± 2.00				100.00 ± 1.00	mm


RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

Packaging Specifications – Paper Tape (sizes 01005 - 1210)



Type/Code	Nominal Typical Full Reel Weight (g)	Tape Width	A	B	W	E	Unit
RMCF01005	127.3	0.315 8.00	0.009 ± 0.002 0.24 ± 0.05	0.018 ± 0.004 0.45 ± 0.10	0.315 ± 0.008 8.00 ± 0.20	0.069 ± 0.004 1.75 ± 0.10	inches
RMCF0201 RMCP0201	97.2		0.016 ± 0.006 0.40 ± 0.15	0.028 ± 0.006 0.70 ± 0.15			mm
RMCF0402 RMCP0402	94.5		0.028 ± 0.006 0.70 ± 0.15	0.047 ± 0.006 1.20 ± 0.15			inches
RMCF0603 RMCP0603	118.3		0.041 ± 0.008 1.05 ± 0.20	0.071 ± 0.008 1.80 ± 0.20			mm
RMCF0805 RMCP0805	139.2		0.063 ± 0.010 1.60 ± 0.25	0.093 ± 0.010 2.35 ± 0.25			inches
RMCF1206 RMCP1206	151.4		0.077 ± 0.010 1.95 ± 0.25	0.140 ± 0.010 3.55 ± 0.25			mm
RMCF1210 RMCP1210	175.7		0.110 ± 0.010 2.80 ± 0.25	0.138 ± 0.008 3.50 ± 0.20			inches
RMCF1210 RMCP1210							mm
Type/Code	F	T	P	P0	P1	DØ	Unit
RMCF01005	0.138 ± 0.002 3.50 ± 0.05	0.016 ± 0.004 0.40 ± 0.10	0.079 ± 0.004 2.00 ± 0.10	0.157 ± 0.004 4.00 ± 0.10	0.079 ± 0.004 2.00 ± 0.10	0.059 ± 0.004/-0 1.50 ± 0.10/-0	inches
RMCF0201 RMCP0201		0.015 ± 0.006 0.38 ± 0.15					mm
RMCF0402 RMCP0402		0.016 ± 0.008 0.40 ± 0.20					inches
RMCF0603 RMCP0603		0.024 ± 0.004 0.60 ± 0.10					mm
RMCF0805 RMCP0805		0.030 ± 0.004 0.75 ± 0.10	0.157 ± 0.004 4.00 ± 0.10				inches
RMCF1206 RMCP1206							mm
RMCF1210 RMCP1210							inches
RMCF1210 RMCP1210							mm


RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.


Resistive Product Solutions

Packaging Specifications – Plastic Tape (sizes 2010 and 2512)



Type/Code	Nominal Typical Full Reel Weight (g)	Tape Width	A	B	W	E	F	Unit
RMCF2010 RMCP2010	183.1	0.472	0.110 ± 0.008 2.80 ± 0.20	0.217 ± 0.012 5.50 ± 0.30	0.472 ± 0.008	0.069 ± 0.004	0.217 ± 0.002	inches mm
RMCF2512 RMCP2512	255.3	12.00	0.134 ± 0.008 3.40 ± 0.20	0.264 ± 0.008 6.70 ± 0.20	12.00 ± 0.20	1.75 ± 0.10	5.50 ± 0.05	inches mm
Type/Code	G	H	T	ØD	ØD1	T1	P	Unit
RMCF2010 RMCP2010	0.157 ± 0.004	0.079 ± 0.002	0.009 ± 0.004	0.059 +0.004/-0	0.059 ± 0.004	0.035 ± 0.008	0.157 ± 0.004	inches
RMCF2512 RMCP2512	4.00 ± 0.10	2.00 ± 0.05	0.23 ± 0.10	1.50 +0.10/-0	1.50 ± 0.10	0.90 ± 0.20	4.00 ± 0.10	mm

Single Pulse Power



The data provided are for reference only. They are typical performance for this product but are not guaranteed. The actual pulse handling of each individual resistor may vary depending on a variety of factors including resistance tolerance and resistance value. Stackpole Electronics, Inc. assumes no liability for the use of this information. Customers should validate the performance of these products in their applications. Contact Stackpole marketing to discuss specific pulse application requirements.

Temperature Measurement of Resistor Surface

Description: The resistor surface generated temperature variation after applied rated voltage.

Products and power:

Size	0201	0402	0603	0805	1206	1210	2010	2512
R-V	15K	40.2K	57.6K	180K	182K	100K	100K	75K
Rated Power (W)	1/20	1/16	1/10	1/8	1/4	1/2	3/4	1
Max Rated Voltage (V)	25	50	75	150	200	200	200	200

Test method: Measure component surface temperature directly after the temperature stabilizes.

Test result: As per table below:


RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

Hot Spot Temperature - RMCF



Size	0201	0402	0603	0805	1206	1210	2010	2512
Surface Temp. (°C)	36	37	46.2	50.4	70.6	110.6	141	150.4


The thermal resistance of the RMCP will be similar to the RMCF. For example, the RMCF2512 and the RMCP2512 will have similar surface temperatures at 1W; the RMCP is designed to withstand higher temperatures associated with high power levels.

Part Marking Instructions


E96 and E24 Values for 0805-2512 (1% tolerances)

The nominal resistance is marked on the surface of the overcoating with the use of **four character markings**.

- Values <100Ω will use "R" as the decimal holder.



1.21Ω




100Ω

E24 Values for 0805-2512 (5% tolerance, ≤ 0.91Ω)

The nominal resistance is marked on the surface of the overcoating with the use of **four character markings**.

- Values ≤ 0.91Ω will use "R" as the decimal holder.




0.68Ω


E24 Values for 0805-2512 (5% tolerance, ≥ 1Ω)

The nominal resistance is marked on the surface of the overcoating with the use of **three character markings**.

- Values between 1Ω and 9.1Ω will use "R" as the decimal holder.



1Ω



1.2 KΩ


E24 Values for 0603

The nominal resistance is marked on the surface of the overcoating with the use of **three character markings**.


- Values between 0.1Ω and 9.1Ω will use "R" as the decimal holder.
- Values ≥10Ω will use no decimal holder.
- 5% tolerance is not underlined. 1% tolerance is underlined.



0.68Ω 5%



10Ω 5%




220Ω 1%

(Effective date for 1% underline marking is date codes on/or after April 1st 2025)

- Values that are both E24 and E96 follow E96 marking rules.

E96 Values for 0603 size (1% tolerances)

A two character number is assigned to each standard R-Value (E96) as shown in the chart below. This is followed by one alpha character which is used as a multiplier. Each letter from "Y" - "F" represents a specific multiplier.



10.5Ω

Alpha Character = Multiplier	
Y = 0.1	C = 1000
X = 1	D = 10000
A = 10	E = 100000
B = 100	F = 1000000

Chip Marking	Value
01B =	10.0 x 100 = 1 KΩ
25C =	17.8 x 1000 = 17.8 KΩ
93D =	90.9 x 10000 = 909 KΩ

E96											
#	R-Value	#	R-Value	#	R-Value	#	R-Value	#	R-Value	#	R-Value
01	10.0	17	14.7	33	21.5	49	31.6	65	46.4	81	68.1
02	10.2	18	15.0	34	22.1	50	32.4	66	47.5	82	69.8
03	10.5	19	15.4	35	22.6	51	33.2	67	48.7	83	71.5
04	10.7	20	15.8	36	23.2	52	34.0	68	49.9	84	73.2
05	11.0	21	16.2	37	23.7	53	34.8	69	51.1	85	75.0
06	11.3	22	16.5	38	24.3	54	35.7	70	52.3	86	76.8
07	11.5	23	16.9	39	24.9	55	36.5	71	53.6	87	78.7
08	11.8	24	17.4	40	25.5	56	37.4	72	54.9	88	80.6
09	12.1	25	17.8	41	26.1	57	38.3	73	56.2	89	82.5
10	12.4	26	18.2	42	26.7	58	39.2	74	57.6	90	84.5
11	12.7	27	18.7	43	27.4	59	40.2	75	59.0	91	86.6
12	13.0	28	19.1	44	28.0	60	41.2	76	60.4	92	88.7
13	13.3	29	19.6	45	28.7	61	42.2	77	61.9	93	90.9
14	13.7	30	20.0	46	29.4	62	43.2	78	63.4	94	93.1
15	14.0	31	20.5	47	30.1	63	44.2	79	64.9	95	95.3
16	14.3	32	21.0	48	30.9	64	45.3	80	66.5	96	97.6

Note: 01005, 0201, and 0402 sizes are unmarked.

RoHS Compliance

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

RoHS Compliance Status						
Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition	Lead-Free Mfg. Effective Date (Std Product Series)	Lead-Free Effective Date Code (YY/WW)
RMCF	General Purpose Thick Film Standard Power Chip Resistor	SMD	YES ⁽¹⁾	100% Matte Sn over Ni	Jan-04 (Japan) Jan-05 (Taiwan, China)	04/01 05/01
RMCP	General Purpose Thick Film High-Power Chip Resistor	SMD	YES ⁽¹⁾	100% Matte Sn over Ni	Always	Always

Note (1): RoHS Compliant by means of exemption 7c-I.

"Conflict Metals" Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the "conflict region" of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

Compliance to "REACH"

We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, "The Registration, Evaluation, Authorization and Restriction of Chemicals", otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

Environmental Policy

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.

RMCF / RMCP Series

General Purpose Thick Film Standard Power
and High-Power Chip Resistor

Stackpole Electronics, Inc.

Resistive Product Solutions

How to Order - RMCF

R	M	C	F	0	6	0	3	J	T	4	K	7	0							
Product Series		Size		Tolerance			Packaging				Resistance Value									
Code		Size	W	Code	Tol	Value	Code	Description	Size	Quantity	Four characters with the multiplier used as the decimal holder. 0.1 ohm = R100 4.70 ohm = 4R70 10.0 Kohm = 10K0 1 Mohm = 1M00 Zero ohm jumper = 0R00									
RMCF		01005	0.03	F	1%	E96, E24	T	7" Reel Paper Tape	01005	10000										
		0201	0.05	J	5%	E24			0201, 0402	10000										
		0402	0.063	Z Jumper					0603, 0805, 1206	5000										
		0603	0.1						1210	4000										
		0805	0.125				G	10" Reel Paper Tape	2010, 2512											
		1206	0.25																	
		1210	0.5																	
		2010	0.75																	
		2512	1																	

How to Order - RMCP

R	M	C	P	0	6	0	3	J	T	4	K	7	0					
Product Series		Size		Tolerance			Packaging				Resistance Value							
Code		Size	W	Code	Tol	Value	Code	Description	Size	Quantity	Four characters with the multiplier used as the decimal holder. 1 ohm = 1R00 10 Kohm = 10K0 1 Mohm = 1M00							
RMCP		0201	0.063	F	1%	E96, E24	T	7" Reel Paper Tape	0201, 0402	10000								
		0402	0.125	J	5%	E24			0603, 0805	5000								
		0603	0.25	Z		Jumper			1206, 1210	5000								
		0805	0.33	G	10" Reel Paper Tape	2010, 2512	4000											
		1206	0.5											0603, 0805	10000			
		1210	0.66											1206	10000			
		2010	1															
		2512	2															

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

SEI Stackpole:

RMCF0805JT1R00	RMCF0805FT2K70	RMCF0805FT49R9	RMCF0805JT51K0	RMCF0603JT10R0
RMCF0603JT120R	RMCF0603FT150K	RMCF1206FT100R	RMCF1206FT2K87	RMCF0805ZT0R00
RMCF0402FT270R	RMCF0805FT121K	RMCF0805FT301K	RMCF0603FT105K	RMCF0603FT33R0
RMCF0603FT4K02	RMCF0603FT470K	RMCF0603FT511R	RMCF0603FT562R	RMCF0603FT7K50
RMCF0603FT806R	RMCF0402FT1K15	RMCF0402FT41K2	RMCF0402FT560R	RMCF1206JT120R
RMCF1206JT820R	RMCF2512JT2R00	RMCF2512JT33R0	RMCF0603FT1R50	RMCF0402FT47R0
RMCF0402FT240R	RMCF0603FT590K	RMCF0603FT178R	RMCF1206FT1K43	RMCF1210FT249K
RMCF1206FT4K87	RMCF0805JT240K	RMCF1206FT2K05	RMCF0603FT9K53	RMCF1206FT10K5
RMCF0603FT953K	RMCF0603FT909K	RMCF1206FT191K	RMCF1206JT200K	RMCF1206JT3K90
RMCF2010JT68K0	RMCF0805FT150R	RMCF0805JT22K0	RMCF0603FT15K0	RMCF0603FT220R
RMCF0603FT249R	RMCF0603FT39K2	RMCF0603FT4R99	RMCF0603JT470R	RMCF1206FT10R0
RMCF0805FT1K80	RMCF0805FT14K0	RMCF0805JT2K40	RMCF0805JT3K00	RMCF0805FT56K2
RMCF0805JT75R0	RMCF0603FT10K7	RMCF0603FT110R	RMCF0603FT18K0	RMCF0603FT33K0
RMCF0603FT51R0	RMCF0603JT51R0	RMCF0603FT6K19	RMCF0603JT820R	RMCF0402FT1K40
RMCF0402JT10M0	RMCF0402FT150R	RMCF0402FT17K8	RMCF0402FT22K1	RMCF0402FT30K9
RMCF0402FT37K4	RMCF0402FT44K2	RMCF0402FT8K25	RMCF1210JT1K00	RMCF0805JT180R
RMCF0603FT619K	RMCF0603FT681K	RMCF0603FT1M02	RMCF0603FT14K7	RMCF2010JT470R
RMCF1206FT22K1	RMCF2010JT330R	RMCF1206FT3K57	RMCF1206FT130K	RMCF1206FT1K15
RMCF1206FT45K3	RMCF0603FT127R	RMCF0603FT768K	RMCF1206FT178K	RMCF1206FT237R
RMCF0805FT7K68	RMCF1206FT13K0	RMCF1206JT12M0	RMCF1206JT62K0	RMCF2512FT2K00