





DWG. SIZE	DWG. NO.		
D	031-3651		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	23902	12/16/98	REDRAWN ON CAD
B	25804	10/16/06	
	UPDATED PER SCREEN 639-0243		
C	28069	12/5/14	UPDATED PER SCREEN 639-0243




NOTE:  
UNIT IS SUPPLIED WITH A 3.75 [95.2] DIA.  
0-100 GRADUATED DIAL PLATE FOR PANEL  
MOUNTING.



COIL SCHEMATIC  
AS VIEWED FROM BASE END  
FUSE RECOMMENDED BUT  
NOT SUPPLIED



SPECIFICATIONS												
WIRING	INPUT		OUTPUT				SHAFT ROTATION TO INCREASE VOLTAGE	TERMINAL CONNECTIONS				
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD		FOR INCREASING VOLTAGE AS VIEWED FROM BASE END				
				MAX. AMPS	MAX. KVA	MAX. AMPS		MAX. KVA	INPUT	JUMPER	OUTPUT	
SINGLE PHASE	120	50/60	0-120	15	1.80	20	2.40	CW	2-4	——	4-3	
									CCW	2-4	——	2-3
									CW	1-4	——	4-3
			0-140	15	2.10	——	——	CCW	5-2	——	2-3	
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ± DECIMALS      HOLES      ANGLES      DRAFT .XX .005      .005 .01      1°      1-1/2°			UNITS IN [mm]		TITLE: SPEC. CONTROL DRAWING VARIABLE TRANSFORMER MODEL: 1510CT					 A Components Corporation of America Company 301 Gastle Boulevard Dayton, Ohio 45403 USA		
MATERIAL:		ALL DIMENSIONS APPLY AFTER PLATING										
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sole rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.				DRAWN BY S.A. SMITH		DATE 11/15/96		FIRST USED ON 1510CT		DO NOT SCALE DWG.		
				CHECKER		DATE		WEIGHT APPROX. 16 LBS		CAGE CODE 83008		
				ENGINEER		DATE		SCALE 1=1		SHEET 1 of 1		
										DWG. NO. 031-3651		



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

1510CT