



+ MOTOR DRIVEN UNITS USE TERMINAL CONNECTIONS FOR CCW INCREASING VOLTAGE, AS VIEWED FROM BASE END.

SPEED (SECONDS)	MODEL NUMBER
5	5M1010BCT
15	15M1010BCT
30	30M1010BCT
60	60M1010BCT

SPECIFICATIONS																		
WIRING	INPUT		OUTPUT				SHAFT ROTATION TO INCREASE VOLTAGE	TERMINAL CONNECTIONS										
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD		FOR INCREASING VOLTAGE AS VIEWED FROM BASE END +										
				MAX. AMPS	MAX. KVA	MAX. AMPS		MAX. KVA	INPUT	JUMPER	OUTPUT							
SINGLE PHASE	120	50/60	0-120	10	1.2	13	1.56	CW	1-4	—	4-3							
			0-140	10	1.4	—	—	CCW	1-4	—	1-3							
								CW	4-5	—	4-3							
								CCW	2-1	—	1-3							
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±			UNITS			SPEC. CONTROL DRAWING MOTORIZED VARIABLE XFMR. MODEL: M1010BCT												
DECIMALS			IN [mm]															
Holes .002			ANGLES 1°															
DRAFT 1-1/2°			DIMENSIONS APPLY AFTER PLATING			STACO ENERGY PRODUCTS CO. A CORPORATION OF AMERICA COMPANY DAYTON, OHIO U.S.A.												
MATERIAL:						DRAWN BY S.A. SMITH			DATE 9/22/97		FIRST USED ON		DO NOT SCALE DWG.		CUSTOMER APPROVAL		DATE	
						CHECKER			DATE		WEIGHT APPROX. 16.75 LBS		CODE IDENT. NO. 83008		DWG. SIZE		DWG. NO.	
						ENGINEER			DATE		SCALE 1=1		SHEET 1 OF 1		D		031-1810	
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.																		



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

M1010BCT