


NOTE:
FUSE RECOMMENDED BUT NOT SUPPLIED



MOTOR CIRCUIT


120V, 50/60 HZ

* ROTATION AS VIEWED FROM MOTOR END

MOTOR SPEED: SEE CHART

- ⚡ IF GANGED UNITS ARE USED IN A SYSTEM THAT ORDINARILY HAS A COMMON NEUTRAL OR GROUND BETWEEN SOURCE AND LOAD, THE NEUTRAL OR GROUND MUST BE CONNECTED TO THE COMMON TERMINALS OF THE VARIABLE TRANSFORMER ASSEMBLY. IF THE SYSTEM HAS NO NEUTRAL, THE LOAD MUST BE BALANCED OR THE TRANSFORMERS WILL BE DAMAGED.
- JUMPER PROVIDED IN THE STANDARD COMMON POSITION AND SHOULD BE MOVED OR REMOVED AS REQUIRED.

++ LINE TO LINE VOLTAGE

MODEL NO.		SPEED (SECONDS)		DIM. "A"		UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ± DECIMALS XX .000 .06 .002 .005		ANGLES 1° 1-1/2°		UNITS IN [mm]		TITLE: SPEC. CONTROL DRAWING MOTORIZED VARIABLE XFMR. TYPE: M1510-3				 STACO ENERGY PRODUCTS CO. A COMPONENTS CORPORATION OF AMERICA COMPANY DAYTON, OHIO U.S.A.	
5M1510-3		5		20.38 [517.6]		MATERIAL:				ALL DIMENSIONS APPLY AFTER PLATING							
15M1510-3		15		20.38 [517.6]		The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.		DRAWN BY TIM RAU		DATE 11/23/98		FIRST USED ON DO NOT SCALE DWG.		CUSTOMER APPROVAL DATE			
30M1510-3		30		20.75 [527.1]													
60M1510-3		60		20.75 [527.1]													
												WEIGHT APPROX. 65.75 LBS.		CODE IDENT. NO. 83008		DWG. NO. 031-3769	
												SCALE .5=1		SHEET 1 OF 1		DWG. SIZE D	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Staco:](#)

[M1510-3](#)