


MAXIMUM OUTPUT CURRENT IN OUTPUT VOLTAGE RANGE FROM 0 TO 25 PERCENT ABOVE LINE VOLTAGE. AT HIGHER OUTPUT VOLTAGES, OUTPUT CURRENT MUST BE REDUCED ACCORDING TO RATING CURVE (SEE FIGURE A).

++ MAXIMUM KVA AT MAXIMUM OUTPUT AND CORRESPONDING DE-RATED CURRENT. MAXIMUM KVA AT LOWER OUTPUT VOLTAGES MAY BE CALCULATED FROM RATING CURVE, (SEE FIGURE A).

V.D. = VOLTAGE DOUBLER.

						SPEED (SECONDS)		MODEL NUMBER			
						15		15M6020E-6PS			
						30		30M6020E-6PS			
						60		60M6020E-6PS			
SPECIFICATIONS											
WIRING		INPUT		OUTPUT			SHAFT ROTATION FOR VOLTAGE INCREASE	TERMINAL CONNECTIONS FOR INCREASING VOLTAGE AS VIEWED FROM TOP			
		VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD			INPUT	OUTPUT		
					MAX. AMPS	MAX. KVA					
SINGLE PHASE SERIES PARALLEL		480	50/60	0-480	105	50.4	CW	4-4	D-D		
				0-560	105	58.8	CW	2-2	D-D		
		240	50/60	0-560	105 # V.D.	25.2 ++	CW	5-5	D-D		
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ± DECIMALS HOLES ANGLES DRAFT .XX .0005 .12 .0002 .03 1° 1-1/2° .XXX .005				TITLE: SPEC. CONTROL DRAWING MOTORIZED VARIABLE XFMR. M6020E-6PS				 A Components Corporation of American Century 301 Gadella Boulevard Dayton, Ohio 45403 USA			
MATERIAL: _____		ALL DIMENSIONS APPLY AFTER PLATING									
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.				DRAWN BY TIM RAU		DATE 11/20/96				FIRST USED ON M6020E-6PS	
				CHECKER		DATE				WEIGHT APPROX.	
				ENGINEER		DATE		SCALE .2=1		SHEET 1 OF 1	
										DWG. NO. 032-7832	

DWG. SIZE D	DWG. NO. 032-7832		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	24585	5/3/01	
REVISED & UPDATED			



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

M6020E-6PS