



**SET POINT ADJUSTMENT:**  
THE OUTPUT SET POINT MAY BE ADJUSTED WITH THE REMOTE 1K POTENTIOMETER PROVIDED OR WITH A 0-5 VDC SIGNAL TO THE J3 CONNECTOR ON THE STEPPER DRIVE CONTROL. MAKE CONNECTIONS TO J3-2(+) & J3-3(-). A NOMINAL +5 VDC SETPOINT SUPPLY IS AVAILABLE AT J3-1 (ADJUSTABLE AT TRIMPOT R22).

SPECIFICATIONS										
WIRING	INPUT			OUTPUT				TERMINAL CONNECTIONS		
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD				
				MAX. AMPS	MAX. KVA	MAX. AMPS	MAX. KVA	INPUT	OUTPUT	
SINGLE PHASE	120	50/60	0-120	10	1.2	13	1.56	1-4	4-3	
			0-140	10	1.4	-	-	5-4	4-3	
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±			TITLE:							
DECIMALS		HOLES	ANGLES	DRAFT	UNITS		SPEC. CONTROL DRAWING			
.XX		.0000	.06 .002	1°	1-1/2°	IN [mm]				
MATERIAL			ALL DIMENSIONS APPLY AFTER PLATING		STEPPER DRIVEN VARIABLE TRANSFORMER MODEL SD1010					
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.					DRAWN BY	DATE	FIRST USED ON	DO NOT SCALE DWG.	CUSTOMER APPROVAL	DATE
					CHECKER	DATE	WEIGHT APPROX.	CODE IDENT. NO. 83008	DWG. SIZE	DWG. NO.
					ENGINEER	DATE	SCALE 1 = 1	SHEET 1 OF 1	D	095-1803

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

SD1010