





DWG. SIZE	DWG. NO.		
D	095-1801		
REVISIONS			
SYM.	E.C.N.	DATE	APVD.
A	22984	12/1/95	
	RELOCATED SWITCHES		
B	23275	12/6/96	
	8.06 WAS 7.94		
C	23938	3/1/99	
	REVISED BASE		



SET POINT ADJUSTMENT:
THE OUTPUT SET POINT MAY BE ADJUSTED WITH THE REMOTE 1K POTENTIOMETER PROVIDED OR WITH A 0-5 VDC SIGNAL TO THE J3 CONNECTOR ON THE STEPPER DRIVE CONTROLLER. MAKE CONNECTIONS TO J3-2 & J3-3.

SPECIFICATIONS														
WIRING	INPUT		OUTPUT				TERMINAL CONNECTIONS							
	VOLTS	HERTZ	VOLTS	CONSTANT CURRENT LOAD		CONSTANT IMPEDANCE LOAD								
				MAX. AMPS	MAX. KVA	MAX. AMPS	MAX. KVA	INPUT	OUTPUT					
SINGLE PHASE	120	60	0-120	12	1.44	15	1.80	1-4	4-3					
UNLESS OTHERWISE SPECIFIED, TOLERANCE IS ±			TITLE: SPEC. CONTROL DRAWING STEPPER DRIVEN VARIABLE TRANSFORMER SD1210					 ENERGY PRODUCTS CO. A COMPONENTS CORPORATION OF AMERICA COMPANY DAYTON, OHIO U.S.A.						
DECIMALS .XX .0005		HOLES .06 .002								ANGLES 1°		DRAFT 1-1/2°		
UNITS IN [mm]		ALL DIMENSIONS APPLY AFTER PLATING												
MATERIAL :			DRAWN BY S.A. SMITH DATE 9/12/95 FIRST USED ON DO NOT SCALE DWG. CUSTOMER APPROVAL DATE											
The information and design disclosed herein was originated by and is the property of STACO ENERGY PRODUCTS CO., which reserves all patent, proprietary, design, manufacturing, reproduction, use and sale rights thereto, and to any article disclosed therein except to the extent rights are expressly granted to others. The foregoing does not apply to vendor proprietary parts.			CHECKER		DATE		WEIGHT APPROX.		CODE IDENT. NO. 83008		DWG. NO.			
			ENGINEER		DATE		SCALE 1=1		SHEET 1 OF 1		D 095-1801			

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Staco:

SD1210