

Product data sheet

Characteristics

XSPN10122

inductive sensor XSP - cylindrical M30 - Sn 10 mm - cable 2m

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XS
Series name	Application
Sensor type	Inductive proximity sensor
Sensor name	XSP
Sensor design	Cylindrical M30
Body type	Fixed
Type of output signal	Discrete
[Us] rated supply voltage	12...48 V DC
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Detection face	Frontal
Supply voltage limits	10...58 V DC
Residual current	<= 0.5 mA open state
Marking	CE

Environment

Product certifications	CCC
Ambient air temperature for operation	-13...158 °F (-25...70 °C)

Ordering and shipping details

Category	22486 - SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	00785901267171
Nbr. of units in pkg.	1
Package weight(Lbs)	0.31
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XSPN10122](#)