

## Product data sheet

### Characteristics

# XUYFVERTD201

glass fibre optic for sensor - thru-beam -  
straight - High temp - 2m - Sn200mm

Product availability: Non-Stock - Not normally stocked in distribution facility



### Main

Range of product	OsiSense XU
Sensor name	XUY
Sensor design	Fiber design
Sheath type	High temperature
[Sn] nominal sensing distance	7.87 in (200 mm) XUYAFV
End fitting type	Straight with nickel plated brass, M4 x 0.7

### Complementary

Electronic sensor type	Photo-electric sensor
Optic fiber material	50 µ glass
Sheath material	Flexible stainless steel
Detection system	Thru beam
Optic fiber length	6.56 ft (2 m)
Minimum bending radius	1.18 in (30 mm)
Head mounting	M4 x 0.7
Product weight	0.13 lb(US) (0.06 kg)


### Environment

Ambient air temperature for operation	-13...392 °F (-25...200 °C)
---------------------------------------	-----------------------------

### Ordering and shipping details

Category	22481 - SENSORS, PHOTOELECTRIC
Discount Schedule	DS2
GTIN	003389119008433
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20000000000000001
Returnability	N
Country of origin	FR

### Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0647 - Schneider Electric declaration of conformity  Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>

### Contractual warranty

Warranty period	18 months
-----------------	-----------

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XUYFVERTD201](#)