

Product data sheet

Characteristics

XUYFVPTD301NUCL

glass fibre optic for sensor - diffuse - lateral - standard

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	OsiSense XU
Sensor name	XUY
Sensor design	Fiber design
Sheath type	High temperature
[Sn] nominal sensing distance	3.15 in (80 mm) XUYAFV
End fitting type	Lateral with nickel plated brass, M4 x 0.7

Complementary

Electronic sensor type	Photo-electric sensor
Optic fiber material	50 μ glass
Sheath material	Flexible stainless steel
Detection system	Diffuse
Head mounting	M4 x 0.7

Ordering and shipping details

Category	22481 - SENSORS, PHOTOELECTRIC
Discount Schedule	DS2
GTIN	003389119040563
Nbr. of units in pkg.	1
Package weight(Lbs)	1.3200000000000001
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Compliant - since 0647 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XUYFVPTD301NUCL](#)