


## 30 A - 800 V - 150 °C 8H Triac in TO-220AB



### Features

- 30 A high current Triac
- 800 V symmetrical blocking voltage
- 150 °C maximum junction temperature  $T_j$
- Three triggering quadrants
- High noise immunity - static  $dV/dt$
- Robust dynamic turn-off commutation -  $(di/dt)_c$
- ECOPACK2 compliant component

### Applications

- Home automation Smart AC plug
- Water heater, room heater and coffee machine
- AC Induction and Universal Motor control
- Inrush current limiter in AC DC rectifiers
- Lighting and automation I/O control
- General purpose AC line load control

### Description

Specifically designed to operate at 800 V and 150 °C, the T3035H-8T Triac housed in TO-220AB provides an enhanced thermal management: this 30 A Triac is the right choice for a compact drive of heavy AC loads and enables the heatsink size reduction.

Based on the ST Snubberless high temperature technology, it offers higher specified turn off commutation and noise immunity levels up to the  $T_j$  max.

The T3035H-8T safely optimizes the control of the hardest universal motors, heaters and inductive loads for industrial control and home appliances.

| Product status link       |       |
|---------------------------|-------|
| <a href="#">T3035H-8T</a> |       |
| Product summary           |       |
| $I_{T(RMS)}$              | 30 A  |
| $V_{DRM}/V_{RRM}$         | 800 V |
| $V_{DSM}/V_{RSM}$         | 900 V |
| $I_{GT}$                  | 35 mA |

# 1 Characteristics

**Table 1. Absolute maximum ratings (limiting values)**

| Symbol            | Parameter                                                                                                             |                                                                     | Value       | Unit                   |
|-------------------|-----------------------------------------------------------------------------------------------------------------------|---------------------------------------------------------------------|-------------|------------------------|
| $I_{T(RMS)}$      | RMS on-state current (full sine wave)                                                                                 | $T_c = 121\text{ }^{\circ}\text{C}$                                 | 30          | A                      |
| $I_{TSM}$         | Non repetitive surge peak on-state current<br>(full cycle, $T_j$ initial = $25\text{ }^{\circ}\text{C}$ )             | $t = 16.7\text{ ms}$                                                | 283         | A                      |
|                   |                                                                                                                       | $t = 20\text{ ms}$                                                  | 270         |                        |
| $I^2t$            | $I^2t$ value for fusing                                                                                               | $t_p = 10\text{ ms}$                                                | 482         | $\text{A}^2\text{s}$   |
| $di/dt$           | Critical rate of rise of on-state current,<br>$I_G = 2 \times I_{GT}$ , $tr \leq 100\text{ ns}$ , $f = 100\text{ Hz}$ | $T_j = 25\text{ }^{\circ}\text{C}$                                  | 100         | $\text{A}/\mu\text{s}$ |
| $V_{DRM}/V_{RRM}$ | Repetitive peak off-state voltage                                                                                     |                                                                     | 800         | V                      |
| $V_{DSM}/V_{RSM}$ | Non Repetitive peak off-state voltage                                                                                 | $t_p = 10\text{ ms}$ , $T_j = 25\text{ }^{\circ}\text{C}$           | 900         | V                      |
| $I_{GM}$          | Peak gate current                                                                                                     | $t_p = 20\text{ }\mu\text{s}$ , $T_j = 150\text{ }^{\circ}\text{C}$ | 4           | A                      |
| $P_{GM}$          | Maximum gate power dissipation                                                                                        |                                                                     | 5           | W                      |
| $P_{G(AV)}$       | Average gate power dissipation                                                                                        | $T_j = 150\text{ }^{\circ}\text{C}$                                 | 1           | W                      |
| $T_{stg}$         | Storage temperature range                                                                                             |                                                                     | -40 to +150 | $^{\circ}\text{C}$     |
| $T_j$             | Operating junction temperature range                                                                                  |                                                                     | -40 to +150 | $^{\circ}\text{C}$     |
| $T_L$             | Maximum lead temperature for soldering during 10 s                                                                    |                                                                     | 260         | $^{\circ}\text{C}$     |

**Table 2. Electrical characteristics ( $T_j = 25\text{ }^{\circ}\text{C}$ , unless otherwise specified)**

| Symbol            | Test conditions                                |                                     | Quadrants; $T_j$                    |      | Value | Unit                   |
|-------------------|------------------------------------------------|-------------------------------------|-------------------------------------|------|-------|------------------------|
| $I_{GT}$          | $V_D = 12\text{ V}$ , $R_L = 30\text{ }\Omega$ |                                     | I - II - III                        | Min. | 5     | mA                     |
|                   | $V_D = 12\text{ V}$ , $R_L = 30\text{ }\Omega$ |                                     | I - II - III                        | Max. | 35    | mA                     |
| $V_{GT}$          | $V_D = 12\text{ V}$ , $R_L = 30\text{ }\Omega$ |                                     | I - II - III                        | Max. | 1.3   | V                      |
| $V_{GD}$          | $V_D = V_{DRM}$ , $R_L = 3.3\text{ k}\Omega$   | $T_j = 150\text{ }^{\circ}\text{C}$ | I - II - III                        | Min. | 0.15  | V                      |
| $I_L$             | $I_G = 1.2 \times I_{GT}$                      |                                     | I - III                             | Max. | 75    | mA                     |
|                   |                                                |                                     | II                                  | Max. | 90    | mA                     |
| $I_H^{(1)}$       | $I_T = 500\text{ mA}$ , gate open              |                                     |                                     | Max. | 60    | mA                     |
| $dV/dt^{(1)}$     | $V_D = 536\text{ V}$ , gate open               |                                     | $T_j = 150\text{ }^{\circ}\text{C}$ | Min. | 2000  | $\text{V}/\mu\text{s}$ |
| $(di/dt)_c^{(1)}$ | Without snubber network                        |                                     | $T_j = 150\text{ }^{\circ}\text{C}$ | Min. | 25    | $\text{A}/\text{ms}$   |

1. For both polarities of A2 referenced to A1.

**Table 3. Static characteristics**

| Symbol            | Test conditions                                      | $T_j$  |      | Value | Unit |
|-------------------|------------------------------------------------------|--------|------|-------|------|
| $V_{TM}^{(1)}$    | $I_T = 42\text{ A}$ , $t_p = 380\text{ }\mu\text{s}$ | 25 °C  | Max. | 1.55  | V    |
| $V_{TO}^{(1)}$    | Threshold voltage                                    | 150 °C | Max. | 0.83  | V    |
| $R_D^{(1)}$       | Dynamic resistance                                   | 150 °C | Max. | 16    | mΩ   |
| $I_{DRM}/I_{RRM}$ | $V_D = V_R = V_{DRM} = V_{RRM}$                      | 25 °C  | Max. | 2.5   | μA   |
|                   |                                                      | 150 °C |      | 8.5   | mA   |
|                   | $V_D = V_R = 400\text{ V}$ , peak voltage            | 150 °C | Max. | 3.6   | mA   |


1. For both polarities of A2 referenced to A1.

**Table 4. Thermal resistance**


| Symbol        | Parameter             |      | Value | Unit |
|---------------|-----------------------|------|-------|------|
| $R_{th(j-c)}$ | Junction to case (AC) | Max. | 0.8   | °C/W |
| $R_{th(j-a)}$ | Junction to ambient   | Typ. | 60    | °C/W |

## 1.1 Characteristics (curves)


**Figure 1. Maximum power dissipation versus on-state RMS current**




**Figure 2. On-state RMS current versus case temperature**




**Figure 3. On-state RMS current versus ambient temperature (free air convection)**




**Figure 4. On-state characteristics (maximum values)**




**Figure 5. Relative variation of thermal impedance versus pulse duration**




**Figure 6. Recommended maximum case-to-ambient thermal resistance versus ambient temperature for different peak off-state voltages**




**Figure 7. Relative variation of gate trigger voltage and current versus junction temperature (typical values)**




**Figure 8. Relative variation of holding current and latching current versus junction temperature (typical values)**




**Figure 9. Surge peak on-state current versus number of cycles**




**Figure 10. Non repetitive surge peak on-state current for a sinusoidal pulse with width  $t_p < 10$  ms**




**Figure 11. Relative variation of static dV/dt immunity versus junction temperature**



**Figure 12. Relative variation of critical rate of decrease of main current versus junction temperature**



**Figure 13. Relative variation of Leakage current versus junction temperature for different values of blocking voltage**




## 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK is an ST trademark.

### 2.1 TO-220AB package information

- Epoxy resin is halogen free and meets UL94 flammability standard, level V0
- Lead-free plating package leads
- Recommended torque: 0.4 to 0.6 N·m

**Figure 14. TO-220AB package outline**



(1) Resin gate position accepted in one of the two positions or in the symmetrical opposites.

**Table 5. TO-220AB package mechanical data**

| Ref. | Dimensions  |       |       |                       |        |        |
|------|-------------|-------|-------|-----------------------|--------|--------|
|      | Millimeters |       |       | Inches <sup>(1)</sup> |        |        |
|      | Min.        | Typ.  | Max.  | Min.                  | Typ.   | Max.   |
| A    | 15.20       |       | 15.90 | 0.5984                |        | 0.6260 |
| a1   |             | 3.75  |       |                       | 0.1476 |        |
| a2   | 13.00       |       | 14.00 | 0.5118                |        | 0.5512 |
| B    | 10.00       |       | 10.40 | 0.3937                |        | 0.4094 |
| b1   | 0.61        |       | 0.88  | 0.0240                |        | 0.0346 |
| b2   | 1.23        |       | 1.32  | 0.0484                |        | 0.0520 |
| C    | 4.40        |       | 4.60  | 0.1732                |        | 0.1811 |
| c1   | 0.49        |       | 0.70  | 0.0193                |        | 0.0276 |
| c2   | 2.40        |       | 2.72  | 0.0945                |        | 0.1071 |
| e    | 2.40        |       | 2.70  | 0.0945                |        | 0.1063 |
| F    | 6.20        |       | 6.60  | 0.2441                |        | 0.2598 |
| I    | 3.73        |       | 3.88  | 0.1469                |        | 0.1528 |
| L    | 2.65        |       | 2.95  | 0.1043                |        | 0.1161 |
| l2   | 1.14        |       | 1.70  | 0.0449                |        | 0.0669 |
| l3   | 1.14        |       | 1.70  | 0.0449                |        | 0.0669 |
| l4   | 15.80       | 16.40 | 16.80 | 0.6220                | 0.6457 | 0.6614 |
| M    |             | 2.6   |       |                       | 0.1024 |        |

1. Inch dimensions are for reference only.

### 3 Ordering information

Figure 15. Ordering information scheme




Table 6. Ordering information

| Order code | Marking   | Package  | Weight | Base qty. | Delivery mode |
|------------|-----------|----------|--------|-----------|---------------|
| T3035H-8T  | T3035H-8T | TO-220AB | 2.1 g  | 50        | Tube          |

## Revision history

**Table 7. Document revision history**

| Date        | Version | Changes                           |
|-------------|---------|-----------------------------------|
| 27-Jul-2018 | 1       | Initial release.                  |
| 25-Jun-2019 | 2       | Minor text changed.               |
| 20-Dec-2019 | 3       | Added <a href="#">Figure 10</a> . |
| 15-Jan-2020 | 4       | Updated <a href="#">Table 6</a> . |
| 21-Dec-2020 | 5       | Updated general description.      |

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to [www.st.com/trademarks](http://www.st.com/trademarks). All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics – All rights reserved

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[T3035H-8T](#)