

Product availability: Stock - Normally stocked in distribution facility



Main

Range of product	Preventa Safety automation
Product or component type	Preventa safety module
Safety module name	XPSATE
Safety module application	For emergency stop and switch monitoring
Function of module	Emergency stop button with 2 NC contacts
Safety level	Can reach PL d/category 3 conforming to EN/ISO 13849-1 time delay safety outputs Can reach PL e/category 4 conforming to EN/ISO 13849-1 instantaneous safety outputs Can reach SILCL 3 conforming to EN/IEC 62061 instantaneous safety outputs Can reach SILCL 2 conforming to EN/IEC 62061 time delay safety outputs
Safety reliability data	DC > 99 % conforming to EN/ISO 13849-1 instantaneous safety outputs MTTFd = 134.8 years conforming to EN/ISO 13849-1 instantaneous safety outputs MTTFd = 54.5 years conforming to EN/ISO 13849-1 time delay safety outputs DC > 98.4 conforming to EN/ISO 13849-1 time delay safety outputs PFHd = 6.81E-9 1/h conforming to EN/IEC 62061 instantaneous safety outputs PFHd = 1.96E-8 1/h conforming to EN/IEC 62061 time delay safety outputs
Type of start	Configurable
Connections - terminals	Captive screw clamp terminals, clamping capacity: 2 x 0.5...2 x 1.5 mm ² flexible cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 1 x 0.14...1 x 2.5 mm ² flexible cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 1 x 0.14...1 x 2.5 mm ² solid cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 1.5 mm ² flexible cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 1 x 0.25...1 x 2.5 mm ² flexible cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 2 x 0.14...2 x 0.75 mm ² flexible cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 2 x 0.14...2 x 0.75 mm ² solid cable with cable end, with double bezel Captive screw clamp terminals, clamping capacity: 2 x 0.25...2 x 1 mm ² flexible cable with cable end, with double bezel
Output type	Relay instantaneous opening 2 NO, volt-free Relay time delay opening 3 NO, volt-free
Number of additional circuits	3 solid state outputs
[Us] rated supply voltage	24 V AC/DC (- 15...10 %)

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Synchronisation time between inputs	75 ms
Supply frequency	50/60 Hz
Power consumption in W	<= 8 W
Input protection type	Internal, electronic
Time delay range	0...30 s
[Uc] control circuit voltage	24 V AC/DC
Breaking capacity	C300: 180 VA, AC-15 (holding) relay output C300: 1800 VA, AC-15 (inrush) relay output
Breaking capacity	1 A at 24 V (DC-13) time constant: 50 ms for relay output
Output thermal current	2.5 A time delay outputs 5 A instantaneous outputs
[Ith] conventional free air thermal current	8 A
Associated fuse rating	4 A fuse type gG for time delay outputs conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fuse type gG for instantaneous outputs conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum output current	10 mA relay output
Minimum output voltage	17 V relay output
Response time on input open	<= 20 ms
[Ui] rated insulation voltage	300 V (degree of pollution: 2) conforming to DIN VDE 0110 part 1 300 V (degree of pollution: 2) conforming to IEC 60947-5-1
[Uimp] rated impulse withstand voltage	4 kV overvoltage category III conforming to IEC 60947-5-1 4 kV overvoltage category III conforming to DIN VDE 0110 part 1
Local signalling	4 LEDs
Mounting support	35 mm symmetrical DIN rail
Product weight	0.62 lb(US) (0.28 kg)

Environment

Standards	EN/IEC 60204-1 EN/IEC 60947-5-1 EN/ISO 13850
Product certifications	TÜV UL CSA
IP degree of protection	IP20 (terminals) conforming to EN/IEC 60529 IP40 (enclosure) conforming to EN/IEC 60529
Ambient air temperature for operation	14...131 °F (-10...55 °C)
Ambient air temperature for storage	-13...185 °F (-25...85 °C)

Ordering and shipping details

Category	22477 - SAFETY MODULES (PREVENTA)
Discount Schedule	SAF2
GTIN	00785901690542
Nbr. of units in pkg.	1
Package weight(Lbs)	0.7399999999999999
Returnability	Y
Country of origin	ID


Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XPSATE5110](#)