

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Preventa Safety automation
Product or component type	Preventa safety time delay module
Safety module name	XPSTSA
Safety module application	For application with interlocking on high inertia
Function of module	Monitoring safety time delays
Safety level	Can reach PL d/category 3 conforming to EN/ISO 13849-1 Can reach SILCL 2 conforming to EN/IEC 62061
Safety reliability data	DC = 60...90 % conforming to EN/ISO 13849-1 MTTFd = 126 years conforming to EN/ISO 13849-1 PFHd = 1.3E-7 1/h conforming to EN/IEC 62061
[Us] rated supply voltage	24 V AC (- 20...10 %) 24 V DC (- 15...15 %)
Output type	Relay 1 NO + 2 NC, volt-free
Number of additional circuits	2 solid state outputs

Complementary

Supply frequency	50/60 Hz
Power consumption in VA	<= 2.3 VA DC <= 4.3 VA AC
Input protection type	Internal, electronic
Time delay	1...31 s configurable
Breaking capacity	C300: holding 180 VA AC-15 relay output C300: inrush 1800 VA AC-15 relay output
Breaking capacity	1.5 A/24 V - L/R = 50 ms, DC-13 relay output 20 mA / 24 V solid state output circuit 10 mA/48 V
[Ith] conventional free air thermal current	<= 6 A for relay output
Associated fuse rating	4 A gG relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200 6 A fast blow relay output conforming to EN/IEC 60947-5-1, DIN VDE 0660 part 200
Minimum output current	10 mA relay output
Minimum output voltage	17 V relay output
[Ui] rated insulation voltage	300 V, degree of pollution 2 conforming to IEC 60947-5-1 300 V, degree of pollution 2 conforming to DIN VDE 0110 part 1
[Uimp] rated impulse withstand voltage	4 kV overvoltage category III, conforming to IEC 60947-5-1 4 kV overvoltage category III, conforming to DIN VDE 0110 part 1
Local signalling	4 LEDs

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. It is not intended to be used as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections - terminals	Captive screw clamp terminals flexible cable: 0.14...0.75 mm ² without cable end, 1 wire Captive screw clamp terminals flexible cable: 0.14...2.5 mm ² without cable end, 1 wire Captive screw clamp terminals flexible cable: 0.25...1 mm ² with cable end, without bezel, 1 wire Captive screw clamp terminals flexible cable: 0.25...1.5 mm ² with cable end, with bezel, 1 wire Captive screw clamp terminals flexible cable: 0.25...2.5 mm ² with cable end, without bezel, 1 wire Captive screw clamp terminals flexible cable: 0.5...1.5 mm ² with cable end, with double bezel, 1 wire Captive screw clamp terminals solid cable: 0.14...0.75 mm ² without cable end, 1 wire Captive screw clamp terminals solid cable: 0.14...2.5 mm ² without cable end, 1 wire
Mounting support	35 mm symmetrical DIN rail
Depth	4.49 in (114 mm)
Height	3.9 in (99 mm)
Width	1.77 in (45 mm)
Product weight	0.55 lb(US) (0.25 kg)

Environment

Standards	EN/IEC 60204-1 EN/IEC 60947-5-1
Product certifications	CSA TÜV UL
IP degree of protection	IP20(Terminals) conforming to EN/IEC 60529 IP40(enclosure) conforming to EN/IEC 60529
Ambient air temperature for operation	14...131 °F (-10...55 °C)
Ambient air temperature for storage	-13...185 °F (-25...85 °C)

Ordering and shipping details

Category	22477 - SAFETY MODULES (PREVENTA)
Discount Schedule	SAF2
GTIN	00785901512707
Nbr. of units in pkg.	1
Package weight(Lbs)	0.5500000000000004
Returnability	N
Country of origin	ID


Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Dimensions



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XPSTSA5142P](#)