



Automotive 2-line ESD protection for high speed lines




SOT323-3L
(Jedec TO-236)



Functional diagram

Features

- AEC-Q101 qualified 
- Flow-through routing to keep signal integrity
- Ultra large bandwidth: 3 GHz
- Ultra low capacitance: 0.7 pF
- Extended operating junction temperature range: -40 °C to 150 °C
- RoHS compliant
- Complies with ISO 10605 - C = 150 pF, R = 330 Ω exceeds level 4
 - ±12 kV (contact discharge)
 - ±15 kV (air discharge)
- Complies with ISO 10605 - C = 330 pF, R = 330 Ω
 - ±8 kV (contact discharge)
 - ±12 kV (air discharge)

Application

The **HSP051-2W3Y** is designed to protect against electrostatic discharge on automotive circuits such as:

- APIX
- LVDS & digital video interface
- Ethernet and BroadReach
- USB 2.0 and USB 3.0
- High speed communication buses

Description

The **HSP051-2W3Y** is an ESD array designed for high-speed differential lines protection.


The ultralow capacitance variation ensures negligible influence on signal-skew.

Product status link	
HSP051-2W3Y	
Product summary	
Order code	HSP051-2W3Y
Marking	H5Y
Package	SOT323-3L
Packing	Tape and reel

1 Characteristics

Table 1. Absolute maximum ratings ($T_{amb} = 25^{\circ}\text{C}$)

Symbol	Parameter		Value	Unit
V_{PP}	Peak pulse voltage	ISO10605 / IEC 61000-4-2 ($C = 150\text{ pF}$, $R = 330\ \Omega$):		
		Contact discharge	12	kV
		Air discharge	15	
		ISO10605 ($C = 330\text{ pF}$, $R = 330\ \Omega$)		
		Contact discharge	8	
		Air discharge	12	
P_{PP}	Peak pulse power dissipation (8/20 μs)		20	W
I_{PP}	Peak Pulse current (8/20 μs)		1.8	A
T_{stg}	Storage temperature range		-65 to +150	$^{\circ}\text{C}$
T_j	Operating junction temperature range		-40 to +150	$^{\circ}\text{C}$
T_L	Maximum lead temperature for soldering during 10 s		260	$^{\circ}\text{C}$

Figure 1. Electrical characteristics - parameter definitions

Table 2. Electrical characteristics (values) ($T_{amb} = 25^{\circ}\text{C}$)

Symbol	Test conditions	Min.	Typ.	Max.	Unit
V_{BR}	$I_R = 1\text{ mA}$	5.3			V
I_R	$V_R = 3\text{ V}$			100	nA
	$V_R = 5\text{ V}$			150	
V_{CL}	ISO 10605- $C = 150\text{ pF}$, $R = 330\ \Omega$ +8 kV contact discharge, measured at 30 ns		18		V
$C_{I/O-GND}$	$V_{I/O} = 0\text{ V}$, $f = 1\text{ MHz}$, $V_{OSC} = 30\text{ mV}$		0.7	1.0	pF
$\Delta C_{I/O-GND}$			0.03		
f_C	$S_{21} = -3\text{ dB}$		3		GHz

1.1 Characteristics (curves)

Figure 2. Leakage current versus junction temperature




Figure 3. Junction capacitance versus reverse applied voltage




Figure 4. ESD response to ISO 10605 - C = 150 pF, R = 330 Ω (+8 kV contact discharge)



Figure 5. ESD response to ISO 10605 - C = 150 pF, R = 330 Ω (-8 kV contact discharge)




Figure 6. TLP




Figure 7. S₂₁ attenuation




Figure 8. Fast transient pulse 3a ($U_s = -150\text{ V}$)




Figure 9. Fast transient pulse 3b ($U_s = +150\text{ V}$)




Figure 10. Slow transient pulse - negative 2a ($U_s = -85\text{ V}$)





Figure 11. Slow transient pulse - positive 2a ($U_s = +85\text{ V}$)



2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

2.1 SOT323-3L package information

- Epoxy meets UL 94,V0
- Lead-free package

Figure 12. SOT323-3L package outline




Table 3. SOT323-3L package mechanical data

Ref.	Dimensions					
	Millimeters			Inches ⁽¹⁾		
	Min.	Typ.	Max.	Min.	Typ.	Max.
A	0.8		1.1	0.031		0.043
A1	0.0		0.1	0.000		0.003
b	0.25		0.4	0.0098		0.0157
c	0.1		0.26	0.003		0.0102
D	1.8	2.0	2.2	0.070	0.078	0.086
E	1.15	1.25	1.35	0.0452	0.0492	0.0531
e	0.60	0.65	0.70	0.024	0.026	0.028
H	1.8	2.1	2.4	0.070	0.082	0.094
L	0.1	0.2	0.30	0.004	0.008	0.012
Θ		0	30°	0		30°

1. Values in inches are converted from mm and rounded to 3 decimal digits

Figure 13. SOT323-3L recommended footprint (dimensions in inches)






Figure 14. SOT323-3L marking



XXXX : Marking

Figure 15. Package orientation in reel



Pin 1 located according to EIA-481

Note: Pocket dimensions are not on scale
Pocket shape may vary depending on package

Figure 16. Tape and reel orientation




Figure 17. 7" reel dimension values




Figure 18. Inner box dimension values





Figure 19. Tape outline



Note: Pocket dimensions are not on scale
Pocket shape may vary depending on package


Table 4. Tape dimension values

Ref.	Dimensions		
	Millimeters		
	Min.	Typ.	Max.
D0	1.45	1.5	1.6
D1	1		
F	3.45	3.5	3.55
K0	1.3	1.4	1.5
P0	3.9	4.0	4.1
P1	3.9	4.0	4.1
P2	1.95	2.0	2.05
W	7.9	8	8.3

3 Recommendation on PCB assembly

3.1 Reflow profile

Figure 20. ST ECOPACK® recommended soldering reflow profile for PCB mounting



Note: Minimize air convection currents in the reflow oven to avoid component movement.

4 Ordering information

Figure 21. Ordering information scheme




Table 5. Ordering information

Order code	Marking ⁽¹⁾	Package	Weight	Base qty.	Delivery mode
HSP051-2W3Y	H5Y	SOT323-3L	6 mg	3000	Tape and reel

1. The marking can be rotated by multiples of 90° to differentiate assembly location

Revision history

Table 6. Document revision history

Date	Version	Changes
10-Jul-2018	1	Initial release.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[HSP051-2W3Y](#)