



Automotive-grade N-channel 40 V, 1.6 mΩ typ., 100 A, STripFET™ F7 Power MOSFET in an LFPAK 5x6 package


LFPAK 5x6


G4S123DTAB_LFPAK



Features

Order code	V _{DS}	R _{DS(on)} max.	I _D
STK184N4F7AG	40 V	2.0 mΩ	100 A

- AEC-Q101 qualified 
- Among the lowest R_{DS(on)} on the market
- Excellent FoM (figure of merit)
- Low C_{rss}/C_{iss} ratio for EMI immunity
- High avalanche ruggedness

Applications

- Switching applications

Description

This N-channel Power MOSFET utilizes STripFET™ F7 technology with an enhanced trench gate structure that results in very low on-state resistance, while also reducing internal capacitance and gate charge for faster and more efficient switching.

Product status link

[STK184N4F7AG](#)

Product summary

Order code	STK184N4F7AG
Marking	184N4F7AG
Package	LFPAK 5x6
Packing	Tape and reel

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{DS}	Drain-source voltage	40	V
V_{GS}	Gate-source voltage	± 20	V
$I_D^{(1)}$	Drain current (continuous) at $T_C = 25\text{ }^\circ\text{C}$	100	A
	Drain current (continuous) at $T_C = 100\text{ }^\circ\text{C}$	100	A
$I_{DM}^{(2)}$	Drain current (pulsed)	400	A
P_{TOT}	Total power dissipation at $T_C = 25\text{ }^\circ\text{C}$	136	W
I_{AV}	Avalanche current, repetitive or not repetitive (pulse width limited by maximum junction temperature)	42	A
E_{AS}	Single pulse avalanche energy (starting $T_J = 25\text{ }^\circ\text{C}$, $I_D = I_{AV}$, $V_{DD} = 25\text{ V}$)	280	mJ
T_J	Operating junction temperature range	-55 to 175	$^\circ\text{C}$
T_{stg}	Storage temperature range		

1. Drain current is limited by package, the current capability of the silicon is 184 A at 25 $^\circ\text{C}$.

2. Pulse width limited by safe operating area.

Table 2. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj-pcb}^{(1)}$	Thermal resistance junction-pcb	31.3	$^\circ\text{C/W}$
$R_{thj-case}$	Thermal resistance junction-case	1.1	$^\circ\text{C/W}$

1. When mounted on FR-4 board of 1 inch², 2oz Cu, $t < 10\text{ s}$.

2 Electrical characteristics

($T_C = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

Table 3. On/off states

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)DSS}$	Drain-source breakdown voltage	$V_{GS} = 0\text{ V}$, $I_D = 1\text{ mA}$	40			V
I_{DSS}	Zero gate voltage drain current	$V_{GS} = 0\text{ V}$, $V_{DS} = 40\text{ V}$			1	μA
I_{GSS}	Gate-body leakage current	$V_{GS} = 20\text{ V}$, $V_{DS} = 0\text{ V}$			100	nA
$V_{GS(th)}$	Gate threshold voltage	$V_{DS} = V_{GS}$, $I_D = 250\text{ }\mu\text{A}$	2		4	V
$R_{DS(on)}$	Static drain-source on-resistance	$V_{GS} = 10\text{ V}$, $I_D = 50\text{ A}$		1.6	2.0	m Ω

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{iss}	Input capacitance	$V_{DS} = 25\text{ V}$, $f = 1\text{ MHz}$, $V_{GS} = 0\text{ V}$	-	2750	-	pF
C_{oss}	Output capacitance		-	625	-	pF
C_{rss}	Reverse transfer capacitance		-	200	-	pF
Q_g	Total gate charge	$V_{DD} = 20\text{ V}$, $I_D = 100\text{ A}$, $V_{GS} = 0\text{ to }10\text{ V}$ (see Figure 13. Test circuit for gate charge behavior)	-	35	-	nC
Q_{gs}	Gate-source charge		-	16	-	nC
Q_{gd}	Gate-drain charge		-	8.9	-	nC

Table 5. Switching times

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	$V_{DD} = 20\text{ V}$, $I_D = 50\text{ A}$, $R_G = 4.7\text{ }\Omega$, $V_{GS} = 10\text{ V}$ (see Figure 12. Test circuit for resistive load switching times and Figure 17. Switching time waveform)	-	12	-	ns
t_r	Rise time		-	20	-	ns
$t_{d(off)}$	Turn-off delay time		-	33.4	-	ns
t_f	Fall time		-	20.7	-	ns

Table 6. Source-drain diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{SD}^{(1)}$	Forward on voltage	$I_{SD} = 100\text{ A}$, $V_{GS} = 0\text{ V}$	-		1.1	V
t_{rr}	Reverse recovery time	$I_D = 100\text{ A}$, $di/dt = 100\text{ A}/\mu\text{s}$	-	25		ns
Q_{rr}	Reverse recovery charge	$V_{DD} = 20\text{ V}$	-	9.5		nC
I_{RRM}	Reverse recovery current	(see Figure 14. Test circuit for inductive load switching and diode recovery times)	-	0.8		A

1. Pulsed: pulse duration = 300 μs , duty cycle 1.5%

2.1 Electrical characteristics (curves)

Figure 1. Safe operating area




Figure 2. Thermal impedance




Figure 3. Output characteristics




Figure 4. Transfer characteristics




Figure 5. Gate charge vs gate-source voltage




Figure 6. Static drain-source on-resistance




Figure 7. Capacitance variations




Figure 8. Normalized $V_{(BR)DSS}$ vs temperature




Figure 9. Normalized gate threshold voltage vs temperature




Figure 10. Normalized on-resistance vs temperature







Figure 11. Source-drain diode forward characteristics




3 Test circuits

Figure 12. Test circuit for resistive load switching times



AM01468v1

Figure 13. Test circuit for gate charge behavior



AM01469v1

Figure 14. Test circuit for inductive load switching and diode recovery times



AM01470v1

Figure 15. Unclamped inductive load test circuit


AM01471v1

Figure 16. Unclamped inductive waveform


AM01472v1

Figure 17. Switching time waveform



AM01473v1

4 Package information

In order to meet environmental requirements, ST offers these devices in different grades of **ECOPACK®** packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.

4.1 LPAK 5x6 package information

Figure 18. LPAK 5x6 package outline




00299525_A

Table 7. LFPACK 5x6 package mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	1.01		1.20
A1	0.00		0.15
A2	0.95		1.10
A3		0.25	
A4	0.50	0.55	0.65
b	0.35		0.50
b2	3.62		4.41
b3	2.0		2.20
b4	0.70		0.90
b5			0.7
c	0.19	0.20 ⁽¹⁾	0.25
c2	0.24		0.30
D	3.80		4.10
D1	3.80	4.00	4.20
E	4.8		5.0
E1	3.1		3.3
e		1.27	
H	5.8		6.2
L	0.40		0.85
L1	0.80		1.30
L2	0.80		1.3
w		0.25	
y		0.10	
Θ	0°		8°

1. Dimension without plating

Figure 19. LFPACK 5x6 recommended footprint



00299525_FP_A

Revision history

Table 8. Document revision history

Date	Revision	Changes
05-Jul-2018	1	First release.
10-Jan-2019	2	Updated title and features on cover page. Updated Section 1 Electrical ratings and Section 2 Electrical characteristics . Added Section 2.1 Electrical characteristics (curves) . Minor text changes

Contents

1	Electrical ratings	2
2	Electrical characteristics.....	3
2.1	Electrical characteristics (curves)	4
3	Test circuits	6
4	Package information.....	7
4.1	LFPACK 5x6 package information	7
	Revision history	11

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2019 STMicroelectronics – All rights reserved

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[STK184N4F7AG](#)