

High voltage fast-switching NPN power transistor

Features

- High voltage capability
- Very high switching speed
- Minimum lot-to-lot spread for reliable operation
- Low base-drive requirements

Applications

- Switch mode power supplies
- Motor control

Description

The BUF410A is manufactured using high voltage multi epitaxial planar technology for high switching speeds and high voltage capacity. It uses a cellular emitter structure with planar edge termination to enhance switching speeds while maintaining a wide RBSOA.




Figure 1. Internal schematic diagram




Table 1. Device summary

Order code	Marking	Package	Packaging
BUF410A	BUF410A	TO-247	Tube

1 Electrical ratings

Table 2. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CEV}	Collector-emitter voltage ($V_{BE} = -1.5$ V)	1000	V
V_{CEO}	Collector-emitter voltage ($I_B = 0$)	450	V
V_{EBO}	Emitter-base voltage ($I_C = 0$)	7	V
I_C	Collector current	15	A
I_{CM}	Collector peak current ($t_P < 5$ ms)	30	A
I_B	Base current	3	A
I_{BM}	Base peak current ($t_P < 5$ ms)	15	A
P_{tot}	Total dissipation at $T_C = 25$ °C	125	W
T_{stg}	Storage temperature	-65 to 150	°C
T_J	Max. operating junction temperature	150	°C

Table 3. Thermal data

Symbol	Parameter	Value	Unit
$R_{thj-case}$	Thermal resistance junction-case max	1	°C/W

2 Electrical characteristics

($T_{\text{case}} = 25\text{ }^{\circ}\text{C}$ unless otherwise specified)

Table 4. Electrical characteristics

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
I_{CER}	Collector cut-off current ($R_{\text{BE}} = 10\ \Omega$)	$V_{\text{CE}} = 1000\text{ V}$ $V_{\text{CE}} = 1000\text{ V}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$			0.2 1	mA mA
I_{CEV}	Collector cut-off current ($V_{\text{BE}} = -1.5\text{ V}$)	$V_{\text{CE}} = 1000\text{ V}$ $V_{\text{CE}} = 1000\text{ V}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$			0.2 1	mA mA
I_{EBO}	Emitter cut-off current ($I_{\text{C}} = 0$)	$V_{\text{EB}} = 5\text{ V}$			1	mA
$V_{\text{CEO(sus)}}^{(1)}$	Collector-emitter sustaining voltage ($I_{\text{B}} = 0$)	$I_{\text{C}} = 200\text{ mA}$	450			V
V_{EBO}	Emitter-base voltage ($I_{\text{C}} = 0$)	$I_{\text{E}} = 50\text{ mA}$	7			V
$V_{\text{CE(sat)}}^{(1)}$	Collector-emitter saturation voltage	$I_{\text{C}} = 5\text{ A}$ $I_{\text{B}} = 0.5\text{ A}$ $I_{\text{C}} = 5\text{ A}$ $I_{\text{B}} = 0.5\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$ $I_{\text{C}} = 10\text{ A}$ $I_{\text{B}} = 2\text{ A}$ $I_{\text{C}} = 10\text{ A}$ $I_{\text{B}} = 2\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$		0.8 0.5	2.8 2	V V V V
$V_{\text{BE(sat)}}^{(1)}$	Base-emitter saturation voltage	$I_{\text{C}} = 5\text{ A}$ $I_{\text{B}} = 0.5\text{ A}$ $I_{\text{C}} = 5\text{ A}$ $I_{\text{B}} = 0.5\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$ $I_{\text{C}} = 10\text{ A}$ $I_{\text{B}} = 2\text{ A}$ $I_{\text{C}} = 10\text{ A}$ $I_{\text{B}} = 2\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$		0.9 1.1	1.5 1.5	V V V V
di_{C}/dt	Rate of rise on-state collector current	$V_{\text{CC}} = 300\text{ V}$ $R_{\text{C}} = 0$ $t_{\text{p}} = 3\text{ }\mu\text{s}$ $I_{\text{B1}} = 0.75\text{ A}$ $T_{\text{C}} = 25\text{ }^{\circ}\text{C}$ $I_{\text{B1}} = 0.75\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$ $I_{\text{B1}} = 3\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$	45 100	60		A/ μs A/ μs A/ μs
$V_{\text{CE(dyn)}}$	Collector-emitter dynamic voltage (3 μs)	$V_{\text{CC}} = 300\text{ V}$ $R_{\text{C}} = 60\ \Omega$ $I_{\text{B1}} = 0.75\text{ A}$ $T_{\text{C}} = 25\text{ }^{\circ}\text{C}$ $I_{\text{B1}} = 0.75\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$		2.1	8	V V
$V_{\text{CE(dyn)}}$	Collector-emitter dynamic voltage (5 μs)	$V_{\text{CC}} = 300\text{ V}$ $R_{\text{C}} = 60\ \Omega$ $I_{\text{B1}} = 0.75\text{ A}$ $T_{\text{C}} = 25\text{ }^{\circ}\text{C}$ $I_{\text{B1}} = 0.75\text{ A}$ $T_{\text{C}} = 100\text{ }^{\circ}\text{C}$		1.1	4	V V
t_{s}	Inductive load Storage time	$I_{\text{C}} = 5\text{ A}$ $V_{\text{CC}} = 50\text{ V}$ $V_{\text{BB}} = -5\text{ V}$ $R_{\text{BB}} = 1.2\ \Omega$		0.8		μs
t_{f}	Fall time	$V_{\text{Clamp}} = 400\text{ V}$ $I_{\text{B1}} = 0.5\text{ A}$		0.05		μs
t_{c}	Cross over time	$L = 0.5\text{ mH}$		0.08		μs

Table 4. Electrical characteristics (continued)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
t_s	Inductive load Storage time	$I_C = 5\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = -5\text{ V}$ $R_{BB} = 1.2\ \Omega$			1.8	μs
t_f	Fall time	$V_{Clamp} = 400\text{ V}$ $I_{B1} = 0.5\text{ A}$			0.1	μs
t_c	Cross over time	$L = 0.5\text{ mH}$ $T_C = 100\text{ }^\circ\text{C}$			0.18	μs
V_{CEW}	Maximum collector emitter voltage without snubber	$I_C = 5\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = -5\text{ V}$ $R_{BB} = 1.2\ \Omega$ $I_{B1} = 0.5\text{ A}$ $L = 0.5\text{ mH}$ $T_C = 125\text{ }^\circ\text{C}$	500			V
t_s	Inductive load Storage time	$I_C = 5\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = 0$ $R_{BB} = 0.3\ \Omega$		1.5		μs
t_f	Fall time	$V_{Clamp} = 400\text{ V}$ $I_{B1} = 0.5\text{ A}$		0.04		μs
t_c	Cross over time	$L = 0.5\text{ mH}$		0.07		μs
t_s	Inductive load Storage time	$I_C = 5\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = 0$ $R_{BB} = 0.3\ \Omega$			3	μs
t_f	Fall time	$V_{Clamp} = 400\text{ V}$ $I_{B1} = 0.5\text{ A}$			0.15	μs
t_c	Cross over time	$L = 0.5\text{ mH}$ $T_C = 100\text{ }^\circ\text{C}$			0.25	μs
V_{CEW}	Maximum collector emitter voltage without snubber	$I_C = 5\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = 0$ $R_{BB} = 0.3\ \Omega$ $I_{B1} = 0.5\text{ A}$ $L = 0.5\text{ mH}$ $T_C = 125\text{ }^\circ\text{C}$	500			V
t_s	Inductive load Storage time	$I_C = 10\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = -5\text{ V}$ $R_{BB} = 1.2\ \Omega$		1.9		μs
t_f	Fall time	$V_{Clamp} = 400\text{ V}$ $I_{B1} = 2\text{ A}$		0.06		μs
t_c	Cross over time	$L = 0.25\text{ mH}$		0.12		μs
t_s	Inductive load Storage time	$I_C = 10\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = -5\text{ V}$ $R_{BB} = 1.2\ \Omega$			3.2	μs
t_f	Fall time	$V_{Clamp} = 400\text{ V}$ $I_{B1} = 2\text{ A}$			0.12	μs
t_c	Cross over time	$L = 0.25\text{ mH}$ $T_C = 100\text{ }^\circ\text{C}$			0.3	μs
V_{CEW}	Maximum collector emitter voltage without snubber	$I_C = 15\text{ A}$ $V_{CC} = 50\text{ V}$ $V_{BB} = -5\text{ V}$ $R_{BB} = 1.2\ \Omega$ $I_{B1} = 3\text{ A}$ $L = 0.1\text{ mH}$ $T_C = 125\text{ }^\circ\text{C}$	400			V

1. Pulse duration = 300 μs , duty cycle $\leq 1.5\%$

2.1 Electrical characteristics (curves)

Figure 2. Forward biased safe operating area






Figure 3. Reverse biased safe operating area



2.2 Test circuit

Figure 4. Inductive load switching test circuit




3 Package mechanical data

In order to meet environmental requirements, ST offers these devices in ECOPACK® packages. These packages have a Lead-free second level interconnect. The category of second level interconnect is marked on the package and on the inner box label, in compliance with JEDEC Standard JESD97. The maximum ratings related to soldering conditions are also marked on the inner box label. ECOPACK is an ST trademark. ECOPACK specifications are available at: www.st.com

TO-247 Mechanical data

Dim.	mm.		
	Min.	Typ	Max.
A	4.85		5.15
A1	2.20		2.60
b	1.0		1.40
b1	2.0		2.40
b2	3.0		3.40
c	0.40		0.80
D	19.85		20.15
E	15.45		15.75
e		5.45	
L	14.20		14.80
L1	3.70		4.30
L2		18.50	
øP	3.55		3.65
øR	4.50		5.50
S		5.50	



4 Revision history

Table 5. Document revision history

Date	Revision	Changes
18-Mar-2002	2	
13-Mar-2008	3	Package change from TO-218 to TO-247.

Please Read Carefully:

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.

UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED REPRESENTATIVE OF ST, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS, WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2008 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

www.st.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[BUF410A](#)