

# XCSCM4110L2

safety limit switch XCSM - metal - steel plunger  
- 2 NC + 2 NO - cable 2 m



Product availability: Stock - Normally stocked in distribution facility



## Main

|                               |                                                                      |
|-------------------------------|----------------------------------------------------------------------|
| Range of product              | Preventa Safety detection                                            |
| Product or component type     | Safety limit switch                                                  |
| Component name                | XCSM                                                                 |
| Design                        | Miniature                                                            |
| Material                      | Metal                                                                |
| Head type                     | Plunger head                                                         |
| Protection technology         | Plastic protective cover, secured by 5-lobe socket head safety screw |
| Type of operator              | Metal end plunger                                                    |
| Contacts type and composition | 1 NC + 1 NC + 1 NO + 1 NO                                            |
| Contact operation             | Snap action                                                          |

## Complementary

|                                        |                                                                                                                                                                                                                                                                                                        |
|----------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Electrical connection                  | Pre-cabled                                                                                                                                                                                                                                                                                             |
| Cable length                           | 6.56 ft (2 m)                                                                                                                                                                                                                                                                                          |
| Cable composition                      | 9 x 0.34 mm <sup>2</sup>                                                                                                                                                                                                                                                                               |
| Fixing mode                            | By the body                                                                                                                                                                                                                                                                                            |
| Number of poles                        | 4                                                                                                                                                                                                                                                                                                      |
| Positive opening                       | With NC contact                                                                                                                                                                                                                                                                                        |
| Mechanical durability                  | 10000000 cycles                                                                                                                                                                                                                                                                                        |
| Minimum force for tripping             | 8.5 N                                                                                                                                                                                                                                                                                                  |
| Positive opening minimum force         | 42.5 N                                                                                                                                                                                                                                                                                                 |
| Minimum actuation speed                | 0.01 m/min                                                                                                                                                                                                                                                                                             |
| Maximum actuation speed                | 1.64 ft/s (0.5 m/s)                                                                                                                                                                                                                                                                                    |
| Contact code designation               | B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN 60947-5-1<br>B300, AC-15 (Ue = 240 V, Ie = 1.5 A) conforming to EN/IEC 60947-5-1 appendix A<br>R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN 60947-5-1<br>R300, DC-13 (Ue = 250 V, Ie = 0.1 A) conforming to EN/IEC 60947-5-1 appendix A |
| [Ui] rated insulation voltage          | 300 V conforming to CSA C22.2 No 14<br>400 V (degree of pollution: 3) conforming to IEC 60947-5-1<br>300 V conforming to UL 508                                                                                                                                                                        |
| [Uimp] rated impulse withstand voltage | 4 kV conforming to IEC 60664<br>4 kV conforming to IEC 60947-1                                                                                                                                                                                                                                         |
| Resistance across terminals            | <= 25 MOhm conforming to IEC 60255-7 category 3                                                                                                                                                                                                                                                        |
| Short-circuit protection               | 6 A cartridge fuse type gG (gl)                                                                                                                                                                                                                                                                        |
| Repeat accuracy                        | 0.05 mm on the tripping points                                                                                                                                                                                                                                                                         |
| Body material                          | Zamak                                                                                                                                                                                                                                                                                                  |
| Head material                          | Zamak                                                                                                                                                                                                                                                                                                  |
| Depth                                  | 0.63 in (16 mm)                                                                                                                                                                                                                                                                                        |
| Height                                 | 2.36 in (60 mm)                                                                                                                                                                                                                                                                                        |
| Width                                  | 1.18 in (30 mm)                                                                                                                                                                                                                                                                                        |
| Product weight                         | 0.36 lb(US) (0.165 kg)                                                                                                                                                                                                                                                                                 |

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environment

|                                       |                                                                                                                                                                                                                                                                                                                                |
|---------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Standards                             | EN/IEC 60947-5-1<br>EN 1088<br>CSA C22.2 No 14<br>UL 508<br>EN/IEC 60204-1                                                                                                                                                                                                                                                     |
| Product certifications                | CSA<br>UL                                                                                                                                                                                                                                                                                                                      |
| Safety level                          | Can reach category 4 with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1<br>Can reach PL = e with the appropriate monitoring system and correctly wired conforming to EN/ISO 13849-1<br>Can reach SIL 3 with the appropriate monitoring system and correctly wired conforming to IEC 61508 |
| Safety reliability data               | B10d = 50000000 (value given for a life time of 20 years limited by mechanical or contact wear)                                                                                                                                                                                                                                |
| Protective treatment                  | TC                                                                                                                                                                                                                                                                                                                             |
| Ambient air temperature for operation | -13...158 °F (-25...70 °C)                                                                                                                                                                                                                                                                                                     |
| Ambient air temperature for storage   | -40...158 °F (-40...70 °C)                                                                                                                                                                                                                                                                                                     |
| Vibration resistance                  | 5 gn (f = 10...500 Hz) conforming to IEC 60068-2-6                                                                                                                                                                                                                                                                             |
| Shock resistance                      | 25 gn 18 ms conforming to IEC 60068-2-27                                                                                                                                                                                                                                                                                       |
| Electrical shock protection class     | Class I conforming to EN/IEC 61140<br>Class I conforming to NF C 20-030                                                                                                                                                                                                                                                        |
| IP degree of protection               | IP68 conforming to IEC 60529<br>IP66 conforming to IEC 60529<br>IP67 conforming to IEC 60529                                                                                                                                                                                                                                   |
| IK degree of protection               | IK06 conforming to EN 50102                                                                                                                                                                                                                                                                                                    |

## Ordering and shipping details

|                       |                                 |
|-----------------------|---------------------------------|
| Category              | 22411 - LIMIT SWITCHES,IEC,XCKJ |
| Discount Schedule     | T                               |
| GTIN                  | 00785901590385                  |
| Nbr. of units in pkg. | 1                               |
| Package weight(Lbs)   | 1.2                             |
| Returnability         | Y                               |
| Country of origin     | ID                              |

## Offer Sustainability

|                                  |                                                                                                                                    |
|----------------------------------|------------------------------------------------------------------------------------------------------------------------------------|
| Sustainable offer status         | Green Premium product                                                                                                              |
| RoHS (date code: YYWW)           | Compliant - since 1002 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a> |
| REACH                            | Reference not containing SVHC above the threshold                                                                                  |
| Product environmental profile    | Available                                                                                                                          |
| Product end of life instructions | Need no specific recycling operations                                                                                              |
| California proposition 65        | WARNING: This product can expose you to chemicals including:                                                                       |
| - - - - - Substance 1            | Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and                                        |
| - - - - - Substance 2            | Diisodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.          |
| - - - - - More information       | For more information go to <a href="http://www.p65warnings.ca.gov">www.p65warnings.ca.gov</a>                                      |

## Contractual warranty

|                 |           |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XCSM4110L2](#)