


## Low drop OR-ing power Schottky diode

Datasheet - production data



### Description

Packaged in TO-220AC or D<sup>2</sup>PAK, this device is especially intended for use as an OR-ing diode in fault tolerant power supply equipments.

Table 1: Device summary

| Symbol       | Value  |
|--------------|--------|
| $I_{F(AV)}$  | 20 A   |
| $V_{RRM}$    | 15 V   |
| $V_F$ (typ.) | 0.28 V |
| $T_j$ (max.) | 125 °C |

### Features

- Very low forward voltage drop for less power dissipation and reduced heatsink size
- Reverse voltage suited to OR-ing of 3 V, 5 V and 12 V rails
- Avalanche capability specified
- ECOPACK<sup>®</sup>2 compliant component for D<sup>2</sup>PAK on demand

# 1 Characteristics

**Table 2: Absolute ratings (limiting values at 25 °C, unless otherwise specified)**

| Symbol              | Parameter                                             |                                                 | Value       | Unit |
|---------------------|-------------------------------------------------------|-------------------------------------------------|-------------|------|
| V <sub>RRM</sub>    | Repetitive peak reverse voltage                       |                                                 | 15          | V    |
| I <sub>F(RMS)</sub> | Forward rms current                                   |                                                 | 30          | A    |
| I <sub>F(AV)</sub>  | Average forward current                               | T <sub>C</sub> = 115 °C, DC                     | 20          | A    |
| I <sub>FSM</sub>    | Surge non repetitive forward current                  | t <sub>p</sub> = 10 ms sinusoidal               | 310         | A    |
| P <sub>ARM</sub>    | Repetitive peak avalanche power                       | t <sub>p</sub> = 10 μs, T <sub>j</sub> = 125 °C | 970         | W    |
| T <sub>stg</sub>    | Storage temperature range                             |                                                 | -65 to +150 | °C   |
| T <sub>j</sub>      | Maximum operating junction temperature <sup>(1)</sup> |                                                 | 125         |      |

**Notes:**

<sup>(1)</sup>(dP<sub>tot</sub>/dT<sub>j</sub>) < (1/R<sub>th(j-a)</sub>) condition to avoid thermal runaway for a diode on its own heatsink.

**Table 3: Thermal parameters**

| Symbol               | Parameter        | Max. value | Unit |
|----------------------|------------------|------------|------|
| R <sub>th(j-c)</sub> | Junction to case | 1.6        | °C/W |

**Table 4: Static electrical characteristics**

| Symbol                        | Parameter               | Test conditions         |                       | Min. | Typ. | Max. | Unit |
|-------------------------------|-------------------------|-------------------------|-----------------------|------|------|------|------|
| I <sub>R</sub> <sup>(1)</sup> | Reverse leakage current | T <sub>j</sub> = 25 °C  | V <sub>R</sub> = 15 V | -    |      | 6    | mA   |
|                               |                         | T <sub>j</sub> = 100 °C |                       | -    | 200  | 500  |      |
| V <sub>F</sub> <sup>(1)</sup> | Forward voltage drop    | T <sub>j</sub> = 25 °C  | I <sub>F</sub> = 19 A | -    |      | 0.41 | V    |
|                               |                         |                         | I <sub>F</sub> = 40 A | -    |      | 0.52 |      |
|                               |                         | T <sub>j</sub> = 125 °C | I <sub>F</sub> = 19 A | -    | 0.28 | 0.33 |      |
|                               |                         |                         | I <sub>F</sub> = 40 A |      | 0.42 | 0.50 |      |


**Notes:**

<sup>(1)</sup>Pulse test: t<sub>p</sub> = 380 μs, δ < 2%


To evaluate the maximum conduction losses, use the following equation:

$$P = 0.18 \times I_{F(AV)} + 8.10^{-3} \times I_{F(RMS)}^2$$


## 1.1 Characteristics (curves)




**Figure 2: Average forward current versus ambient temperature ( $\delta = 1$ )**




**Figure 3: Normalized avalanche power derating versus pulse duration ( $T_j = 125^{\circ}C$ )**




**Figure 4: Relative variation of thermal impedance junction to case versus pulse duration**




**Figure 5: Reverse leakage current versus reverse voltage applied (typical values)**




**Figure 6: Junction capacitance versus reverse voltage applied (typical values)**




**Figure 7: Forward voltage drop versus forward current (typical values)**



**Figure 8: Forward voltage drop versus forward current (maximum values)**



**Figure 9: Thermal resistance junction to ambient versus copper surface under tab for D<sup>2</sup>PAK**




## 2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK® is an ST trademark.

- Cooling method: by conduction (C)
- Epoxy meets UL 94,V0
- Recommended torque value: 0.55 N·m (for TO-220AC)
- Maximum torque value: 0.7 N·m (for TO-220AC)


## 2.1 D<sup>2</sup>PAK package information

Figure 10: D<sup>2</sup>PAK package outline

This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

Table 5: D<sup>2</sup>PAK package mechanical data

| Ref. | Dimensions  |       |        |       |
|------|-------------|-------|--------|-------|
|      | Millimeters |       | Inches |       |
|      | Min.        | Max.  | Min.   | Max.  |
| A    | 4.36        | 4.60  | 0.172  | 0.181 |
| A1   | 0.00        | 0.25  | 0.000  | 0.010 |
| b    | 0.70        | 0.93  | 0.028  | 0.037 |
| b2   | 1.14        | 1.70  | 0.045  | 0.067 |
| c    | 0.38        | 0.69  | 0.015  | 0.027 |
| c2   | 1.19        | 1.36  | 0.047  | 0.053 |
| D    | 8.60        | 9.35  | 0.339  | 0.368 |
| D1   | 6.90        | 8.00  | 0.272  | 0.311 |
| D2   | 1.10        | 1.50  | 0.043  | 0.060 |
| E    | 10.00       | 10.55 | 0.394  | 0.415 |
| E1   | 8.10        | 8.90  | 0.319  | 0.346 |
| E2   | 6.85        | 7.25  | 0.266  | 0.282 |
| e    | 2.54 typ.   |       | 0.100  |       |
| e1   | 4.88        | 5.28  | 0.190  | 0.205 |
| H    | 15.00       | 15.85 | 0.591  | 0.624 |
| J1   | 2.49        | 2.90  | 0.097  | 0.112 |
| L    | 1.90        | 2.79  | 0.075  | 0.110 |
| L1   | 1.27        | 1.65  | 0.049  | 0.065 |
| L2   | 1.30        | 1.78  | 0.050  | 0.070 |
| R    | 0.4 typ.    |       | 0.015  |       |
| V2   | 0°          | 8°    | 0°     | 8°    |

Figure 11: D<sup>2</sup>PAK recommended footprint (dimensions in mm)



## 2.2 TO-220AC package information

Figure 12: TO-220AC package outline




Table 6: TO-220AC package mechanical data

| Ref. | Dimensions  |       |            |       |
|------|-------------|-------|------------|-------|
|      | Millimeters |       | Inches     |       |
|      | Min.        | Max.  | Min.       | Max.  |
| A    | 4.40        | 4.60  | 0.173      | 0.181 |
| C    | 1.23        | 1.32  | 0.048      | 0.051 |
| D    | 2.40        | 2.72  | 0.094      | 0.107 |
| E    | 0.49        | 0.70  | 0.019      | 0.027 |
| F    | 0.61        | 0.88  | 0.024      | 0.034 |
| F1   | 1.14        | 1.70  | 0.044      | 0.066 |
| G    | 4.95        | 5.15  | 0.194      | 0.202 |
| H2   | 10.00       | 10.40 | 0.393      | 0.409 |
| L2   | 16.40 typ.  |       | 0.645 typ. |       |
| L4   | 13.00       | 14.00 | 0.511      | 0.551 |
| L5   | 2.65        | 2.95  | 0.104      | 0.116 |
| L6   | 15.25       | 15.75 | 0.600      | 0.620 |
| L7   | 6.20        | 6.60  | 0.244      | 0.259 |
| L9   | 3.50        | 3.93  | 0.137      | 0.154 |
| M    | 2.6 typ.    |       | 0.102 typ. |       |
| Diam | 3.75        | 3.85  | 0.147      | 0.151 |

### 3 Ordering information

Table 7: Ordering information

| Order code    | Marking    | Package            | Weight | Base qty. | Delivery mode |
|---------------|------------|--------------------|--------|-----------|---------------|
| STPS20L15D    | STPS20L15D | TO-220AC           | 1.86 g | 50        | Tube          |
| STPS20L15G-TR | STPS20L15G | D <sup>2</sup> PAK | 1.38 g | 1000      | Tape and reel |

### 4 Revision history

Table 8: Document revision history

| Date        | Revision | Changes                                                                                                                                                                                                                                                |
|-------------|----------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| 24-Jul-2012 | 3        |                                                                                                                                                                                                                                                        |
| 13-Oct-2016 | 4        | Updated cover page, <a href="#">Section 3.1: "Characteristics (curves)"</a> , <a href="#">Section 3: "Characteristics"</a> , <a href="#">Section 4.2: "D<sup>2</sup>PAK package information"</a> and <a href="#">Table 7: "Ordering information"</a> . |

**IMPORTANT NOTICE – PLEASE READ CAREFULLY**

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2016 STMicroelectronics – All rights reserved

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[STMicroelectronics:](#)

[STPS20L15D](#) [STPS20L15G-TR](#)