


AVERY DENNISON MARKETING SPECIFICATION

HISTORY

| ENG | REV. | DATE | DESCRIPTION |
|-----|------|---------|-------------|
| DMG | A | 9-26-14 | RELEASED |

THE SUBJECT MATTER DISCLOSED HEREIN EMBODIES PROPRIETARY INFORMATION WHICH IS THE CONFIDENTIAL PROPERTY OF THE AVERY DENNISON CO. NONE OF WHICH SHALL BE COPIED, REPRODUCED, DISCLOSED TO OTHERS, PUBLISHED OR USED IN WHOLE OR IN PART, FOR ANY PURPOSE OTHER THAN THAT FOR WHICH IT IS BEING MADE AVAILABLE WITHOUT THE EXPRESS ADVANCE WRITTEN PERMISSION OF A DULY AUTHORIZED AGENT OF THE COMPANY. THIS DOCUMENT IS THE PROPERTY OF THE AVERY DENNISON CO. AND IS TO BE RETURNED TO THE COMPANY ON DEMAND.



DIMENSION TAKEN FROM THE CROWN OF THE FIRST TOOTH

| | |
|------------------------|---|
| MOUNTING: | 7mm X12mm MIN. SLOTTED HOLE |
| PANEL THICKNESS RANGE: | 0.6mm TO 3.0mm THK. |
| TENSILE STRENGTH: | 50 LBF / 222.4N MIN. |
| OPERATING TEMP RANGE: | -40°F (-40°C) TO 239°F (115°C) CONTINUOUS AND 257°F (125°C) AT MAXIMUM EXPOSURE |
| WEIGHT: | 2.35 GRAMS EACH |
| BUNDLE DIAMETER: | Ø.06" (1.6mm) TO Ø 1.50" (38.1mm) |
| INSTALLATION TOOL: | 12001 - HAND TOOL 12500 - PNEUMATIC TOOL |
| TOOL TENSION SETTING: | 6 - 8 |
| PACKAGING: | 1000/BAG, 5 BAGS/MASTER |

| | |
|------------|---------------------------------------|
| APPROVALS: | ENG. APPR. <i>[Signature]</i> 9/26/14 |
| | Q.A. APPR. <i>[Signature]</i> 9/26/14 |



AVERY DENNISON

FASTENER DIVISION
FITCHBURG, MA 01420 U.S.A.
TEL 1-800-225-9913
FAX 978-353-8157

| SPECIFIED TOLERANCES | |
|----------------------|-----------|
| INCHES | mm |
| .XX ± .03 | .X ± .7 |
| .XXX ± .010 | .XX ± .25 |
| ANGULAR: ± 2° | |

| | |
|----------|--|
| MATERIAL | NYLON 6/6, IMPACT MODIFIED, HEAT STABILIZED |
| COLOR | GREY |

| | | |
|-------------|-----------------------------------|---------------|
| DESCRIPTION | OFFSET SLOT TIE, 15mm, REV | |
| STOCK NO. | 20143-0 | REV. A |

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Avery Dennison:](#)

[20143-0](#)