





- Inductor for high withstand voltage (DC 120V) and large current
- Magnetically shielded
- Qualified AEC-Q200
- Operating temperature range: - 40°C~+150°C
(including coil's self temperature rise)



- LED Head light for Automobile
- ECU
- Automotive and other high temperature, high reliability application

Reference Land pattern - [mm]



Ver.1.7 (August 1, 2017)

Low-Profile High Current Power Inductor

CDEP15D90/T150



Electrical Characteristics: Standard Types

Part No.	Inductance (μ H) ($\pm 20\%$) ※1	D.C.R (m Ω) ($\pm 20\%$)	Saturation Current (A) ※2		Temperature Rise current (A) ※3
			at 20°C	at 150°C	
CDEP15D90T150NP-0R5MC-125	0.50	1.20	63.0	43.0	33.5
CDEP15D90T150NP-1R2MC-125	1.20	1.75	41.9	28.5	24.5
CDEP15D90T150NP-2R0MC-125	2.00	2.40	31.0	22.0	23.0
CDEP15D90T150NP-3R3MC-125	3.30	2.90	25.0	17.0	18.5
CDEP15D90T150NP-4R7MC-125	4.70	3.50	21.3	14.8	16.5
CDEP15D90T150NP-6R2MC-125	6.20	4.90	18.5	13.0	14.8
CDEP15D90T150NP-100MC-125	10.0	7.90	15.0	10.5	12.5
CDEP15D90T150NP-120MC-125	12.5	8.90	12.8	9.50	12.2
CDEP15D90T150NP-150MC-125	15.0	10.6	12.0	8.20	8.50
CDEP15D90T150NP-220MC-125	22.0	14.5	9.70	6.60	7.50

Electrical Characteristics: High Power Types

Part No.	Inductance (μ H) ($\pm 20\%$) ※1	D.C.R (m Ω) ($\pm 20\%$)	Saturation Current (A) ※2		Temperature Rise current (A) ※3
			at 20°C	at 150°C	
CDEP15D90T150NP-1R0MC-100	1.00	1.75	51.6	35.8	24.5
CDEP15D90T150NP-1R6MC-100	1.60	2.40	42.0	28.0	23.0
CDEP15D90T150NP-2R4MC-100	2.40	2.90	34.5	24.5	18.5
CDEP15D90T150NP-3R6MC-100	3.60	3.50	26.5	18.5	16.5
CDEP15D90T150NP-4R7MC-100	4.70	4.90	24.0	16.7	14.8
CDEP15D90T150NP-6R8MC-100	6.80	5.50	20.3	13.8	13.5
CDEP15D90T150NP-100MC-100	10.0	8.90	16.2	11.3	12.2
CDEP15D90T150NP-120MC-100	12.5	10.6	15.0	10.2	8.50
CDEP15D90T150NP-150MC-100	15.0	13.4	13.4	9.70	8.00
CDEP15D90T150NP-220MC-100	22.0	20.1	11.0	7.50	6.50

※ 1 Measuring frequency at 100kHz 0.1V

※ 2 Saturation current: This indicates the actual value of D.C. current when the inductance becomes 30% lower than its nominal value.

※ 3 Temperature rise current: The actual value of D.C. current when the temperature of coil becomes $\Delta T=40^{\circ}\text{C}$ ($T_a=20^{\circ}\text{C}$).

Please note that when using the product while applying current with audio-frequency (AF) signals may results in audible noises due to magnetostriction. Also, in order to avoid an audible noise problem, operating with non-AF signals would be recommended. The noise amplify depending on the coil mount area on the PCB.


Note : This specification is subject to change without notice. Please contact your nearest sales office for updated information when placing an order.

Low-Profile High Current Power Inductor CDEP15D90/T150




Saturation Current & Temperature Rise Graph — L (20°C) — L (150°C) — ΔT
<Standard Types>


CDEP15D90T150NP-0R5MC-125




CDEP15D90T150NP-1R2MC-125




CDEP15D90T150NP-2R0MC-125




CDEP15D90T150NP-3R3MC-125



CDEP15D90T150NP-4R7MC-125



CDEP15D90T150NP-6R2MC-125




Note : This specification is subject to change without notice. Please contact your nearest sales office for updated information when placing an order.

Low-Profile High Current Power Inductor


CDEP15D90/T150




CDEP15D90T150NP-100MC-125




CDEP15D90T150NP-120MC-125



CDEP15D90T150NP-150MC-125



CDEP15D90T150NP-220MC-125



Note : This specification is subject to change without notice. Please contact your nearest sales office for updated information when placing an order.


Low-Profile High Current Power Inductor

CDEP15D90/T150




Saturation Current & Temperature Rise Graph — L (20°C) — L (150°C) — ΔT
 <High Power Types>


CDEP15D90T150NP-1R0MC-100




CDEP15D90T150NP-1R6MC-100




CDEP15D90T150NP-2R4MC-100




CDEP15D90T150NP-3R6MC-100



CDEP15D90T150NP-4R7MC-100



CDEP15D90T150NP-6R8MC-100




Note : This specification is subject to change without notice. Please contact your nearest sales office for updated information when placing an order.

Low-Profile High Current Power Inductor


CDEP15D90/T150




CDEP15D90T150NP-100MC-100




CDEP15D90T150NP-120MC-100



CDEP15D90T150NP-150MC-100



CDEP15D90T150NP-220MC-100



For sales office information, please [click here](#) to visit our website.

Note : This specification is subject to change without notice. Please contact your nearest sales office for updated information when placing an order.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Sumida:

[CDEP15D90T150NP-0R5MC-125](#) [CDEP15D90T150NP-120MC-100](#) [CDEP15D90T150NP-120MC-125](#)
[CDEP15D90T150NP-150MC-100](#) [CDEP15D90T150NP-150MC-125](#) [CDEP15D90T150NP-1R6MC-100](#)
[CDEP15D90T150NP-220MC-100](#) [CDEP15D90T150NP-220MC-125](#) [CDEP15D90T150NP-2R0MC-125](#)
[CDEP15D90T150NP-2R4MC-100](#) [CDEP15D90T150NP-3R3MC-125](#) [CDEP15D90T150NP-3R6MC-100](#)
[CDEP15D90T150NP-4R7MC-100](#) [CDEP15D90T150NP-4R7MC-125](#) [CDEP15D90T150NP-6R2MC-125](#)
[CDEP15D90T150NP-6R8MC-100](#)