# Type: CDR125

### Product Description


- -13.1×12.1mm Max.(L×W), 5.9mm Max. Height.
- •Inductance range:  $10 \sim 820 \, \mu$  H.
- -Rated current range: 0.36~2.65A.
- In addition to the standards versions shown here,


custom inductors are also available to meet your exact requirements.

### Feature


- -Magnetically shielded construction.
- Storage temperature range: -40°C ~+100°C.
- Operating temperature range: -40°C ~+100°C (Including coil's self temperature rise).
- Ideally used in Notebook PC ,LCD TV ,Game machine ,HDD,DSC/DVC, etc as DC-DC converter inductors.
- •RoHS compliance.

### Dimensions (mm)





### Land Pattern (mm)






# Type: CDR125

### Specification

Part name	Stamp	Inductance (μ H) ※ 1	D.C.R.( Ω ) [Max.] (at 20℃)	Rated Current (A) ※2	S.R.F. (MHz) [Typ.]
CDR125NP-100M	100M	10±20%	0.05	2.65	24.2
CDR125NP-120M	120M	12±20%	0.05	2.50	21.2
CDR125NP-150M	150M	15±20%	0.06	2.45	18.9
CDR125NP-180M	180M	18±20%	0.06	2.40	16.1
CDR125NP-220M	220M	22 +20% / -15%	0.07	2.20	15.2
CDR125NP-270M	270M	27 +20% / -15%	0.08	2.00	13.9
CDR125NP-330M	330M	33 +20% / -15%	0.10	1.80	12.8
CDR125NP-390M	390M	39 +20% / -15%	0.11	1.65	11.6
CDR125NP-470M	470M	47 +20% / -15%	0.12	1.50	10.4
CDR125NP-560M	560M	56 +20% / -15%	0.15	1.38	9.12
CDR125NP-680M	680M	68 +20% / -15%	0.17	1.26	8.50
CDR125NP-820M	820M	82 +20% / -15%	0.20	1.14	7.85
CDR125NP-101M	101M	100 +20% / -15%	0.25	1.05	6.92
CDR125NP-121M	121M	120 +20% / -15%	0.28	0.95	6.34
CDR125NP-151M	151M	150 +20% / -15%	0.40	0.85	5.55
CDR125NP-181M	181M	180 +20% / -15%	0.48	0.77	5.10
CDR125NP-221M	221M	220 +20% / -15%	0.52	0.70	4.51
CDR125NP-271M	271M	270 +20% / -15%	0.70	0.63	4.37
CDR125NP-331M	331M	330 +20% / -15%	0.80	0.57	3.90
CDR125NP-391M	391M	390 +20% / -15%	1.08	0.52	3.55
CDR125NP-471M	471M	470 +20% / -15%	1.20	0.48	3.25
CDR125NP-561M	561M	560 +20% / -15%	1.34	0.44	2.94
CDR125NP-681M	681M	680 +20% / -15%	1.78	0.40	2.64
CDR125NP-821M	821M	820 +20% / -15%	2.00	0.36	2.42

#### **※** Description of part name



% 1: Measuring frequency:10  $\mu$  H  $\,\sim\,$  82  $\mu$  H  $\,$  ;  $\,$  at  $\,$  2.52 MHz  $\,$ 

 $100\,\mu\,H\,\sim\!\!820\,\mu\,H$  ; at  $1\,kHz$ 

%2: Rated current: The D.C. current at which the inductance decreases to 75%(10  $\mu$  H~18  $\mu$  H) and 80% (22  $\mu$  H~820  $\mu$  H) of it's initial value or when∆t=40°C, whichever is lower(Ta=20°C).

# **Mouser Electronics**

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Sumida:

CDR125NP-100MC CDR125NP-220MC CDR125NP-101MC CDRH125NP-2R1NC CDR125NP-220JC CDR125NP-270JC CDR125NP-391JC CDR125NP-680JC CDR125NP-471JC CDR125NP-561MC CDR125NP-680MC CDR125NP-390MC CDR125NP-821JC CDR125NP-270MC CDR125NP-150MC CDR125NP-820JC CDR125NP-681MC CDR125NP-331JC CDR125NP-560JC CDR125NP-471MC CDR125NP-120MC CDR125NP-331MC CDR125NP-330JC CDR125NP-391MC CDR125NP-221MC CDR125NP-470JC CDR125NP-681JC CDR125NP-271JC CDR125NP-271MC CDR125NP-151MC CDR125NP-820MC CDR125NP-181JC CDR125NP-221JC CDR125NP-330MC CDR125NP-180MC CDR125NP-821MC CDR125NP-470MC CDR125NP-181MC CDR125NP-560MC CDR125NP-121MC CDR125NP-151JC CDR125NP-121JC CDR125NP-390JC