



# High power thin film chip resistors (long side terminal)

■ PRG series

AEC-Q200 Compliant


## Features

- Long side terminal enabling higher power capability
- Significantly larger power handling capability than conventional same size resistors  
Size: 3216 ~ 6432, power ratings: 0.5 ~ 3.0W, Resistance range: 2.5 ~ 250KΩ
- Precision resistance tolerance:  $\pm 0.1\%$ , very small TCR:  $\pm 25\text{ppm}/^\circ\text{C}$
- Thin film structure enabling low noise and anti-sulfur

## Applications

- Automotive electronics
- DC motor, inverters
- Robotics, Industrial control system

## ◆ Part numbering system



## ◆ Electrical Specification

| Type    | Power ratings | Temperature coefficient of resistance | Resistance range(Ω)<br>Resistance tolerance |            | Maximum voltage | Resistance value series | Operating temperature | Packaging quantity |
|---------|---------------|---------------------------------------|---------------------------------------------|------------|-----------------|-------------------------|-----------------------|--------------------|
|         |               | (ppm/°C)                              | ±0.1% (B)                                   | ±0.5% (D)  |                 |                         |                       |                    |
| PRG3216 | 1.0W          | ±25(P)                                | 47≤R≤100k                                   | 10≤R≤100k  | 150V            | E-24, E-96              | -55℃ ~ 155℃           | T5                 |
|         |               | ±50(Q)                                |                                             | 2.5≤R≤100k |                 |                         |                       |                    |
| PRG5025 | 1.5W ~ 2.0W   | ±25(P)                                | 47≤R≤200k                                   | 10≤R≤200k  | 200V            |                         |                       | T4                 |
|         |               | ±50(Q)                                |                                             | 2.5≤R≤200k |                 |                         |                       |                    |
| PRG6432 | 2.0W ~ 3.0W   | ±25(P)                                | 47≤R≤250k                                   | 10≤R≤250k  | 400V            |                         |                       |                    |
|         |               | ±50(Q)                                |                                             | 2.5≤R≤250k |                 |                         |                       |                    |

## ◆Dimensions



| Type           | Size (inch) | W               | L         | a         | b         | t               |
|----------------|-------------|-----------------|-----------|-----------|-----------|-----------------|
| <b>PRG3216</b> | 1206        | 3.20±0.40/-0.20 | 1.60±0.20 | 0.30±0.20 | 0.35±0.20 | 0.45±0.15/-0.10 |
| <b>PRG5025</b> | 2010        | 5.00±0.20       | 2.50±0.20 | 0.55±0.20 | 0.60±0.20 | 0.45±0.15/-0.10 |
| <b>PRG6432</b> | 2512        | 6.40±0.20/-0.40 | 3.20±0.20 | 0.40±0.20 | 0.55±0.20 | 0.45±0.15/-0.10 |

(unit : mm)

Thin film surface mount resistors

PRG series

## ◆Reliability specification

| Test items                     | Condition (test methods (JIS C5201-1))                          | Standard       |                |
|--------------------------------|-----------------------------------------------------------------|----------------|----------------|
|                                |                                                                 | ≤47Ω           | ≥47Ω           |
| Life (biased)                  | 70°C, rated voltage <sup>*1</sup> 90min on 30min off, 1000hours | ±(0.25%+0.05Ω) | ±(0.1%+0.01Ω)  |
| High temperature high humidity | 85°C, 85%RH, 1/10 of rated power, 90min on 30min off, 1000hours | ±(0.25%+0.05Ω) | ±(0.1%+0.01Ω)  |
| Temperature shock              | -55°C (30min) ~ 125°C (30min) 1000cycles                        | ±(0.25%+0.05Ω) | ±(0.1%+0.01Ω)  |
| High temperature exposure      | 155°C, no bias, 1000hours                                       | ±(0.25%+0.05Ω) | ±(0.1%+0.01Ω)  |
| Resistance to soldering heat   | 260±5°C, 10 seconds (reflow)                                    | ±(0.1%+0.01Ω)  | ±(0.05%+0.01Ω) |

\*1 Rated voltage is given by  $E = \sqrt{R \times P}$

E= rated voltage (V), R=nominal resistance value(Ω), P=rated power(W)




If rated voltage exceeds maximum voltage /element, maximum voltage/element is the rated voltage.

# High power thin film chip resistors (long side terminal)



## PRG series

### Reliability test data

#### Biased life test



#### High temperature high humidity (biased)



## ○ Temperature shock



## ○ High temperature exposure



## ◆ Derating Curve

### ○ PRG3216



### ○ PRG6432



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Susumu:](#)

[PRG3216P-3900-B-T5](#)