



Main

Range of product	OsiSense XM
Product or component type	Electronic pressure sensors
Pressure switch type of operation	Regulation between 2 thresholds
Pressure sensor name	XMLF
Wiring technique	5-wire
Pressure sensor size	1015.26 psi (70 bar)
Fluid connection type	1/4" - 18 NPT (female)
Controlled fluid	Air (5...176 °F (-15...80 °C)) Corrosive fluid (5...176 °F (-15...80 °C)) Hydraulic oil (5...176 °F (-15...80 °C)) Fresh water (32...176 °F (0...80 °C))
Type of output signal	Discrete
Analogue output function	-
Discrete output type	Relay
Electrical connection	5 pins male connector SAE 7/8"16 UN
Product specific application	-
Adjustable range of switching point on rising pressure	81.22...1015.26 psi (5.6...70 bar)
Adjustable range of switching point on falling pressure	50.76...984.81 psi (3.5...67.9 bar)
Destruction pressure	6091.59 psi (420 bar)
Type of installation	Control circuit
Scale type	Adjustable differential scale
Maximum switching current	1500 mA C300 AC-15 2.5 A
[Us] rated supply voltage	120 V AC, voltage limits: 102...132 V
Materials in contact with fluid	FPM (Viton) Stainless steel type AISI 303

Complementary

Setting	External setting
Possible differential minimum at low setting	30.46 psi (2.1 bar)
Possible differential minimum at high setting	30.46 psi (2.1 bar)
Possible differential maximum at high setting	964.5 psi (66.5 bar)
Maximum permissible accidental pressure	4061.06 psi (280 bar)
Local display	With
Protection type	Connection faults Overload protection Reverse polarity Short-circuit protection
Current consumption	32 mA
Operating rate in Hz	<= 50 Hz
Drift of the sensitivity	+/- 0.03 % of measuring range/°C
Drift of the zero point	+/- 0.1 % of measuring range/°C
Time delay range	0...50 s in steps of 1 second
Response time on output	5...500 ms, in steps of 1 ms
Mechanical durability	>= 10000000 cycles
Display response time type	Fast Normal Slow
Height	4.69 in (119 mm)
Depth	2.28 in (58 mm)

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Width	1.81 in (46 mm)
Product weight	1.34 lb(US) (0.61 kg)
Surge withstand	1 kV AC
Measurement accuracy	<= 0.6 % of the measuring range
Repeat accuracy	<= 0.5 %

Environment

operating position	Any position
standards	CE EN 50081 EN 50082 EN/IEC 60947-1 EN/IEC 60947-5-1 EN/IEC 61000-4-11 EN/IEC 61000-4-2 EN/IEC 61000-4-3 EN/IEC 61000-4-4 EN/IEC 61000-4-5 EN/IEC 61000-4-6 EN/IEC 61000-6-2 EN/IEC 61000-4-8
product certifications	CSA UL
ambient air temperature for operation	-13...167 °F (-25...75 °C)
vibration resistance	35 gn (f = 60...2000 Hz) conforming to EN/IEC 60068-2-6 5 gn (f = 25...200 Hz) conforming to EN/IEC 60068-2-6
protective treatment	TC
shock resistance	50 gn conforming to EN/IEC 60068-2-27
resistance to fast transients	2 kV conforming to EN/IEC 61000-4-4
IP degree of protection	IP67 conforming to EN/IEC 60529
NEMA degree of protection	NEMA 12 NEMA 13 NEMA 4 NEMA 6
resistance to electrostatic discharge	4 kV (on contact) conforming to EN/IEC 61000-4-2 8 kV (in air) conforming to EN/IEC 61000-4-2
resistance to electromagnetic fields	9.14 V/yd (10 V/m) conforming to EN/IEC 61000-4-3
resistance to conducted disturbances	10 V conforming to EN/IEC 61000-4-6

Offer Sustainability

Not Green Premium product	Not Green Premium product
Compliant - since 0627 - Schneider Electric declaration of conformity	Compliant - since 0627 - Schneider Electric declaration of conformity
Reference not containing SVHC above the threshold	Reference not containing SVHC above the threshold

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Telemecanique Sensors:](#)

[XMLF070E2046](#)