



Schneider Electric Relays


200 N. Martingale Rd., Suite 1000

Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: relays@schneider-electric.com • Web site: www.serelays.com

ITEM # 788XBXRC-110D, 788 POWER RELAYS / DPDT, 10 AMP RATING



[SPECIFICATIONS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#) | [PRODUCT CERTIFICATIONS](#)

Specifications

Check Inventory

[Check Distributor Inventory](#)

Status

Standard

Legacy Part No.

788XBXC-110/125D

Terminal Style

Plug-in

Contact Configuration

DPDT

Thermal (Carrying) Current

10 A

Coil Resistance (Ohms)

7500 Ohm

Load Type

Standard

Contact Materials

Silver Alloy with Gold Flash

Maximum Switching Voltages

IEC: 250 VAC/28 VDC
UL: 300 VAC/30 VDC

Switching Current at Voltage (AC, Resistive)

IEC: 10 A at 250 VAC 50/60 Hz
UL: 10 A at 277 VAC 50/60 Hz

Switching Current at Voltage (DC, Resistive)	IEC: 10 A at 28 VDC UL: 10 A at 30 VDC
--	---

Switching Current at Voltage (HP)	1 at 277 VAC hp 1/3 at 120 VAC hp
-----------------------------------	--------------------------------------

Pilot Duty	B300
------------	------

Minimum Switching Requirement	10 mA at 17 VDC
-------------------------------	-----------------

Cover Options	Plain Cover
---------------	-------------

Features	Mechanical flag indicator
----------	---------------------------

California Proposition 65 Warning



WARNING: This product can expose you to chemicals including:
Substance 1: Nickel compounds, which is known to the State of California to cause cancer.
Substance 2: DIDP, which is known to the State of California to cause birth defects or other reproductive harm.
 For more information go to www.p65warnings.ca.gov

Coil Characteristics

Coil Voltage	110 VDC
--------------	---------

Operating Range - % of Nominal (AC)	85 to 110 %
-------------------------------------	-------------

Operating Range - % of Nominal (DC)	80 to 110 %
-------------------------------------	-------------

Average Consumption (DC / W)	1.40 W
------------------------------	--------

Drop-out Voltage Threshold (DC)	10 %
---------------------------------	------

Performance Characteristics

Electrical Life (UL508), Operations at Rated Current (Resistive)	100000
--	--------

Mechanical Life, Unpowered	5000000
----------------------------	---------

Operating Time (Response Time)	20 ms
--------------------------------	-------

Dielectric Strength - Between Coil and Contact (AC)	2500 V(rms)
---	-------------

Dielectric Strength - Between Poles (AC)	2000 V(rms)
--	-------------

Environment

Vibration Resistance - Operational	3 g-n at 35-150 Hz
------------------------------------	--------------------

Shock Resistance	10 g-n
------------------	--------

Degree of Protection	IP 40
Weight	83 g 2.93 oz

Product Certifications		—
Agency Approvals	UL (E164862) CSA (225619 Class 3211-07) CE RoHs	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[788XBXRC-110D](#)