



Schneider Electric Relays

200 N. Martingale Rd., Suite 1000


Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: relays@schneider-electric.com • Web site: www.serelays.com

ITEM # 841CS2-UNI, 841 CURRENT SENSING RELAYS / SPDT, 15 AMP RATING

The 841 Current Sensor Series allows the user to monitor the current of one circuit (1 to 8 amps) and switch another circuit in case of an over current or under current condition.



[SPECIFICATIONS](#) | [OUTPUT CHARACTERISTICS](#) | [INPUT CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#) | [PRODUCT CERTIFICATIONS](#)

Specifications

Check Inventory [Check Distributor Inventory](#)

Status Standard

Type of Device Current Sensor

Rated Current Load 15 A

Timing Range 0.1s to 10s

Sensing Current Range 0.2 to 2 A

California Proposition 65 Warning



WARNING: This product can expose you to chemicals including:
Substance 1: Nickel compounds, which is known to the State of California to cause cancer.
Substance 2: DIDP, which is known to the State of California to cause birth defects or other reproductive harm.
 For more information go to www.p65warnings.ca.gov

Output Characteristics

Contact Configuration	SPDT
Contact Materials	Silver Alloy
Current Rating at 240 VAC, 24 VDC	15 A
Switching Voltage	24 VDC 240 VAC, 50/60 Hz
Switching Voltage [hp]	1 hp at 240 VAC 1/2 hp at 120 VAC
Switching Voltage (Pilot Duty)	B300
Indication (LED)	Red

Input Characteristics		—
Maximum Consumption LED	1.50 VA	
Indication	Green	
Sensing Range	0.2 to 2 A	
Functions Available	A - On Delay (Power On)	
Time Scales	1	
Time Ranges Available	0 to 10 s	
Tolerance, Mechanical Setting	5 %	
Repeatability, Constant Voltage and Temperature	1 %	
Operate Time, Maximum	25 ms	
Reset Time, Maximum	20 ms	

Performance Characteristics		—
Electrical Life (UL508), Operations at Rated Current (Resistive)	100000	
Mechanical Life, Unpowered	10000000	
Dielectric Strength - Input to Contacts	2500 VAC	
Dielectric Strength - Between Open Contacts	1000 VAC	
Terminal Wire Capacity	14 AWG 2.10 mm_	

Terminal Torque (Maximum)	7.10 in lb
---------------------------	------------

Environment		—
Ambient Air Temperature around the Device - Operation	-20 to +55 °C	
Ambient Air Temperature around the Device - Storage	-30 to +70 °C	
Degree of Protection	IP 20	

Product Certifications		—
Agency Approvals	UL (E234203) CE (per IEC 61810-1) RoHs	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[841CS2-UNI](#)