



Schneider Electric Relays


200 N. Martingale Rd., Suite 1000

Schaumburg, IL 60173

Phone: 847-441-2540 • Fax: 847-881-0741

E-Mail: relays@schneider-electric.com • Web site: www.serelays.com

ITEM # W92S11D22D-12, 92 DIN & FLANGE COVER POWER RELAYS / DPDT, 30 AMP RATING (DC)



[SPECIFICATIONS](#) | [CONTACT CHARACTERISTICS](#) | [COIL CHARACTERISTICS](#) | [PERFORMANCE CHARACTERISTICS](#) | [ENVIRONMENT](#) | [PRODUCT CERTIFICATIONS](#)

Specifications

Check Inventory

[Check Distributor Inventory](#)

Status

Standard

Legacy Part No.

W92S11D22-12

Cover Style

DIN & Flange Cover

California Proposition 65 Warning



WARNING: This product can expose you to chemicals including:

Substance 1: Nickel compounds, which is known to the State of California to cause cancer.

Substance 2: DIDP, which is known to the State of California to cause birth defects or other reproductive harm.

For more information go to www.p65warnings.ca.gov

Contact Characteristics

Contact Rating

30 A

Contact Configuration

DPDT

Contact Materials	Silver Alloy
Maximum Switching Voltage (V)	300 V
Switching Current at Voltage (AC, Resistive)	3 A at 277 VAC 50/60 Hz (Normally Closed Contact) 30 A at 277 VAC 50/60 Hz (Normally Open Contact)
Switching Current at Voltage (DC, Resistive)	20 A at 28 V (Normally Open Contact) 3 A at 28 V (Normally Closed Contact)
Switching Current at Voltage (Pilot Duty)	720 VA (Normally Open Contact)
Minimum Switching Requirement	100 mA at 6 VAC/VDC (Normally Closed Contact) 500 mA at 12 VAC/VDC (Normally Open Contact)

Coil Characteristics		—
Nominal Input Voltage	12 VDC	
Coil Resistance (Ohms)	86 Ohm	
Operating Range - % of Nominal (AC)	80 to 110 %	
Operating Range - % of Nominal (DC)	80 to 110 %	
Average Consumption (AC / VA)	4 VA	
Average Consumption (DC / W)	1.70 W	
Drop-out Voltage Threshold (DC)	10 %	
Drop-out Voltage Threshold (AC)	10 %	

Performance Characteristics		—
Electrical Life (UL508), Operations at Rated Current (Resistive)	100000	
Mechanical Life, Unpowered	5000000	
Operating Time (Response Time)	15 ms	

Environment		—
Ambient Air Temperature around the Device - Storage	-40 to +85 °C	
Ambient Air Temperature around the Device - Operation	-40 to +55 °C	
Shock Resistance	10 g-n	

Product Certifications



Agency Approvals

UL
CE
CSA
RoHs

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[92S11D22D-12](#)