



High temperature thin film chip resistors

■ RGA series

AEC-Q200 Compliant

Features

- Conductive epoxy compatible
- Operating temperature up to 230°C
- Resistance tolerance: $\pm 0.1\%$, TCR: $\pm 10\text{ppm}/^\circ\text{C}$
- Thin film structure enabling low noise and anti-sulfur

Applications

- Automotive electronics
- Equipment used in high temperature
- Downhole drilling

◆ Part numbering system

RGA 2012 N - 104 - B - T1

Series code

Size: RGA1005, RGA1608, RGA2012

Temperature coefficient of resistance

Packaging quantity:
T1 (1,000pcs), T5 (5,000pcs)


Resistance tolerance

Nominal resistance value (E-24: 3digit, E-96: 4digit)

◆ Electrical Specification

Type	Power ratings	Temperature coefficient of resistance	Resistance range(Ω) Resistance tolerance		Maximum voltage	Resistance value series	Operating temperature	Packaging quantity
		(ppm/°C)	±0.1% (B)	±0.5% (D)				
RGA1005	1/32W	±10(N)	47≤R≤100k		50V	E-24, E-96	-55℃ ~ 230℃	T1 T5
		±25(P)						
RGA1608	1/16W	±10(N)	47≤R≤274k		100V			
		±25(P)	47≤R≤332k	47≤R≤360k				
RGA2012	1/10W	±10(N)	47≤R≤475k		150V			
		±25(P)	47≤R≤475k	47≤R≤1M				

◆ Dimensions



Type	Size (inch)	L	W	a	b	t
RGA1005	0402	$1.00 \pm 0.1/-0.05$	0.50 ± 0.05	0.20 ± 0.10	0.25 ± 0.05	0.35 ± 0.05
RGA1608	0603	1.60 ± 0.20	$0.80 \pm 0.25/-0.20$	0.30 ± 0.20	0.30 ± 0.20	$0.40 \pm 0.15/-0.10$
RGA2012	0805	2.00 ± 0.20	$1.25 \pm 0.25/-0.20$	0.40 ± 0.20	0.40 ± 0.20	$0.40 \pm 0.15/-0.10$

(unit : mm)

◆ Reliability specification

Test items	Condition (test methods (MIL-PRF-55342/JIS C5201-1))	Standard
Short time overload	2.5 x rated voltage,*1 5seconds	$\pm (0.1\%+0.01\Omega)$
Life (biased)	125°C, rated voltage,*1 90min on 30min off, 1000hours	$\pm (0.2\%+0.05\Omega)$
High temperature high humidity	85°C, 85%RH, 1/10 of rated power, 90min on 30min off, 1000hours	$\pm (0.2\%+0.01\Omega)$
Temperature shock	-55°C (30min) ~ 125°C (30min) 1000cycles	$\pm (0.2\%+0.01\Omega)$
High temperature exposure	155°C, no bias, 1000hours	$\pm (0.2\%+0.05\Omega)$
Vibration	Frequency 10Hz ~ 500Hz, vibration amplitude 1.5mm or acceleration 10gn test duration for each of 3 axis: 6 hours	$\pm (0.2\%+0.05\Omega)$
Resistance to soldering heat	260±5°C, 10 seconds (reflow)	$\pm (0.5\%+0.01\Omega)$

*1 Rated voltage is given by $E=\sqrt{R \times P}$

E= rated voltage (V), R=nominal resistance value(Ω), P=rated power(W)


If rated voltage exceeds maximum voltage /element, maximum voltage/element is the rated voltage.

Thin film surface mount resistors


RGA series

◆ Reliability test data


○ Biased life test




○ High temperature high humidity (biased)




○ Temperature shock



○ High temperature exposure



◆ Derating Curve



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Susumu:

[RGA1608P-100-B-T1](#) [RGA1608P-101-B-T1](#) [RGA1608P-1020-B-T1](#) [RGA1608P-1021-B-T1](#) [RGA2012P-95R3-B-T1](#)
[RGA2012P-9760-B-T1](#) [RGA2012P-9761-B-T1](#) [RGA2012P-9762-B-T1](#) [RGA2012P-9763-B-T1](#) [RGA2012P-97R6-B-T1](#)
[RGA2012P-9313-B-T1](#) [RGA2012P-93R1-B-T1](#) [RGA2012P-9530-B-T1](#) [RGA2012P-9531-B-T1](#) [RGA2012P-9532-B-](#)
[T1](#) [RGA2012P-9533-B-T1](#) [RGA2012P-912-B-T1](#) [RGA2012P-913-B-T1](#) [RGA2012P-914-B-T1](#) [RGA2012P-9310-B-T1](#)
[RGA2012P-9311-B-T1](#) [RGA2012P-9312-B-T1](#) [RGA2012P-9091-B-T1](#) [RGA2012P-9092-B-T1](#) [RGA2012P-9093-B-T1](#)
[RGA2012P-90R9-B-T1](#) [RGA2012P-910-B-T1](#) [RGA2012P-911-B-T1](#) [RGA2012P-8870-B-T1](#) [RGA2012P-8871-B-T1](#)
[RGA2012P-8872-B-T1](#) [RGA2012P-8873-B-T1](#) [RGA2012P-88R7-B-T1](#) [RGA2012P-9090-B-T1](#) [RGA2012P-84R5-B-T1](#)
[RGA2012P-8660-B-T1](#) [RGA2012P-8661-B-T1](#) [RGA2012P-8662-B-T1](#) [RGA2012P-8663-B-T1](#) [RGA2012P-86R6-B-](#)
[T1](#) [RGA2012P-8253-B-T1](#) [RGA2012P-82R5-B-T1](#) [RGA2012P-8450-B-T1](#) [RGA2012P-8451-B-T1](#) [RGA2012P-8452-](#)
[B-T1](#) [RGA2012P-8453-B-T1](#) [RGA2012P-822-B-T1](#) [RGA2012P-823-B-T1](#) [RGA2012P-824-B-T1](#) [RGA2012P-8250-B-](#)
[T1](#) [RGA2012P-8251-B-T1](#) [RGA2012P-8252-B-T1](#) [RGA2012P-8061-B-T1](#) [RGA2012P-8062-B-T1](#) [RGA2012P-8063-B-](#)
[T1](#) [RGA2012P-80R6-B-T1](#) [RGA2012P-820-B-T1](#) [RGA2012P-821-B-T1](#) [RGA2012P-7870-B-T1](#) [RGA2012P-7871-B-](#)
[T1](#) [RGA2012P-7872-B-T1](#) [RGA2012P-7873-B-T1](#) [RGA2012P-78R7-B-T1](#) [RGA2012P-8060-B-T1](#) [RGA2012P-754-B-](#)
[T1](#) [RGA2012P-7680-B-T1](#) [RGA2012P-7681-B-T1](#) [RGA2012P-7682-B-T1](#) [RGA2012P-7683-B-T1](#) [RGA2012P-76R8-](#)
[B-T1](#) [RGA2012P-7323-B-T1](#) [RGA2012P-73R2-B-T1](#) [RGA2012P-750-B-T1](#) [RGA2012P-751-B-T1](#) [RGA2012P-752-B-](#)
[T1](#) [RGA2012P-753-B-T1](#) [RGA2012P-7152-B-T1](#) [RGA2012P-7153-B-T1](#) [RGA2012P-71R5-B-T1](#) [RGA2012P-7320-B-](#)
[T1](#) [RGA2012P-7321-B-T1](#) [RGA2012P-7322-B-T1](#) [RGA2012P-6981-B-T1](#) [RGA2012P-6982-B-T1](#) [RGA2012P-6983-B-](#)
[T1](#) [RGA2012P-69R8-B-T1](#) [RGA2012P-7150-B-T1](#) [RGA2012P-7151-B-T1](#) [RGA2012P-681-B-T1](#) [RGA2012P-682-B-](#)
[T1](#) [RGA2012P-683-B-T1](#) [RGA2012P-684-B-T1](#) [RGA2012P-68R1-B-T1](#) [RGA2012P-6980-B-T1](#) [RGA2012P-66R5-B-](#)
[T1](#) [RGA2012P-680-B-T1](#) [RGA2012P-6810-B-T1](#) [RGA2012P-6811-B-T1](#) [RGA2012P-6812-B-T1](#) [RGA2012P-6813-B-](#)
[T1](#)