



NOTES:

1. ORIENTATION OF  $\varnothing 0.110$  HOLES TO TERMINALS IS NOT CONTROLLED.
2. HARDWARE IS ONLY ASSEMBLED TO FRONT OF JACK. THE REST OF THE HARDWARE IS SHIPPED UNASSEMBLED.
3. MATERIALS:  
JACK:  
BODY - COPPER ALLOY, NICKEL PLATED  
INSERT - THERMOPLASTIC  
GROUND CLIP AND SPRINGS - SPECIAL COPPER ALLOY  
INSULATING WASHER - PHENOLIC  
CABLE CLAMP - STEEL, ELECTRO TIN  
HARDWARE:  
STRAP NUT - COPPER ALLOY, GOLD PLATED  
HEX NUT, WASHER, HANDLE - COPPER ALLOY, NICKEL PLATED  
LOCK WASHER - SPRING STEEL, NICKEL PLATED
4. SAME AS 6J1206.
5. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.														
						SIZE	WIDTH		MULT		LBS/M		TEMPER							
						FINISH						MATERIAL								
						SPEC No.						SPEC No.								
						FIRST USED ON				SCALE 2:1		Switchcraft®								
						DATE DRAWN	BY	CHKD		APVD										
A	28374	03/25/21	PC	TJK		03/16/21	PC	PC 03/16/21		TJK 03/16/21		SHEET 1 OF 1								
REV	ECO NUMBER	DATE	BY	APVD		NAME THICK PANEL JAX WITH GOLD STRAP NUT, RoHS										PART No. 157G				REV A
REVISIONS						DO NOT SCALE DRAWING														

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[157G](#)