

6

5

4

3

2

.100 DIA.  
2.54  $\phi$

1.190  
30.22

INCH  
MM

THIRD ANGLE  
PROJECTION

.138  
3.50

.328  
8.33

.502  
12.75

1.000  
25.4

.150  
3.81

THROW  
EITHER DIRECTION

.200  
5.08

.020  
0.51

.187  
4.75

.030  
0.76

.307  
7.79

.453  
11.50

.082  
2.08

SLOT

.070  
1.79

X

.036  
0.91

.181  
4.59

.800  
20.32

.400  
10.16

.125  
3.17

.203  
5.15

NOTES:

1. ELECTRICAL RATING:  
0.5 AMP 125 VAC/DC
2. MATERIALS AND FINISHES:  
HOUSING- STEEL - ZINC PLATED  
BUTTON & BOARD - THERMOPLASTIC  
TERMINALS - COPPER ALLOY  
SILVER PLATED  
CONTACT SLIDERS - BI-METAL  
SILVER ON COPPER ALLOY  
DUST SHIM - THERMOPLASTIC
3. THIS PRODUCT IS RoHS  
COMPLIANT.

CUSTOMER DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT, INC., AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSE ONLY.		FINISH	
UNLESS OTHERWISE SPECIFIED:		DRAWN BY RUMSEY	
1. DECIMAL DIMENSIONS <del>IN INCHES</del>		DATE 11-5-74	
2. FRACTIONAL DIMENSIONS <del>IN INCHES</del>		CHECKED BY RUC	
3. ANGLES <del>IN DEGREES</del>		DATE 3/4/13	
4. ALL DIA'S CONCENTRIC WITHIN .005		APPROVED BY RUC	
5. ALL DIMENSIONS IN INCHES & MM		DATE 9/4/18	
6. FOR THREADS USE UNIFIED PLUG AND RING GAGES ONLY.		SCALE 4:1	
7. REMOVE ALL BURRS.		FIRST USED ON	
8. PART TO BE FABRICATED AS SPECIFIED. MAKE NO DIMENSIONAL ALLOWANCES FOR APPLIED FINISHES, I.E., PLATING, PAINTING, ETC.		NAME SLIDE SWITCH, RoHS	
9. HOLES ON SAME CENTERLINE MUST BE ALIGNED WITHIN .005		PART NO. 56313L2X	
DO NOT SCALE DRAWING		SHEET 1 OF 1	
		ISSUE A	



SCHEMATIC

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[56313L2](#) [56313L2X](#)