

NOTES:


1. MATERIALS:  
FRONT PANEL - ALUMINUM ALLOY, BLUE ANODIZED  
REAR COVER - ALUMINUM ALLOY, UNPLATED  
XLR CONNECTORS:  
HOUSING - ZINC DYCAST  
CONTACTS - COPPER ALLOY, SILVER PLATED
- DB25 CONNECTORS:  
BODY - STEEL, NICKEL PLATED  
CONTACTS - COPPER ALLOY, SILVER PLATED  
CONNECTOR INSULATOR - BLACK THERMOPLASTIC  
PCB - FR4
2. THIS PRODUCT IS RoHS COMPLIANT

DETAIL C  
SCALE 3 : 1

DB25F AND XLRM WIRING CHART				
XLR (CHANNEL)	XLR (DESC.)	PIN 2	PIN 3	PIN 1
1	XLRM	24	12	25
2	XLRM	10	23	11
3	XLRM	21	9	22
4	XLRM	7	20	8
5	XLRM	18	6	19
6	XLRM	4	17	5
7	XLRM	15	3	16
8	XLRM	1	14	2

WIRING REPEATED FOR CHANNELS "9-16" & "17-36"

CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.												
						UNLESS OTHERWISE SPECIFIED  1. ALL DIMENSIONS IN INCHES [mm]  - TWO PLACE DECIMALS    ±0.02 [0.5]  - THREE PLACE DECIMALS   ±0.005 [0.13]	SIZE		WIDTH		MULT		LBS/M		TEMPER			
							FINISH SPEC No.						MATERIAL SPEC No.					
							FIRST USED ON				SCALE 3:5							
							DATE DRAWN 6/21/16	BY AB	CHKD AB 6/21/16	APVD TJK 10-3-16	SHEET    1    OF    1							
A	27772	9-14-16	TO	TJK			NAME IO PANEL, ALL FRONT, 24 MALE QG TO 3 DB25, RoHS						PART No. AP24MX3DB25F				REV A	
REV	ECO NUMBER	DATE	BY	APVD			DO NOT SCALE DRAWING											
REVISIONS																		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[AP24MX3DB25F](#)