





NOTES:

- DIN 1.0/2.3 FEED-THRU CONNECTOR SPECIFICATIONS:
IMPEDANCE: 75 Ω
FREQUENCY RANGE: 0-3 GHz
W/S VOLTAGE: 250 Vrms
INSULATION RESISTANCE: 1 G Ω min.
CONTACT RESISTANCE: 30 m Ω max. (Initial)
INSERTION LOSS: -1.0 dB max.
RETURN LOSS: per SMPTE 424 M
OPERATING TEMPERATURE: -40°C to +85°C
LIFE: 500 cycles min.
- MATERIALS:
FRONT PANEL - ALUMINUM, ANODIZED
INSERT - THERMOPLASTIC, BLACK
CONNECTOR SHELL - COPPER ALLOY, NICKEL PLATED
CONTACT: COPPER ALLOY, GOLD PLATED
INSULATORS: THERMOPLASTIC
HORIZONTAL MARKING STRIP - THERMOPLASTIC, WHITE
DESIGNATION STRIP COVER - THERMOPLASTIC, CLEAR
KEY-HOLE CLIPS - THERMOPLASTIC
SCREWS - STEEL, ZINC OR NICKEL PLATED
- SUPPLIED WITH (4) #12-24 MOUNTING SCREWS.
- DIMENSIONS SHOWN FOR REFERENCE ONLY
- THIS PRODUCT IS RoHS COMPLIANT



CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.02 - THREE PLACE DECIMALS ±0.005	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE	WIDTH		MULT	LBS/M	TEMPER	
						FINISH					MATERIAL	
						SPEC No.					SPEC No.	
						FIRST USED ON			SCALE		Switchcraft®	
									1:2			
A	26775	06/09/11	BL	TJK	DATE DRAWN	BY	CHKD	APVD		SHEET 1 OF 1		
					5/17/10	PNK	PNK	SRC				
							5/17/10	5/17/10				
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.	REV	
					DIN 1.0/2.3 FEED-THRU PATCHBAY, RoHS					DIN96K1D	A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[DIN96K1D](#)