


Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	XR and XF
Product or component type	Single-stage heavy duty screw limit switch
Device short name	XR2
Product specific application	Liquid level control in pumping systems Position control of moving parts of hoisting or materials handling equipment
Material	Aluminium alloy (body housing) Plastic (cover)
Type of operator	Drive shaft, end fittings with sprocket key and washer
Maximum revolution speed	75 rpm of input drive shaft
Theoretical number of turns	3 of input drive shaft
Number of poles	1

Complementary

Mechanical durability	10000000 cycles
Number of turns	<= 6 of threaded shaft
Threaded shaft screw pitch	0.16 in (4 mm)
Operating finger radius	1.57 in (40 mm)
Length of developed helical travel	0.16 in (4 mm)
Differential snap over angle	30 ° contact actuators measured at finger
Repeat accuracy	0.02 % on the tripping point
Number of teeth	16 (pinion B) 26 (pinion C) 49 (pinion D) 59 (pinion A)
Actual number of turns	3.066 (input drive shaft)
Contacts type and composition	3 C/O
Contact operation	Snap action
[Ie] rated operational current	A300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to EN/IEC 60947-5-1
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	600 V conforming to CSA C22.2 No 14 500 V conforming to EN/IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-1
Resistance across terminals	<= 25 MOhm
Short-circuit protection	10 A cartridge fuse type gG
Connections - terminals	Screw clamp terminals, connection capacity: 2 x 1.5 mm ² with or without cable end Screw clamp terminals, connection capacity: 2 x 2.5 mm ² without cable end

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Cable entry	2 entries tapped for Pg 13 cable gland, clamping capacity: 0.35...0.47 in (9...12 mm)
Product weight	13.23 lb(US) (6 kg)

Environment

Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Shock resistance	50 gn 11 ms
Vibration resistance	> 5 gn (10...55 Hz)
IP degree of protection	IP54 conforming to EN/IEC 60529

Ordering and shipping details

Category	22449 - LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	003389110600520
Nbr. of units in pkg.	1
Package weight(Lbs)	17.98
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Will be compliant on 4Q2013
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XR2AA03K3](#)