



- NOTES:
- FOR HAND INSERTION USE SPACING 0.130 [3.30]  
FOR AUTOMATED INSERTION USE SPACING 0.135 [3.43]
  - HEX NUT AND FLAT WASHER SUPPLIED UNASSEMBLED.
  - MATERIAL:  
HOUSING, HEX NUT - COPPER ALLOY, NICKEL PLATED  
INSULATOR HOUSING - THERMOPLASTIC  
TERMINAL INSULATORS - PHENOLIC  
FLAT WASHER - STEEL, NICKEL PLATED  
PIN, SPRING, TERMINALS - COPPER ALLOY, SILVER PLATED
  - IT IS RECOMMENDED THAT THE JACK MOUNTING NUT BE TIGHTENED SNUG BY HAND BEFORE APPLYING A FINAL TIGHTENING TORQUE OF 8-10 IN-LBS USING HAND TOOLS ONLY. POWER DRIVER OR IMPACT DRIVERS ARE NOT RECOMMENDED.
  - THESE PRODUCTS ARE RoHS COMPLIANT

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS    ±0.02   [0.5]</div> <div>- THREE PLACE DECIMALS   ±0.005   [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.							
						SIZE	WIDTH		MULT	LBS/M	TEMPER		
						FINISH SPEC No.				MATERIAL SPEC No.			
						FIRST USED ON			SCALE 2:1		Switchcraft®		
						DATE DRAWN 4-16-2020	BY SRC	CHKD TJK 05-12-22	APVD TJK 05-12-22				
A	28408	03-08-22	PC	TJK									
REV	ECO NUMBER	DATE	BY	APVD									
REVISIONS					DO NOT SCALE DRAWING	NAME HIGH TEMP POWER JACKS LONG BUSHING RIGHT-ANGLE LOW PROFILE, RoHS					PART No. L7__RAHLP SERIES		REV A

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Switchcraft:

[L712RAHLP](#) [L721RAHLP](#) [L722RAHLP](#)