

XRBA43200

standard duty screw limit switch - bare drive
shaft - 4 C/O - 46:1 - left-hand

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	XR and XF
Product or component type	Standard duty screw limit switch
Device short name	XRBA
Product specific application	Position control of moving parts of hoisting or materials handling equipment Liquid level control in pumping systems
Material	Aluminium alloy (body housing) Aluminium alloy (cover) Stainless steel (input drive shaft)
Type of operator	Bare drive shaft
Operating position	Left-hand side
Maximum revolution speed	1000 rpm of input drive shaft
Number of poles	1
Contact operation	Snap action
[Ie] rated operational current	A300, AC-15 (Ue = 240 V, Ie = 3 A) conforming to EN/IEC 60947-5-1 Q300, DC-13 (Ue = 250 V, Ie = 0.27 A) conforming to EN/IEC 60947-5-1
Product compatibility	XRBAZ900

Complementary

Reduction ratio	46:1
Operating torque	44.25 lbf.in (5 N.m) at 20 °C
Mechanical durability	15000000 cycles
Contacts type and composition	4 C/O
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	250 V conforming to EN/IEC 60947-1
[Uimp] rated impulse withstand voltage	6 kV conforming to EN/IEC 60947-1
Resistance across terminals	<= 25 MOhm
Short-circuit protection	10 A cartridge fuse type gG
Connections - terminals	Captive screw clamp terminals, connection capacity: 2 x 1.5 mm ² with cable end

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Electrical durability	500000 cycles AC-15 50/60 Hz inductive at 12 V, 65 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz inductive at 127 V, 450 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz inductive at 220 V, 530 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz inductive at 24 V, 108 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz inductive at 48 V, 216 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz resistive at 12 V, 18 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz resistive at 127 V, 165 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz resistive at 220 V, 220 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz resistive at 24 V, 35 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles AC-15 50/60 Hz resistive at 48 V, 700 VA, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 inductive at 110 V, 130 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 inductive at 12 V, 55 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 inductive at 220 V, 135 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 inductive at 24 V, 84 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 inductive at 48 V, 110 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 resistive at 110 V, 65 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 resistive at 12 V, 27 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 resistive at 220 V, 67 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 resistive at 24 V, 39 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1 500000 cycles DC-13 resistive at 48 V, 50 W, operating rate 3600 cyc/h, load factor 0.5 EN/IEC 60947-5-1
Adaptation for potentiometer	With, ratio 1.5 (1.333)
Cable entry	1 entry tapped for Pg 16 cable gland, clamping capacity: 0.39...0.55 in (10...14 mm) 1 entry tapped for Pg 9 cable gland, clamping capacity: 0.2...0.31 in (5...8 mm)
Product weight	3.31 lb(US) (1.5 kg)

Environment

Standards	EN/IEC 60947-5-1
Protective treatment	TC
Ambient air temperature for operation	-13...158 °F (-25...70 °C)
Ambient air temperature for storage	-40...158 °F (-40...70 °C)
Shock resistance	80 gn 11 ms
Vibration resistance	> 5 gn (10...60 Hz)
IP degree of protection	IP55 conforming to EN/IEC 60529 IP557 conforming to NF C 20-010

Ordering and shipping details

Category	22449 - LIMIT SWITCHES,ACCESSORIES
Discount Schedule	T
GTIN	00785901512417
Nbr. of units in pkg.	1
Package weight(Lbs)	5.0000000000000003E-2
Returnability	N
Country of origin	FR

Offer Sustainability

California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Diisononyl phthalate (DINP), which is known to the State of California to cause cancer, and
- - - - - Substance 2	Di-isodecyl phthalate (DIDP), which is known to the State of California to cause birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Contractual warranty

Warranty period	18 months
-----------------	-----------

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[XRBA43200](#)