










NOTES:

- MATERIALS:**
HOUSING - THERMOPLASTIC, BLACK
SHIELD - COPPER ALLOY, NICKEL PLATED
CONTACTS - COPPER ALLOY, GOLD PLATED OVER NICKEL UNDERPLATING
- ELECTRICAL CHARACTERISTICS:**
CONTACT RESISTANCE - 20mΩ MAX
INSULATION RESISTANCE - 500MΩ MIN
CURRENT RATING - 1.5AMP MAX @ 120V AC
DIELECTRIC WITHSTAND VOLTAGE - 1000V RMS FOR 1 MINUTE
- OPERATING TEMPERATURE:** -40°C TO +85°C
LIFECYCLE - 500 MATE/UNMATE CYCLES
- THIS PART IS RoHS COMPLIANT.**



CUSTOMER DRAWING

					THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					SIZE	WIDTH	MULT	LBS/M	TEMPER
					FINISH SPEC No.			MATERIAL SPEC No.	
					FIRST USED ON			SCALE 3:1	
					DATE DRAWN 8/25/22	BY TS	CHKD TS	APVD TS	
					NAME VERTICAL SHIELDED RJ45, RoHS			PART No. PCRJ45AUE	
								SHEET 1 OF 1	
								REV A	

SolidWorks CAD File



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[PCRJ45AUE](#)