










NOTES:

1. MATERIALS:
HOUSING - THERMOPLASTIC, BLUE
SHELL - COPPER ALLOY, NICKEL PLATED
TERMINALS - COPPER ALLOY, GOLD PLATED ON CONTACT AREA
TIN PLATED ON SOLDER TAIL
2. ELECTRICAL CHARACTERISTICS:
CONTACT RESISTANCE - 30mΩ MAX
INSULATION RESISTANCE - 100MΩ MIN AT 500V DC
CURRENT RATING - 1.5AMP MAX
DIELECTRIC WITHSTAND VOLTAGE - 500V AC FOR 1 MINUTE
3. OPERATING TEMPERATURE: -30°C TO +85°C
4. THIS PART IS RoHS COMPLIANT.

CUSTOMER DRAWING

						THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.						
						SIZE		WIDTH	MULT	LBS/M	TEMPER	
						FINISH SPEC No.				MATERIAL SPEC No.		
						FIRST USED ON			SCALE 4:1			
						DATE DRAWN 8/25/22	BY TS	CHKD TS	APVD TS	Switchcraft® SHEET 1 OF 1		
						NAME RIGHT ANGLE SMT USB TYPE-A 3.0, RoHS						
						PART No. RAHUA30E					REV A	
						UNLESS OTHERWISE SPECIFIED						DO NOT SCALE DRAWING
						1. ALL DIMENSIONS IN INCHES [mm]						
						- TWO PLACE DECIMALS ±0.02 [0.5]						
						- THREE PLACE DECIMALS ±0.008 [0.20]						
A	28548	10/26/22	PC	TJK								
REV	ECO NUMBER	DATE	BY	APVD								
REVISIONS												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAHUA30E](#)