



- NOTES:**
- MATERIALS:**
HOUSING - THERMOPLASTIC, BLACK
TERMINALS - COPPER ALLOY, GOLD AND TIN PLATED
SHELL - COPPER ALLOY, NICKEL PLATED
 - ELECTRICAL CHARACTERISTICS:**
CONTACT RESISTANCE - 30m OHM MAX
INSULATION RESISTANCE - 1000M OHM MIN @ 500V DC
VOLTAGE AND CURRENT RATING - 1.5A @ 250V AC MIN
DIELECTRIC WITHSTAND VOLTAGE - 750V AC RMS FOR 1MINUTE
 - PRODUCT LIFECYCLE:** 1500 INSERTION/WIDTHDRAWAL CYCLES.
 - THIS PART IS RoHS COMPLIANT.**

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH SPEC No.						MATERIAL SPEC No.					
						FIRST USED ON				SCALE		<div>Switchcraft®</div>					
						-				3:1							
						DATE DRAWN	BY	CHKD		APVD		<div>SHEET 1 OF 1</div>					
						8/24/22	TS	TS		TS							
								10/27/22		10/27/22		<div>PART No. RAHUB20</div> <div>REV A</div>					
A	28548	10/26/22	PC	TJK			NAME RIGHT ANGLE SMT TYPE-B USB 2.0, RoHS										
REV	ECO NUMBER	DATE	BY	APVD													
REVISIONS					DO NOT SCALE DRAWING												

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[RAHUB20](#)