


NOTES:

1. MATERIALS:
 BUSHING - COPPER ALLOY, NICKEL PLATED
 TIP & RING TERMINALS / SPRINGS - COPPER ALLOY
 SLEEVE TERMINAL - COPPER ALLOY, TIN COATED
 INSULATORS - PHENOLIC
 JACK WASHER - COPPER ALLOY, NICKEL PLATED
 HEX NUT - COPPER ALLOY, NICKEL PLATED
 MOUNTING WASHER - STEEL, NICKEL PLATED

2. THIS PRODUCT IS RoHS COMPLIANT.



SCHEMATIC

★ STAR SYMBOL DENOTES CRITICAL DIMENSION

UNLESS OTHERWISE SPECIFIED

1. ALL DIMENSIONS IN INCHES
 - TWO PLACE DECIMALS ± 0.01
 - THREE PLACE DECIMALS ± 0.005
 - ANGLES $\pm 1^\circ$
 - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.

2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ± 0.002

3. REMOVE ALL BURRS

DO NOT SCALE DRAWING

THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.

SIZE	WIDTH	MULT	LBS/M	TEMPER
------	-------	------	-------	--------

FINISH	MATERIAL
SPEC No.	SPEC No.

FIRST USED ON	SCALE
	2:1

DATE DRAWN	BY	CHKD	APVD
4-21-64	JR	CK 5-27-64	LG 6-2-64

Switchcraft®

SHEET | OF |

NAME	PART No.	REV
3 CONDUCTOR, Ø 0.210 OPEN CIRCUIT JAX, RoHS	S12B	A

REV	ECO NUMBER	DATE	BY	APVD
A	23280	3-1-00	JL	DK
REVISIONS				

Pro/Engineer CAD File

A

ROUTING 146 112 105

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[S12B](#)