


SCHEMATIC

2-B
LOCKING

2-B
LOCKING

FRAME






KNURLED NUT
SEE NOTE 3

30° REF

30° REF

NOTES:

- MATERIALS:
FRAME - STEEL, NICKEL PLATED
SPRINGS - SPRING TEMPERED, NICKEL SILVER
BUSHING & SHAFT - BRASS, NICKEL PLATED
INSULATION - PHENOLIC
CONTACTS - FINE SILVER
SCREWS - STEEL, NICKEL PLATED
SHAFT INSULATOR - NYLON
TUBING - THERMOPLASTIC
KNURLED NUT - BRASS, NICKEL PLATED
- ELECTRICAL CHARACTERISTICS:
- CONTACT RESISTANCE: 20 MILLIOHMS MAX
- CONTACT RATING: 3A, 300W MAX AC NON-INDUCTIVE LOAD
- LEAKAGE RESISTANCE: 1000 MEGAOHMS OR GREATER
- DIELECTRIC STRENGTH: 250 VDC
- HARDWARE SHIPPED UNASSEMBLED.
- THIS PRODUCT IS RoHS COMPLIANT.



CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.									
						SIZE	WIDTH		MULT		LBS/M		TEMPER		
						FINISH						MATERIAL			
						SPEC No.						SPEC No.			
						FIRST USED ON				SCALE 2:1		<div>Switchcraft®</div>			
						DATE DRAWN	BY	CHKD		APVD					
A	25997	11/07/08	PC	TJK		03/10/10	RS	RS		TJK		SHEET 1 OF 1			
								03/10/10		06/16/20					
REV	ECO NUMBER	DATE	BY	APVD		NAME RIGHT-ANGLE LEVER SWITCH 3 POSITION LOCKING, RoHS						PART No.		REV	
REVISIONS					DO NOT SCALE DRAWING							12015X		A	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[12015X](#)