



B

TS PLUG AND TS PLUG WIRING CHART							
JACKET COLOR	H.S. TUBING MARKING	END "A" TS PLUG			END "B" TS PLUG		
		RED	BLACK	BARE	RED	BLACK	BARE
BROWN	CHANNEL 1	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
RED	CHANNEL 2	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
ORANGE	CHANNEL 3	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
YELLOW	CHANNEL 4	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
GREEN	CHANNEL 5	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
BLUE	CHANNEL 6	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
PURPLE	CHANNEL 7	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE
GRAY	CHANNEL 8	TIP	N.C.	SLEEVE	TIP	N.C.	SLEEVE

PART NUMBER	CABLE LENGTH "X"
TS05TS	5.00 FT +/- 1.50 IN
TS10TS	10.00 FT +/- 1.50 IN

CUSTOMER DRAWING

NOTES:

1. CABLE BREAKOUT LENGTH IS 18.00 +/- 0.75 IN.
- B

2. CABLE IS SHIPPED COILED AND PACKAGED IN A BAG.
3. MATERIALS:
TS PLUG:
SOLDER AND CLAMP TERMINAL - COPPER ALLOY, TIN PLATED
TIP ROD, PLUG BODY AND HANDLE- COPPER ALLOY, NICKEL PLATED
TUBULAR INSULATOR - MYLAR
INSULATING WASHERS - THERMOPLASTIC
HEAT SHRINK TUBING - THERMOPLASTIC
CABLE - COPPER, THERMOPLASTIC
4. THIS PRODUCT IS RoHS COMPLIANT.

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES</div> <div>- TWO PLACE DECIMALS ±0.02</div> <div>- THREE PLACE DECIMALS ±0.005</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.											
						SIZE	WIDTH		MULT		LBS/M		TEMPER				
						FINISH SPEC No.						MATERIAL SPEC No.					
						FIRST USED ON				SCALE 1:2		<div>Switchcraft®</div>					
B	26637	10/11/10	RS	TJK		DATE DRAWN	BY	CHKD		APVD							
A	25983	10/30/08	RS	TJK		4/14/08	JGK	RS 1/3/11		TJK 1/4/11							
REV	ECO NUMBER	DATE	BY	APVD		NAME						PART No.		REV			
REVISIONS					DO NOT SCALE DRAWING		TS PLUG TO TS PLUG, RoHS						TS__TS		B		

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[TS05TS](#) [TS10TS](#)