



DIMENSIONS SHOWN FOR REFERENCE ONLY



NOTES:

1. MEETS SMPTE 2082-1
CHARACTERISTIC IMPEDANCE: 75 OHMS
CONTACT RESISTANCE: 50 MILLIOHMS MAX.
2. MATERIAL:
BODY: COPPER ALLOY, NICKEL PLATED.
CONTACT PIN: COPPER ALLOY, GOLD PLATED.
SPRING: BERYLLIUM COPPER, NICKEL PLATED.
TINE CONTACT: BERYLLIUM COPPER, GOLD PLATED.
INSULATOR: TEFLON
FERRULE: COPPER ALLOY, NICKEL PLATED.
3. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					UNLESS OTHERWISE SPECIFIED 1. ALL DIMENSIONS IN INCHES [mm] - TWO PLACE DECIMALS ±0.02 [0.5] - THREE PLACE DECIMALS ±0.005 [0.13]	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.													
						SIZE	WIDTH		MULT		LBS/M		TEMPER						
						FINISH					MATERIAL								
						SPEC No.					SPEC No.								
						FIRST USED ON				SCALE		Switchcraft®							
								4:1											
A	28195	08/29/19	PC	TJK		DATE DRAWN	BY	CHKD		APVD									
					04/05/17	PNK	04/05/17 PNK		04/05/17 SRC										
REV	ECO NUMBER	DATE	BY	APVD	NAME					PART No.					REV				
REVISIONS					DO NOT SCALE DRAWING					UHD DIN 1.0/2.3 PLUG 75 OHMS, 4505R, RoHS					UHDDIN05 A				

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft:](#)

[UHDDIN05](#)