



NOTES:


1. ALL PARTS TO BE BULK PACKED.
2. CONTACTS ASSEMBLED INTO CONNECTOR.
3. BACK WELL FILLED WITH EPOXY.
4. ALL DIMENSIONS ARE REFERENCE ONLY EXCEPT WHERE NOTED WITH A TOLERANCE. DIMENSIONS IN BRACKETS [] ARE METRIC.
5. PC TAIL LENGTH OPTIONS:
 - STANDARD (SHORT) TAIL = 0.107in [W4281-1XSG-3ES]
 - INTERMEDIATE = 0.202in [W4291-1XSG-3ES]
 - LONG = 0.267in [W4292-1XSG-3ES]




FACE VIEW
W4281-10SG-3ES
10-POS.




FACE VIEW
W4281-11SG-3ES
11-POS.






FACE VIEW
W4281-12SG-3ES
12-POS.



PC TAIL LAYOUT



**RECOMMENDED
PANEL CUTOUT**
STANDARD MULTI-CON-X



PC TAIL VIEW
W4281-10SG-3ES - 10-POS. (11&12 CLOSED)
W4281-11SG-3ES - 11-POS. (12 CLOSED)
W4281-12SG-3ES - 12-POS. (ALL OPEN)

CUSTOMER APPROVAL		
THIS DOCUMENT CONTAINS CONFIDENTIAL INFORMATION PROPRIETARY TO CONXALL CORPORATION. ANY REPRODUCTION, DISCLOSURE, OR USE OF THIS DOCUMENT /INFORMATION IS EXPRESSLY PROHIBITED UNLESS AUTHORIZED IN WRITING BY CONXALL CORPORATION.		
APPROVED BY: _____		
DATE: _____		

A	PAK	09/12/19	DRAWING CREATED AND RELEASED PER DOR 10-2523JS-1	
REV.	INIT.	DATE	DESCRIPTION	
			ORIG. DRAWN BY: PAK	DATE: 10/03/14
			CHECKED BY:	
			APPROVED BY:	TITLE: PANEL SOCKET, W/ EPOXY
				12-POS., #20 PC TAIL, SHORT (STD.)
			SCALE NTS	SIZE B
				SHEET 1 OF 1
			►	Critical Characteristic Flag per Spec. XXXX
			FILE: W4281-1XSG-3ES	DIRECTORY: SLW
			PART NUMBER: W4281-1XSG-3ES	
			REV A	

CONXALL
601 E. WILDWOOD VILLA PARK, IL 60181

TITLE: PANEL SOCKET, W/ EPOXY
12-POS., #20 PC TAIL, SHORT (STD.)
MULTI-CON-X, E-KEY, WEATHER RESISTANT
CUSTOMER: STANDARD PRODUCT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Switchcraft](#):

[W4281-12SG-3ES](#) [W4281-11SG-3ES](#) [W4281-10SG-3ES](#)