

1A, 50V - 600V Glass Passivated Fast Recovery Rectifiers

FEATURES

- High efficiency, Low VF
- High current capability
- High reliability
- High surge current capability
- Compliant to RoHS Directive 2011/65/EU and in accordance to WEEE 2002/96/EC
- Halogen-free according to IEC 61249-2-21 definition



MECHANICAL DATA

Case: DO-204AL (DO-41)

Molding compound, UL flammability classification rating 94V-0

Part No. with suffix "H" means AEC-Q101 qualified

Packing code with suffix "G" means green compound (halogen-free)

Terminal: Pure tin plated leads, solderable per JESD22-B102

Meet JESD 201 class 2 whisker test

Weight: 0.33 g (approximately)

DO-204AL (DO-41)

MAXIMUM RATINGS AND ELECTRICAL CHARACTERISTICS (T _A =25°C unless otherwise noted)							
PARAMETER	SYMBOL	1N 4933G	1N 4934G	1N 4935G	1N 4936G	1N 4937G	UNIT
Maximum repetitive peak reverse voltage	V _{RRM}	50	100	200	400	600	V
Maximum RMS voltage	V _{RMS}	35	70	140	280	420	V
Maximum DC blocking voltage	V _{DC}	50	100	200	400	600	V
Maximum average forward rectified current	I _{F(AV)}	1.0					A
Peak forward surge current, 8.3 ms single half sine-wave superimposed on rated load	I _{FSM}	30					A
Maximum instantaneous forward voltage (Note 1) @ 1 A	V _F	1.2					V
Maximum reverse current @ rated VR T _J =25 °C T _J =125 °C	I _R	5 150					μA
Maximum reverse recovery time (Note 2)	t _{rr}	200					ns
Typical junction capacitance (Note 3)	C _J	10					pF
Typical thermal resistance	R _{θJA}	65					°C/W
Operating junction temperature range	T _J	- 55 to +150					°C
Storage temperature range	T _{STG}	- 55 to +150					°C

Note1: Pulse Test with PW=300μs, 1% Duty Cycle

Note2: Reverse Recovery Test Conditions: I_F=0.5A, I_R=1.0A, IRR=0.25A

Note3: Measured at 1 MHz and Applied Reverse Voltage of 4.0V D.C.

ORDERING INFORMATION					
PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	PACKAGE	PACKING
1N493xG (Note 1)	H	A0	G	DO-41	3,000 / Ammo box (52mm taping)
		R0		DO-41	5,000 / 13" Paper reel
		R1		DO-41	5,000 / 13" Paper reel (Reverse)
		B0		DO-41	1,000 / Bulk packing

Note 1: "x" defines voltage from 50V (1N4933G) to 600V (1N4937G)

EXAMPLE					
PREFERRED PART NO.	PART NO.	PART NO. SUFFIX	PACKING CODE	PACKING CODE SUFFIX	DESCRIPTION
1N4937GHA0G	1N4937G	H	A0	G	AEC-Q101 qualified Green compound

RATINGS AND CHARACTERISTICS CURVES

(T_A=25°C unless otherwise noted)

FIG.1- MAXMUM FORWARD CURRENT DERATING CURVE




FIG. 2- TYPICAL REVERSE CHARACTERISTICS




FIG. 3- MAXIMUM NON-REPETITIVE PEAK FORWARD SURGE CURRENT




FIG. 4- TYPICAL FORWARD CHARACTERISTICS




FIG. 5- TYPICAL JUNCTION CAPACITANCE






FIG.6- REVERSE RECOVERY TIME CHARACTERISTIC AND TEST CIRCUIT DIAGRAM



PACKAGE OUTLINE DIMENSIONS
DO-204AL (DO-41)



DIM.	Unit (mm)		Unit (inch)	
	Min	Max	Min	Max
A	2.00	2.70	0.079	0.106
B	0.71	0.86	0.028	0.034
C	25.40	-	1.000	-
D	4.20	5.20	0.165	0.205
E	25.40	-	1.000	-

MARKING DIAGRAM



P/N = Specific Device Code
 G = Green Compound
 YWW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[1N4933G](#) [1N4934G](#) [1N4935G](#) [1N4936G](#) [1N4937G](#) [1N4935G R0](#) [1N4937G R0](#) [1N4933G R0](#) [1N4936G R0](#)
[1N4934G R0](#) [1N4934G R0G](#) [1N4936GHR0G](#) [1N4935GHR0G](#) [1N4937GHR0G](#) [1N4936GHR0](#) [1N4933GHR0G](#)
[1N4933G R0G](#) [1N4934GHR0G](#) [1N4937G R0G](#) [1N4936G R0G](#) [1N4935G R0G](#) [1N4936G A0G](#) [1N4937G A0G](#)
[1N4936GHA0G](#)