

3W, 11V - 200V Surface Mount Silicon Zener Diode

FEATURES

- AEC-Q101 qualified
- Photo Glass passivated chip junction
- Ideal for automated placement
- Low inductance
- Moisture sensitivity level: level 1, per J-STD-020
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21

APPLICATIONS

- Voltage regulating
- Reference voltage
- Protection circuit

MECHANICAL DATA

- Case: DO-214AA (SMB)
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: Indicated by cathode band
- Weight: 0.100g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
V_Z	11 - 200	V
Test current I_{ZT}	1.9 - 34.1	mA
P_{tot}	3	W
$T_{J\ MAX}$	175	°C
Package	DO-214AA (SMB)	
Configuration	Single die	



DO-214AA (SMB)



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	VALUE	UNIT
DC power dissipation at $T_L = 75^\circ\text{C}$, measure at zero lead length (Note 1) derate above 75°C	P_{tot}	3	W
Junction temperature	T_J	-55 to +175	°C
Storage temperature	T_{STG}	-55 to +175	°C

Note:

1. Mounted on Cu-Pad size 10mm x 10mm on PCB

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	21	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	59	°C/W
Junction-to-case thermal resistance	$R_{\theta JC}$	23	°C/W

Thermal Performance Note: Units mounted on PCB (10mm x 10mm Cu pad test board)

ELECTRICAL SPECIFICATIONS (TA = 25°C unless otherwise noted)

Device (Note 1)	Device Marking Code	Nominal Zener Voltage			Test current	Zener Impedance (Note 3)			Leakage Current		Maximum DC Zener Current	
		V _Z @I _Z				I _{ZT}	Z _{ZT} @ I _{ZT}		Z _{ZK} @I _{ZK}			I _R @V _R
		V				mA	Ω	Ω	mA	μA		V
		Min	Nom (Note 2)	Max								
1PGSMB5926H	P926B	10.45	11	11.55	34.1	5.5	550	0.25	1	8.4	136	
1PGSMB5927H	P927B	11.40	12	12.60	31.2	6.5	550	0.25	1	9.1	125	
1PGSMB5928H	P928B	12.35	13	13.65	28.8	7.0	550	0.25	1	9.9	115	
1PGSMB5929H	P929B	14.25	15	15.75	25.0	9.0	600	0.25	1	11.4	100	
1PGSMB5930H	P930B	15.20	16	16.80	23.4	10.0	600	0.25	1	12.2	94	
1PGSMB5931H	P931B	17.10	18	18.90	20.8	12.0	650	0.25	1	13.7	83	
1PGSMB5932H	P932B	19.00	20	21.00	18.7	14.0	650	0.25	1	15.2	75	
1PGSMB5933H	P933B	20.90	22	23.10	17.0	17.5	650	0.25	1	16.7	68	
1PGSMB5934H	P934B	22.80	24	25.20	15.6	19	700	0.25	1	18.2	63	
1PGSMB5935H	P935B	25.65	27	28.35	13.9	23	700	0.25	1	20.6	56	
1PGSMB5936H	P936B	28.50	30	31.50	12.5	26	750	0.25	1	22.8	50	
1PGSMB5937H	P937B	31.35	33	34.65	11.4	33	800	0.25	1	25.1	45	
1PGSMB5938H	P938B	34.20	36	37.80	10.4	38	850	0.25	1	27.4	42	
1PGSMB5939H	P939B	37.05	39	40.95	9.6	45	900	0.25	1	29.7	38	
1PGSMB5940H	P940B	40.85	43	45.15	8.7	53	950	0.25	1	32.7	35	
1PGSMB5941H	P941B	44.65	47	49.35	8.0	67	1000	0.25	1	35.8	32	
1PGSMB5942H	P942B	48.45	51	53.55	7.3	70	1100	0.25	1	38.8	29	
1PGSMB5943H	P943B	53.20	56	58.80	6.7	86	1300	0.25	1	42.6	27	
1PGSMB5944H	P944B	58.90	62	65.10	6.0	100	1500	0.25	1	47.1	24	
1PGSMB5945H	P945B	64.60	68	71.40	5.5	120	1700	0.25	1	51.7	22	
1PGSMB5946H	P946B	71.25	75	78.75	5.0	140	2000	0.25	1	56.0	20	
1PGSMB5947H	P947B	77.90	82	86.10	4.6	160	2500	0.25	1	62.2	18	
1PGSMB5948H	P948B	86.45	91	95.55	4.1	200	3000	0.25	1	69.2	16	
1PGSMB5949H	P949B	95.00	100	105.00	3.7	250	3100	0.25	1	76.0	15	
1PGSMB5950H	P950B	104.50	110	115.50	3.4	300	4000	0.25	1	83.6	13	
1PGSMB5951H	P951B	114.00	120	126.00	3.1	360	4500	0.25	1	91.2	12	
1PGSMB5952H	P952B	123.50	130	136.50	2.9	450	5000	0.25	1	98.8	11	
1PGSMB5953H	P953B	142.50	150	157.50	2.5	600	6000	0.25	1	114.0	10	
1PGSMB5954H	P954B	152.00	160	168.00	2.3	700	6500	0.25	1	121.6	9	
1PGSMB5955H	P955B	171.00	180	189.00	2.1	900	7000	0.25	1	136.8	8	
1PGSMB5956H	P956B	190.00	200	210.00	1.9	1200	8000	0.25	1	152.0	7	

Notes:

1. Tolerance and type number designation the type numbers listed indicate a tolerance of 5%
2. Zener voltage (V_Z) measurement Nominal Zener voltage is measured with the device junction in thermal equilibrium with ambient temperature 25°C
3. Zener impedance (Z_Z) derivation : Z_{VT} and Z_{ZK} are measured by dividing the AC voltage drop across the device by the AC current applied.
4. The specified limits are for I_Z (AC) = 0.1 I_Z (DC) with the AC frequency = 60Hz

ORDERING INFORMATION

ORDERING CODE⁽¹⁾	PACKAGE	PACKING
1PGSMB59xH	DO-214AA (SMB)	3,000 / Tape & Reel

Notes:

1. "x" defines voltage from 11V(1PGSMB5926H) to 200V(1PGSMB5956H)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Steady State Power Derating




Fig.2 Typical Junction Capacitance






Fig.3 Typical Zener Impedance




PACKAGE OUTLINE DIMENSIONS

DO-214AA (SMB)



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	1.95	2.65	0.077	0.104
A1	0.05	0.20	0.002	0.008
b	1.95	2.20	0.077	0.087
c	0.15	0.31	0.006	0.012
D	3.30	3.95	0.130	0.156
E	5.10	5.60	0.201	0.220
E1	4.05	4.60	0.159	0.181
L	0.75	1.60	0.030	0.063

SUGGESTED PAD LAYOUT



Symbol	Unit (mm)	Unit (inch)
A	2.30	0.091
B	2.50	0.098
C	4.30	0.169
D	1.80	0.071
E	6.80	0.268

MARKING DIAGRAM



P/N = Marking Code
 G = Green Compound
 YW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[1PGSMB5929HR5G](#) [1PGSMB5930HR5G](#) [1PGSMB5927HR5G](#) [1PGSMB5926HR5G](#) [1PGSMB5956HR5G](#)
[1PGSMB5934HR5G](#) [1PGSMB5935HR5G](#) [1PGSMB5942HR5G](#) [1PGSMB5933HR5G](#) [1PGSMB5951HR5G](#)
[1PGSMB5926H](#) [1PGSMB5927H](#) [1PGSMB5928H](#) [1PGSMB5929H](#) [1PGSMB5930H](#) [1PGSMB5931H](#) [1PGSMB5932H](#)
[1PGSMB5933H](#) [1PGSMB5934H](#) [1PGSMB5935H](#) [1PGSMB5936H](#) [1PGSMB5937H](#) [1PGSMB5938H](#)
[1PGSMB5939H](#) [1PGSMB5940H](#) [1PGSMB5941H](#) [1PGSMB5942H](#) [1PGSMB5943H](#) [1PGSMB5944H](#) [1PGSMB5945H](#)
[1PGSMB5946H](#) [1PGSMB5947H](#) [1PGSMB5948H](#) [1PGSMB5949H](#) [1PGSMB5950H](#) [1PGSMB5951H](#)
[1PGSMB5952H](#) [1PGSMB5953H](#) [1PGSMB5954H](#) [1PGSMB5955H](#) [1PGSMB5956H](#)