

2A, 50V - 1000V Standard Bridge Rectifier

FEATURES

- AEC-Q101 qualified available
- Glass passivated chip junction
- Ideal for printed circuit board
- High case dielectric strength
- Typical IR less than 0.1 μ A
- UL Recognized File # E-326243
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21



APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- Lighting application

MECHANICAL DATA

- Case: GBL
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Meet JESD 201 class 2 whisker test
- Polarity: As marked
- Weight: 2.00g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	2	A
V_{RRM}	50 - 1000	V
I_{FSM}	60	A
$T_{J\ MAX}$	150	°C
Package	GBL	
Configuration	Quad	



ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	SYMBOL	GBL 201	GBL 202	GBL 203	GBL 204	GBL 205	GBL 206	GBL 207	UNIT
Marking code on the device		GBL 201	GBL 202	GBL 203	GBL 204	GBL 205	GBL 206	GBL 207	
Repetitive peak reverse voltage	V_{RRM}	50	100	200	400	600	800	1000	V
Reverse voltage, total rms value	$V_{R(RMS)}$	35	70	140	280	420	560	700	V
Forward current	I_F	2							A
Surge peak forward current, 8.3ms single half sine-wave superimposed on rated load	I_{FSM}	60							A
Rating for fusing ($t < 8.3\text{ms}$)	I^2t	14.9							A ² s
Junction temperature	T_J	- 55 to +150							°C
Storage temperature	T_{STG}	- 55 to +150							°C

THERMAL PERFORMANCE

PARAMETER	SYMBOL	TYP	UNIT
Junction-to-lead thermal resistance	$R_{\theta JL}$	13	°C/W
Junction-to-ambient thermal resistance	$R_{\theta JA}$	32	°C/W

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)

PARAMETER	CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	$I_F = 2\text{A}, T_J = 25^\circ\text{C}$	V_F	-	1	V
Reverse current @ rated V_R per diode ⁽²⁾	$T_J = 25^\circ\text{C}$	I_R	-	5	μA
	$T_J = 125^\circ\text{C}$		-	500	μA
Junction capacitance per diode	1MHz, $V_R = 4.0\text{V}$	C_J	25	-	pF

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION

ORDERING CODE ⁽¹⁾⁽²⁾	PACKAGE	PACKING
GBL2x	GBL	25 / Tube
GBL2xH	GBL	25 / Tube

Notes:

1. "x" defines voltage from 50V(GBL201) to 1000V(GBL207)
2. "H" means AEC-Q101 qualified

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-Repetitive Forward Surge Current



PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	3.30	3.70	0.130	0.146
A2	0.80	1.20	0.031	0.047
b	0.90	1.10	0.035	0.043
b2	1.30	2.00	0.051	0.079
c	0.40	0.60	0.016	0.024
D	10.70	11.30	0.421	0.445
E	19.70	20.30	0.776	0.799
E2	2.30	2.70	0.091	0.106
e	4.80	5.20	0.189	0.205
L	13.00	14.00	0.512	0.551
L4	2.30	2.70	0.091	0.106

MARKING DIAGRAM



P/N = Marking Code
 G = Green Compound
 YWW = Date Code
 F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf, assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Taiwan Semiconductor:

[GBL201](#) [GBL202](#) [GBL203](#) [GBL204](#) [GBL205](#) [GBL206](#) [GBL207](#) [GBL207 D2](#) [GBL204HD2](#) [GBL202 D2](#) [GBL201](#)
[D2](#) [GBL204 D2](#) [GBL207HD2](#) [GBL202HD2](#) [GBL203HD2](#) [GBL205HD2](#) [GBL203 D2](#) [GBL206HD2](#) [GBL206 D2](#)
[GBL201HD2](#) [GBL202 C2](#) [GBL204 C2](#) [GBL205 D2](#) [GBL206 C2](#) [GBL201 C2](#) [GBL207 C2](#) [GBL203 C2](#) [GBL204 C2G](#)
[GBL204 D2G](#) [GBL205 C2G](#) [GBL205 D2G](#) [GBL206 C2G](#) [GBL206 D2G](#) [GBL207 C2G](#) [GBL207 D2G](#)