

Product availability: Non-Stock - Not normally stocked in distribution facility



Main

Range of product	Zelio Relay
Product or component type	Solid state relay
Device short name	SSM
Number of channels	1
Phase	1 phase

Complementary

Mounting support	Symmetrical DIN rail
Line Rated Current	12 A
Output voltage	48...600 V AC
[Uc] control circuit voltage	18...36 V AC
Contacts type and configuration	1 NO
Tightening torque	Input : 0.5...0.8 N.m Output : 0.5...0.8 N.m
Connections - terminals	Screw terminals : 1 x 0.3...1 x 1.5 mm ² , (AWG 22...AWG 16) input Screw terminals : 1 x 0.3...1 x 2.5 mm ² , (AWG 22...AWG 14) output
Maximum capacitance	10 pF input/output
Insulation resistance	1000 MOhm at 500 V DC
Local signalling	LED green input status
Minimum switching voltage	18 V AC turn-on
Maximum switching voltage	4 V AC turn-off
Input current	3.5...8.5 mA
Solid state output type	SCR output Random voltage switching
Load current	0.15...6 A
Transient overvoltage	1200 V
Surge current	715 A for 16.6 ms 750 A for 20 ms
Voltage drop	<= 1.3 V on-state
Motor power hp	0.33 hp at <= 40 °C 240 V AC
Maximum I ² t for fusing	2560 A ² .s 10 ms at 50 Hz half cycle 2330 A ² .s 8.33 ms at 60 Hz half cycle
Leakage current	<= 0.2 mA off-state
DV/dt	500 V/μs off-state at maximum voltage
Response time	30 ms turn-off 20 ms turn-on
Power factor	0.5 with maximum load
Overvoltage category	III
Width	0.71 in (18 mm)
Height	90.3 mm
Depth	83.7 mm
Product weight	0.2 lb(US) (0.09 kg)

Environment

Flame retardance	V0 conforming to UL 94
Dielectric strength	4 kV AC input/output 4 kV AC input or output to case
Pollution degree	2
Standards	IEC 61000 IEC 60950-1 IEC 62314
Product certifications	CSA UL REACH
Marking	CE
IP degree of protection	IP20
Ambient air temperature for operation	-22...176 °F (-30...80 °C)
Ambient air temperature for storage	-22...212 °F (-30...100 °C)


Ordering and shipping details

Category	22375 - INTERFACE MODULE(ABA,R,S)
Discount Schedule	CP2
GTIN	00785901952350
Nbr. of units in pkg.	1
Package weight(Lbs)	0.20000000000000001
Returnability	N
Country of origin	MX


Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1328 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Available
California proposition 65	WARNING: This product can expose you to chemicals including:
- - - - - Substance 1	Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm.
- - - - - More information	For more information go to www.p65warnings.ca.gov

Dimensions



Derating Curves



A : Load Current (Amperes)

B : Ambient Temperature (°C)

1 : Multiple units, no minimum spacing between components

2 : Installed single unit, distance to adjacent components more than 18 mm

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[SSM1A312B7R](#)