

20A, 35V - 200V Schottky Barrier Rectifier

FEATURES

- Low power loss, high efficiency
- Guard ring for overvoltage protection
- High surge current capability
- RoHS Compliant
- Halogen-free according to IEC 61249-2-21



APPLICATIONS

- Switching mode power supply (SMPS)
- Adapters
- DC to DC converters

MECHANICAL DATA

- Case: TO-220AB
- Molding compound meets UL 94V-0 flammability rating
- Terminal: Matte tin plated leads, solderable per J-STD-002
- Mounting torque: 0.56 N·m maximum
- Meet JESD 201 class 1A whisker test
- Polarity: As marked
- Weight: 1.88g (approximately)

KEY PARAMETERS		
PARAMETER	VALUE	UNIT
I_F	20	A
V_{RRM}	35 - 200	V
I_{FSM}	150	A
T_{JMAX}	150	°C
Package	TO-220AB	
Configuration	Dual dies	


TO-220AB


ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)										
PARAMETER	SYMBOL	MBR 2035 CT-Y	MBR 2045 CT-Y	MBR 2050 CT-Y	MBR 2060 CT-Y	MBR 2090 CT-Y	MBR 20100 CT-Y	MBR 20150 CT-Y	MBR 20200 CT-Y	UNIT
Marking code on the device		MBR 2035 CT	MBR 2045 CT	MBR 2050 CT	MBR 2060 CT	MBR 2090 CT	MBR 20100 CT	MBR 20150 CT	MBR 20200 CT	
Repetitive peak reverse voltage	V_{RRM}	35	45	50	60	90	100	150	200	V
Reverse voltage, total rms value	$V_{R(RMS)}$	24	31	35	42	63	70	105	140	V
Forward current	I_F	20								A
Surge peak forward current, 8.3ms single half sine wave superimposed on rated load	I_{FSM}	150								A
Peak repetitive reverse surge current ⁽¹⁾	I_{RRM}	1		0.5						A
Peak repetitive forward current (Rated V_R , Square wave, 20KHz)	I_{FRM}	20								A

ABSOLUTE MAXIMUM RATINGS ($T_A = 25^\circ\text{C}$ unless otherwise noted)									
PARAMETER	SYMBOL	MBR 2035 CT-Y	MBR 2045 CT-Y	MBR 2050 CT-Y	MBR 2060 CT-Y	MBR 2090 CT-Y	MBR 20100 CT-Y	MBR 20150 CT-Y	UNIT
Critical rate of rise of off-state voltage	dv/dt	10,000							V/ μs
Junction temperature	T_J	-55 to +150							$^\circ\text{C}$
Storage temperature	T_{STG}	-55 to +150							$^\circ\text{C}$

Notes:

- $t_p = 2.0\mu\text{s}$, 1.0KHz

THERMAL PERFORMANCE				
PARAMETER		SYMBOL	TYP	UNIT
Junction-to-case thermal resistance	MBR2035CT-Y MBR2045CT-Y MBR2050CT-Y MBR2060CT-Y	$R_{\theta\text{JC}}$	1	$^\circ\text{C/W}$
Junction-to-case thermal resistance	MBR2090CT-Y MBR20100CT-Y MBR20150CT-Y MBR20200CT-Y	$R_{\theta\text{JC}}$	2	$^\circ\text{C/W}$

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Forward voltage per diode ⁽¹⁾	MBR2035CT-Y MBR2045CT-Y	$I_F = 10\text{A}$, $T_J = 25^\circ\text{C}$	V_F	-	-	V
	MBR2050CT-Y MBR2060CT-Y			-	0.80	V
	MBR2090CT-Y MBR20100CT-Y			-	0.85	V
	MBR20150CT-Y MBR20200CT-Y			-	0.99	V
	MBR2035CT-Y MBR2045CT-Y			$I_F = 20\text{A}$, $T_J = 25^\circ\text{C}$	-	0.84
	MBR2050CT-Y MBR2060CT-Y	-			0.95	V
	MBR2090CT-Y MBR20100CT-Y	-			1.23	V
	MBR20150CT-Y MBR20200CT-Y	-			0.57	V
	MBR2035CT-Y MBR2045CT-Y	$I_F = 10\text{A}$, $T_J = 125^\circ\text{C}$			-	0.70
	MBR2050CT-Y MBR2060CT-Y			-	0.75	V
	MBR2090CT-Y MBR20100CT-Y			-	0.87	V
	MBR20150CT-Y MBR20200CT-Y			-	0.72	V
	MBR2035CT-Y MBR2045CT-Y			$I_F = 20\text{A}$, $T_J = 125^\circ\text{C}$	-	0.85
	MBR2050CT-Y MBR2060CT-Y	-			1.10	V
	MBR2090CT-Y MBR20100CT-Y	-				
	MBR20150CT-Y MBR20200CT-Y	-				

ELECTRICAL SPECIFICATIONS ($T_A = 25^\circ\text{C}$ unless otherwise noted)						
PARAMETER		CONDITIONS	SYMBOL	TYP	MAX	UNIT
Reverse current @ rated V_R per diode ⁽²⁾	MBR2035CT-Y MBR2045CT-Y MBR2050CT-Y MBR2060CT-Y MBR2090CT-Y MBR20100CT-Y MBR20150CT-Y MBR20200CT-Y	$T_J = 25^\circ\text{C}$	I_R	-	100	μA
	MBR2035CT-Y MBR2045CT-Y	$T_J = 125^\circ\text{C}$		-	15	mA
	MBR2050CT-Y MBR2060CT-Y			-	10	mA
	MBR2090CT-Y MBR20100CT-Y MBR20150CT-Y MBR20200CT-Y			-	5	mA
				-	0.15	mA

Notes:

1. Pulse test with $PW = 0.3\text{ms}$
2. Pulse test with $PW = 30\text{ms}$

ORDERING INFORMATION		
ORDERING CODE⁽¹⁾	PACKAGE	PACKING
MBR20xCT-Y	TO-220AB	50 / Tube

Notes:

1. "x" defines voltage from 35V(MBR2035CT-Y) to 200V(MBR20200CT-Y)

CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.1 Forward Current Derating Curve




Fig.2 Typical Junction Capacitance




Fig.3 Typical Reverse Characteristics




Fig.4 Typical Forward Characteristics






Fig.5 Maximum Non-Repetitive Forward Surge Current




CHARACTERISTICS CURVES

($T_A = 25^\circ\text{C}$ unless otherwise noted)

Fig.6 Typical Transient Thermal Impedance



PACKAGE OUTLINE DIMENSIONS



DIM.	Unit (mm)		Unit (inch)	
	Min.	Max.	Min.	Max.
A	4.42	4.76	0.174	0.187
A2	2.20	2.80	0.087	0.110
b	0.68	0.94	0.027	0.037
b2	1.14	1.77	0.045	0.070
c	0.35	0.64	0.014	0.025
c2	1.14	1.40	0.045	0.055
D	14.60	16.00	0.575	0.630
D1	2.62	3.44	0.103	0.135
D2	5.84	6.86	0.230	0.270
E	-	10.50	-	0.413
e	2.41	2.67	0.095	0.105
L	13.19	14.79	0.519	0.582
L4	2.80	4.20	0.110	0.165
P	3.54	4.00	0.139	0.157

MARKING DIAGRAM



- P/N = Marking Code
- G = Green Compound
- YWW = Date Code
- F = Factory Code

Notice

Specifications of the products displayed herein are subject to change without notice. TSC or anyone on its behalf assumes no responsibility or liability for any errors or inaccuracies.

Purchasers are solely responsible for the choice, selection, and use of TSC products and TSC assumes no liability for application assistance or the design of Purchasers' products.

Information contained herein is intended to provide a product description only. No license, express or implied, to any intellectual property rights is granted by this document. Except as provided in TSC's terms and conditions of sale for such products, TSC assumes no liability whatsoever, and disclaims any express or implied warranty, relating to sale and/or use of TSC products including liability or warranties relating to fitness for a particular purpose, merchantability, or infringement of any patent, copyright, or other intellectual property right.

The products shown herein are not designed for use in medical, life-saving, or life-sustaining applications. Customers using or selling these products for use in such applications do so at their own risk and agree to fully indemnify TSC for any damages resulting from such improper use or sale.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Taiwan Semiconductor:](#)

[MBR20100CT-Y](#) [MBR20150CT-Y](#) [MBR20200CT-Y](#) [MBR2045CT-Y](#) [MBR2060CT-Y](#)