



Main

Range of Product	Zelio Time
Product or Component Type	Industrial timing relay
Contacts type and composition	1 C/O timed contact, AgNi (cadmium free)
Component name	RE88865
Time delay type	L Li
Time delay range	10 min 10 h 1 min 10 s 100 h 1 h 1 s

Complementary

Discrete output type	Relay
Width pitch dimension	0.89 in (22.5 mm)
[Us] rated supply voltage	24 V DC 24...240 V AC 50/60 Hz
Voltage range	0.85...1.1 Us
Connections - terminals	Screw terminals, 2 x 1.5 mm ² with cable end Screw terminals, 2 x 2.5 mm ² without cable end
Housing material	Self-extinguishing
Repeat accuracy	+/- 0.5 % IEC 61812-1
Temperature Drift	+/- 0.05 %/°C
Voltage drift	+/- 0.2 %/V
Setting accuracy of time delay	+/- 10 % of full scale 25 °C IEC 61812-1
Minimum pulse duration	100 Ms under load 30 ms
Maximum reset time	100 ms on de-energisation
On-load factor	100 %
Maximum power consumption	32 VA 240 V
Maximum power consumption	0.6 W 24 V 1.5 W 240 V
Breaking capacity	2000 VA
Breaking capacity	80 W
Minimum switching current	10 mA
Maximum switching current	8 A
Maximum switching voltage	250 V
Electrical durability	100000 cycles 8 A, 250 V resistive
Mechanical durability	5000000 cycles
[Uimp] rated impulse withstand voltage	5 kV 1.2...50 µs IEC 60664-1 5 kV 1.2...50 µs IEC 61812-1
Marking	CE
Creepage distance	4 kV/3 IEC 60664-1
Surge withstand	1 kV differential mode IEC 61000-4-5 level 3 2 kV common mode IEC 61000-4-5 level 3
Mounting support	35 mm symmetrical mounting rail conforming to EN 50022

Local signalling	For flashing: timing in progress LED indicator (green) For on steady: relay energised, no timing in progress LED indicator (green) LED indicator (green)
Net Weight	0.20 lb(US) (0.09 kg)

Environment

Immunity to microbreaks	10 ms
Dielectric strength	2.5 kV 1 mA/1 minute 50 Hz IEC 61812-1
Standards	IEC 60669-2-3 93/68/EEC 73/23/EEC IEC 61812-1 89/336/EEC EN 50082-1/2 EN 50081-1/2
Product certifications	CULus CSA GL
Ambient Air Temperature for Operation	-4...140 °F (-20...60 °C)
Ambient Air Temperature for Storage	-22...140 °F (-30...60 °C)
IP degree of protection	IP20 IEC 60529 terminal block) IP40 IEC 60529 housing) IP50 IEC 60529 front face)
Vibration resistance	0.35 mm 10...55 Hz)IEC 60068-2-6
Relative Humidity	93 % without condensation IEC 60068-2-3
Resistance to electrostatic discharge	6 kV in contact EN/IEC 61000-4-2 level 3 8 kV in air EN/IEC 61000-4-2 level 3
Resistance to electromagnetic fields	9.14 V/m (10 V/m) 80 MHz to 1 GHz ENV 50140/204 level 3 9.14 V/m (10 V/m) 80 MHz to 1 GHz IEC 61000-4-3 level 3
Resistance to fast transients	1 kV IEC 61000-4-4 level 3 capacitive connecting clip) 2 kV IEC 61000-4-4 level 3 direct)
Immunity to radioelectric fields	10 V 0.15...80 MHz)ENV 50141 (IEC 61000-4-6)
Immunity to voltage dips	30 % / 10 ms IEC 61000-4-11 60 % / 100 ms IEC 61000-4-11 95 % / 5 s IEC 61000-4-11
Disturbance radiated/conducted	Class B EN 55022 (EN 55011 group 1)

Ordering and shipping details

Category	22370-RE, RM MISC TIMERS & COUNTERS
Discount Schedule	CP2
GTIN	00785901573777
Package weight(Lbs)	0.23 lb(US) (0.103 kg)
Returnability	No
Country of origin	FR


Packing Units

Package 1 Height	0.280 dm
Package 1 width	0.880 dm
Package 1 Length	1.100 dm


Contractual warranty

Warranty	18 months
----------	-----------

Width 22.5 mm



Wiring Diagram



1 Link A1-Y1 for function L only.

Function L : Asymmetrical Flasher Relay (Starting Pulse Off)

Description

Repetitive cycle comprises of two, independently adjustable timing periods T_a and T_r . Each timing period corresponds to a different state of the output R.

Function: 1 Output



Function Li : Asymmetrical Flasher Relay (Starting Pulse On)

Description

Repetitive cycle comprises of two, independently adjustable timing periods T_a and T_r . Each timing period corresponds to a different state of the output R.

Function: 1 Output



Legend

Relay de-energised

Relay energised

 Output open

 Output closed

C	Control contact
G	Gate
R	Relay or solid state output
R1/R2	2 timed outputs
R2 inst.	The second output is instantaneous if the right position is selected
T	Timing period
T_a -	Adjustable On-delay
T_r -	Adjustable Off-delay
U	Supply

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Schneider Electric:](#)

[RE88865155](#)